HPE Networking CW 2150 Switch Series



What's new

- Enterprise-class, fully managed, stackable Layer 3 switch series with 8, 16, 24, and 48port Class 4 PoE and nonPoE models, four 1G/10G SFP+ uplinks, and up to 770W of Class 4 PoE
- Up to 176 Gbps in nonblocking bandwidth, 130 Mpps in forwarding, and up to 9switch IRF stack
- Flexible connectivity options with four 1G/10G SFP+ uplinks in the 16, 24, and 48port models and two 1G SFP and two 1G/10G SFP+ uplinks in the 8port model
- Advanced Quality of Service (QoS), IPv6, and dynamic L3 protocols (RIP and OSPF) for reliable connectivity

Overview

HPE Networking CW 2150 Switch Series empowers your business with reliable, high-performance networking tailored for small and medium-sized businesses and branch offices. These fully managed, stackable Layer 3 switches deliver enterprise-grade features without the complexity or high cost. With CW 2150 series, you get seamless management, robust security, and flexibility to scale as your needs grow. Designed for today's evolving networks, these switches provide affordable excellence—enabling you to connect and protect your business with confidence. Upgrade to the CW 2150 series and experience secure, simple, and powerful networking for your organization.

– Fanless design in the 8port and 24/48port nonPoE models. Supports IEEE 802.3az standard for Energy Efficient Ethernet (EEE)

– Managed by Web GUI, CLI, Smart Management Center (SmartMC) web dashboard, HPE Intelligent Management Center (IMC), SNMP, and REST APIs

Features

Enterprise-class secure and reliable connectivity

The HPE Networking CW 2150 Switch Series delivers up to 176Gbps of nonblocking bandwidth and up to 131Mpps forwarding, with nine unit IRF stacking for resilient availability and link redundancy.

The CW 2150 series offers flexible connectivity with four 1G/10G SFP+ uplinks on the 16, 24, and 48 port models, and two 1G SFP plus two 1G/10G SFP+ uplinks on the 8 port model. The 24 port model adds four SFP combo ports.

Advanced Quality of Service (QoS), Internet Protocol version 6 (IPv6) and dynamic L3 protocols (RIP and OSPF) for reliable connectivity

It supports IEEE802.3az Energy Efficient Ethernet and offers a fanless design on the 8, 24, and 48port nonPoE models.

Builtin 6kV serviceport surge protection helps reduce the risk of power strikes in demanding environments such as construction sites.

Powerful PoE capabilities

The HPE Networking CW2150 Switch Series provides 125W, 248W, 405W, 390W, and 770W Class4 PoE across the 8, 16, 24, and 48port models.

It supports advanced PoE features, including fast PoE that delivers power within seconds of system startup.

Perpetual PoE supports enddevice state monitoring to help maintain power during a powersource reboot.

The PoE Watchdog function automatically removes power from a port when the connected device is no longer active.

Comprehensive security control

The HPE Networking CW2150 Switch Series provides security features and network management for modern SMB environments. Secure boot verifies digital signatures to help prevent unauthorized or malicious software from loading at startup.

With HPE IMC, the CW2150 series supports EAD by integrating terminalsecurity policies, networkaccess control, and accessrights enforcement into a unified security framework.

It delivers multilayer access protection with granular ACLs (IPv4/IPv6, VLAN, portbased), identitydriven policies, and authentication options including 802.1X, MAC, Web, RADIUS, TACACS+, plus Guest VLAN detection and dualNIC detection with IMC.

The CW2150 series provides encrypted access using SSHv2, SSL, SNMPv3, and TLS, along with rolebased privileges and audit logging.

Threatprevention features include Control Plane Policing (DoS protection), ARP and DHCP protection, ICMP throttling, port security, and sourceport filtering.

Simple and flexible management

The HPE Networking CW2150 Switch Series offers Web GUI, industrystandard CLI management and can be managed with other CW switches through a built-in dashboard for simplified deployment and centralized management.

Advanced management options include HPE Intelligent Management Center (IMC), HPE Networking Management Software (AirWave), SNMP managers, and REST APIs for integration with existing customer dashboards.

Technical specifications	HPE Networking CW 2150 Switch Series
Power consumption	No load: 16–35W, single AC Typical: 8–54W, single AC
Heat dissipation	119–3306 BTU/hr depending on configuration
Input voltage	Rated voltage range: 100–240V AC at 50 Hz or 60 Hz Maximum voltage range: 90–264V AC at 47 Hz to 63 Hz
Ports	8-port model: 8x 10/100/1000BASE-T, 2x 1000BASE-X SFP ports and 2x 1/10GBASE-X SFP+ ports, or 8x 10/100/1000BASE-T PoE+, 2x 1000BASE-X SFP ports and 2x 1/10GBASE-X SFP+ ports 16-port model: 16x 10/100/1000BASE-T PoE+ (125W) ports and 4x 1/10GBASE-X SFP+ ports 24-port model: 24x 10/100/1000BASE-T ports, or 24x 10/100/1000BASE-T PoE+ and 4x 100/1000BASE-X SFP Combo ports, and 4x 1/10GBASE-X SFP+ ports 48-port model: 48x 10/100/1000BASE-T ports, or 48x 10/100/1000BASE-T PoE+ (390W) ports, or 48x 10/100/1000BASE-T PoE+ (770W) ports, and 4x 1/10GBASE-X SFP+ ports Management ports: 1x RJ-45 console, 1x USB Type-C console, 1x USB and 1x OOBM management
Latency	1 GE: < 5µs 10 GE: < 3µs (64-byte packets)
Switching capacity	60–176 Gbps depending on model
Stacking capabilities	9 member IRF stack
Throughput	44–131 Mpps depending on model
Memory and processor	CPU: Dual-core Arm® at 1.2 GHz Flash: 512 MB SDRAM: 1 GB
Power supply	Fixed, 90–264V, single AC
PoE capability	125–770W depending on model
Management features	Web GUI Command Line Interface (CLI) Smart Management Center (SmartMC) HPE Intelligence Management Center (IMC) HPE Networking Management Software (AirWave) REST API SNMP
Operating temperature	-5°C–50°C (23°F–122°F)
Warranty	Limited lifetime hardware warranty. See the warranty duration.

SKU comparison

	HPE Networking CW 2150 16p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 248W Switch (S6X55A)	HPE Networking CW 2150 24p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X50A)	HPE Networking CW 2150 24p 10M/100M/1G PoE+ 4p SFP 1G Combo 4p SFP+ 1G/10G 405W Switch (S6X51A)	HPE Networking CW 2150 48p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X52A)	HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 390W Switch (S6X53A)
Differentiator	16p 10M/100M/1000M, 4p SFP+, 248W PoE+	24p 10M/100M/1000M, 4p SFP+	24p 10M/100M/1000M, 4p SFP 4p SFP+ Copper and Fiber Combo ports, 405W PoE+	8p 10M/100M/1000M, 4p SFP+	48p 10M/100M/1000M, 4p SFP+, 390W PoE+
Power consumption	Idle: 25W Typical: 38W Full load: 317W (PoE 248W)	Idle: 6W Typical: 16W Full load: 21W	Idle: 23W Typical: 35W Full load: 465W (PoE 405W)	Idle: 13W Typical: 31W Full load: 42W	Idle: 29W Typical: 54W Full load: 512W (PoE 390W)
Heat dissipation	85–1982 BTU/hr depending on configuration	28–65 BTU/hr depending on configuration	78–1587 BTU/hr depending on configuration	44–143 BTU/hr depending on configuration	99–1747 BTU/hr depending on configuration
Input voltage	Rated voltage range: 100–240V AC at 50 Hz or 60 Hz Maximum voltage range: 90–264V AC at 47 Hz to 63 Hz				
Ports	16 x 10/100/1000BASE-T PoE+ ports 4 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management	24 x 10/100/1000BASE-T ports 4 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management	24 x 10/100/1000BASE-T PoE+ ports 4 x 100/1000BASE-X SFP Combo ports 4 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management	48 x 10/100/1000BASE-T ports 4 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management	48 x 10/100/1000BASE-T PoE+ ports 4 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management
Latency	1 GE: < 5µs 10 GE: < 3µs (64-byte packets)				
Switching capacity	112 Gbps	128 Gbps	128 Gbps	176 Gbps	176 Gbps
Stacking capabilities	9 member IRF stack				

	HPE Networking CW 2150 16p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 248W Switch (S6X55A)	HPE Networking CW 2150 24p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X50A)	HPE Networking CW 2150 24p 10M/100M/1G PoE+ 4p SFP 1G Combo 4p SFP+ 1G/10G 405W Switch (S6X51A)	HPE Networking CW 2150 48p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X52A)	HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 390W Switch (S6X53A)
Throughput	83 Mpps	95 Mpps	95 Mpps	130 Mpps	130 Mpps
Memory and processor	CPU: Dual-core Arm® at 1.2 GHz Flash: 512 MB SDRAM: 1 GB				
Power supply	Fixed, 90–264V, single AC				
PoE capability	248W	non-PoE	405W	non-PoE	non-PoE
Management features	Web GUI Command Line Interface (CLI) Smart Management Center (SmartMC) HPE Intelligence Management Center (IMC) HPE Networking Management Software (AirWave) REST API SNMP				
Operating temperature	-5°C–50°C (23°F–122°F)				
Warranty	Limited lifetime hardware warranty. See the warranty duration.				

	HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 770W Switch (S6X54A)	HPE Networking CW 2150 8p 10M/100M/1G 2p SFP 1G 2p SFP+ 1G/10G Switch (S6X56A)	HPE Networking CW 2150 8p 10M/100M/1G PoE+ 2p SFP 1G 2p SFP+ 1G/10G 125W Switch (S6X57A)
Differentiator	48p 10M/100M/1000M, 4p SFP+, 770W PoE+	8p 10M/100M/1000M, 2p SFP, 2p SFP+	8p 10M/100M/1000M, 2p SFP, 2p SFP+ 125W PoE+
Power consumption	Idle: 35W Typical: 56W Full load: 969W (PoE 770W)	Idle: 5W Typical: 8W Full load: 16W	Idle: 8W Typical: 10W Full load: 152W (PoE 125W)
Heat dissipation	119–3306 BTU/hr depending on configuration	17–55 BTU/hr depending on configuration	27–519 BTU/hr depending on configuration
Input voltage	Rated voltage range: 100–240V AC at 50 Hz or 60 Hz Maximum voltage range: 90–264V AC at 47 Hz to 63 Hz		
Ports	48 x 10/100/1000BASE-T PoE+ ports 4 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management	8 x 10/100/1000BASE-T ports 2 x 1000BASE-X SFP ports 2 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management	8 x 10/100/1000BASE-T PoE+ ports 2 x 1000BASE-X SFP ports 2 x 1/10GBASE-X SFP+ ports 1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management
Latency	1 GE: < 5µs 10 GE: < 3µs (64-byte packets)		
Switching capacity	176 Gbps	60 Gbps	60 Gbps
Stacking capabilities	9 member IRF stack		
Throughput	130 Mpps	44 Mpps	44 Mpps
Memory and processor	CPU: Dual-core Arm® at 1.2 GHz Flash: 512 MB SDRAM: 1 GB		
Power supply	Fixed, 90–264V, single AC		
PoE capability	770W	non-PoE	125W

	HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 770W Switch (S6X54A)	HPE Networking CW 2150 8p 10M/100M/1G 2p SFP 1G 2p SFP+ 1G/10G Switch (S6X56A)	HPE Networking CW 2150 8p 10M/100M/1G PoE+ 2p SFP 1G 2p SFP+ 1G/10G 125W Switch (S6X57A)
Management features	Web GUI Command Line Interface (CLI) Smart Management Center (SmartMC) HPE Intelligence Management Center (IMC) HPE Networking Management Software (AirWave) REST API SNMP		
Operating temperature	-5°C–50°C (23°F–122°F)		
Warranty	Limited lifetime hardware warranty. See the warranty duration.		

Related Options

The following options are available for these series:

SKU	Description
Cables/Cable Kits	
JD095C	HPE Networking X240 10G SFP+ SFP+ 0.65m DAC Cable
JD096C	HPE Networking X240 10G SFP+ SFP+ 1.2m DAC Cable
JD097C	HPE Networking X240 10G SFP+ SFP+ 3m DAC Cable
JG081C	HPE Networking X240 10G SFP+ SFP+ 5m DAC Cable
Mounting Rack/Rail Options	
R8M91A	HPE Networking Comware 5140 Rack Mount Kit
Transceiver Options	
JL290A	HPE Networking X2A0 10G SFP+ to SFP+ 7m Active Optical Cable
JL291A	HPE Networking X2A0 10G SFP+ to SFP+ 10m Active Optical Cable
JL292A	HPE Networking X2A0 10G SFP+ to SFP+ 20m Active Optical Cable
JD099B	HPE Networking X120 1G SFP LC BX 10-D Transceiver
JD098B	HPE Networking X120 1G SFP LC BX 10-U Transceiver
JD103A	HPE Networking X120 1G SFP LC LH100 Transceiver
JD119B	HPE Networking X120 1G SFP LC LX Transceiver
JD118B	HPE Networking X120 1G SFP LC SX Transceiver
JD089B	HPE Networking X120 1G SFP RJ45 T Transceiver
JL738A	HPE Networking X130 10G SFP+ LC BiDi 10km-Downlink Transceiver
JL737A	HPE Networking X130 10G SFP+ LC BiDi 10km-Uplink Transceiver
JL740A	HPE Networking X130 10G SFP+ LC BiDi 40km-Downlink Transceiver
JL739A	HPE Networking X130 10G SFP+ LC BiDi 40km-Uplink Transceiver
JG234A	HPE Networking X130 10G SFP+ LC ER 40km Transceiver
JG915A	HPE Networking X130 10G SFP+ LC LH 80km Transceiver
JD094B	HPE Networking X130 10G SFP+ LC LR Transceiver
JD092B	HPE Networking X130 10G SFP+ LC SR Transceiver

Related Services

The following services are available for these series:

SKU	Description
Technology Services	
H10PGE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 8P POE Swch Service
H10LVE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 8P Swch Service
H10ZWE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 16P Swch Service
H11GTE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 24P POE Swch Service
H11DHE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 24P Swch Service
H11MRE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 48P POE Swch Service
H11QCE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 48P POE+ Swch Service
H11KFE	HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 48P Swch Service
H11RRE	HPE Aruba Networking Foundational Care 1Y 4HR Exch EDU/RET 2150 48P POE+ Swch Service
H10PLE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 8P POE Swch Service
H10LZE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 8P Swch Service
H11BBE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 16P Swch Service
H11GYE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 24P POE Swch Service
H11DME	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 24P Swch Service
H11MWE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 48P POE Swch Service
H11QHE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 48P POE+ Swch Service
H11KKE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 48P Swch Service
H10PME	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 8P POE Swch Service
H10MBE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 8P Swch Service
H11BCE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 16P Swch Service
H11GZE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 24P POE Swch Service
H11DNE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 24P Swch Service
H11MXE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 48P POE Swch Service
H11QJE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 48P POE+ Swch Service
H11KLE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 48P Swch Service
H10NLE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite EDU/RET 2150 8P Swch Service
H11CME	HPE Aruba Networking Foundational Care 1Y 4HR Onsite EDU/RET 2150 16P Swch Service
H11RTE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite EDU/RET 2150 48P POE+ Swch Service
H10PKE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 8P POE Swch Service
H10LYE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 8P Swch Service
H10ZZE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 16P Swch Service
H11GXE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 24P POE Swch Service
H11DLE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 24P Swch Service

H11MVE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 48P POE Swch Service
H11QGE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 48P POE+ Swch Service
H11KJE	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 48P Swch Service
H10PNE	HPE Aruba Networking Foundational Care 1Y CTR 2150 8P POE Swch Service
H10MCE	HPE Aruba Networking Foundational Care 1Y CTR 2150 8P Swch Service
H11BDE	HPE Aruba Networking Foundational Care 1Y CTR 2150 16P Swch Service
H11HBE	HPE Aruba Networking Foundational Care 1Y CTR 2150 24P POE Swch Service
H11DQE	HPE Aruba Networking Foundational Care 1Y CTR 2150 24P Swch Service
H11MYE	HPE Aruba Networking Foundational Care 1Y CTR 2150 48P POE Swch Service
H11QKE	HPE Aruba Networking Foundational Care 1Y CTR 2150 48P POE+ Swch Service
H11KME	HPE Aruba Networking Foundational Care 1Y CTR 2150 48P Swch Service
H10PQE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 8P POE Swch Service
H10MDE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 8P Swch Service
H11BFE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 16P Swch Service
H11HCE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 24P POE Swch Service
H11DRE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 24P Swch Service
H11MZE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 48P POE Swch Service
H11QLE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 48P POE+ Swch Service
H11KNE	HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 48P Swch Service
H10QYE	HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 8P POE Swch Service
H11CNE	HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 16P Swch Service
H11PJE	HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 48P POE Swch Service
H11RVE	HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 48P POE+ Swch Service
H10PDE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 8P POE Swch Service
H10LSE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 8P Swch Service
H10ZTE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 16P Swch Service
H11GRE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 24P POE Swch Service
H11DFE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 24P Swch Service
H11MNE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 48P POE Swch Service
H11PZE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 48P POE+ Swch Service
H11KCE	HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 48P Swch Service
H11RQE	HPE Aruba Networking Foundational Care 1Y NBD Exch EDU/RET 2150 48P POE+ Swch Service
H10PFE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 8P POE Swch Service
H10LTE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 8P Swch Service
H10ZVE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 16P Swch Service
H11GSE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 24P POE Swch Service

H11DGE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 24P Swch Service
H11MQE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 48P POE Swch Service
H11QBE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 48P POE+ Swch Service
H11KDE	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 48P Swch Service
H10PHE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 8P POE Swch Service
H10LWE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 8P Swch Service
H10ZXE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 16P Swch Service
H11GVE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 24P POE Swch Service
H11DJE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 24P Swch Service
H11MSE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 48P POE Swch Service
H11QDE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 48P POE+ Swch Service
H11KGE	HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 48P Swch Service
H10PJE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 8P POE Swch Service
H10LXE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 8P Swch Service
H10ZYE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 16P Swch Service
H11GWE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 24P POE Swch Service
H11DKE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 24P Swch Service
H11MTE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 48P POE Swch Service
H11QFE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 48P POE+ Swch Service
H11KHE	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 48P Swch Service
H11JJE	HPE Aruba Networking Foundational Care 1Y NBD Onsite EDU/RET 2150 24P POE Swch Service
H11PGE	HPE Aruba Networking Foundational Care 1Y NBD Onsite EDU/RET 2150 48P POE Swch Service
H10PTE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 8P POE Swch Service
H10MHE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 8P Swch Service
H11BJE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 16P Swch Service
H11HGE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 24P POE Swch Service
H11DVE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 24P Swch Service
H11NDE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 48P POE Swch Service
H11QQE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 48P POE+ Swch Service
H11KSE	HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 48P Swch Service
H11LZE	HPE Aruba Networking Foundational Care 3Y 4HR Exch EDU/RET 2150 48P Swch Service
H10PZE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 8P POE Swch Service
H10MNE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 8P Swch Service
H11BQE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 16P Swch Service
H11HME	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 24P POE Swch Service
H11FBE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 24P Swch Service

H11NKE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 48P POE Swch Service
H11QWE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 48P POE+ Swch Service
H11KYE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 48P Swch Service
H10QBE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 8P POE Swch Service
H10MQE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 8P Swch Service
H11BRE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 16P Swch Service
H11HNE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 24P POE Swch Service
H11FCE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 24P Swch Service
H11NLE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 48P POE Swch Service
H11QXE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 48P POE+ Swch Service
H11KZE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 48P Swch Service
H10NTE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite EDU/RET 2150 8P Swch Service
H10PYE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 8P POE Swch Service
H10MME	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 8P Swch Service
H11BNE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 16P Swch Service
H11HLE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 24P POE Swch Service
H11DZE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 24P Swch Service
H11NJE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 48P POE Swch Service
H11QVE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 48P POE+ Swch Service
H11KXE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 48P Swch Service
H10QCE	HPE Aruba Networking Foundational Care 3Y CTR 2150 8P POE Swch Service
H10MRE	HPE Aruba Networking Foundational Care 3Y CTR 2150 8P Swch Service
H11BSE	HPE Aruba Networking Foundational Care 3Y CTR 2150 16P Swch Service
H11HQE	HPE Aruba Networking Foundational Care 3Y CTR 2150 24P POE Swch Service
H11FDE	HPE Aruba Networking Foundational Care 3Y CTR 2150 24P Swch Service
H11NME	HPE Aruba Networking Foundational Care 3Y CTR 2150 48P POE Swch Service
H11QYE	HPE Aruba Networking Foundational Care 3Y CTR 2150 48P POE+ Swch Service
H11LBE	HPE Aruba Networking Foundational Care 3Y CTR 2150 48P Swch Service
H10QDE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 8P POE Swch Service
H10MSE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 8P Swch Service
H11BTE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 16P Swch Service
H11HRE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 24P POE Swch Service
H11FFE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 24P Swch Service
H11NNE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 48P POE Swch Service
H11QZE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 48P POE+ Swch Service
H11LCE	HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 48P Swch Service

H11CWE	HPE Aruba Networking Foundational Care 3Y CTR EDU/RET 2150 16P Swch Service
H10PSE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 8P POE Swch Service
H10MGE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 8P Swch Service
H11BHE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 16P Swch Service
H11HFE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 24P POE Swch Service
H11DTE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 24P Swch Service
H11NCE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 48P POE Swch Service
H11QNE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 48P POE+ Swch Service
H11KRE	HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 48P Swch Service
H11PKE	HPE Aruba Networking Foundational Care 3Y NBD Exch EDU/RET 2150 48P POE Swch Service
H10PRE	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 8P POE Swch Service
H10MFE	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 8P Swch Service
H11BGE	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 16P Swch Service
H11HDE	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 24P POE Swch Service
H11DSE	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 24P Swch Service
H11NBE	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 48P POE Swch Service
H11QME	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 48P POE+ Swch Service
H11KQE	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 48P Swch Service
H10PVE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 8P POE Swch Service
H10MJE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 8P Swch Service
H11BKE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 16P Swch Service
H11HHE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 24P POE Swch Service
H11DWE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 24P Swch Service
H11NFE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 48P POE Swch Service
H11QRE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 48P POE+ Swch Service
H11KTE	HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 48P Swch Service
H10PWE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 8P POE Swch Service
H10MKE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 8P Swch Service
H11BLE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 16P Swch Service
H11HJE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 24P POE Swch Service
H11DXE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 24P Swch Service
H11NGE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 48P POE Swch Service
H11QSE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 48P POE+ Swch Service
H11KVE	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 48P Swch Service
H10NRE	HPE Aruba Networking Foundational Care 3Y NBD Onsite EDU/RET 2150 8P Swch Service
H11CSE	HPE Aruba Networking Foundational Care 3Y NBD Onsite EDU/RET 2150 16P Swch Service

H10QHE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 8P POE Swch Service
H10MWE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 8P Swch Service
H11BXE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 16P Swch Service
H11HVE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 24P POE Swch Service
H11FJE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 24P Swch Service
H11NSE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 48P POE Swch Service
H11RDE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 48P POE+ Swch Service
H11LGE	HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 48P Swch Service
H11PTE	HPE Aruba Networking Foundational Care 5Y 4HR Exch EDU/RET 2150 48P POE Swch Service
H11SFE	HPE Aruba Networking Foundational Care 5Y 4HR Exch EDU/RET 2150 48P POE+ Swch Service
H10QNE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 8P POE Swch Service
H10NCE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 8P Swch Service
H11CDE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 16P Swch Service
H11JBE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 24P POE Swch Service
H11FQE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 24P Swch Service
H11NYE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 48P POE Swch Service
H11RKE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 48P POE+ Swch Service
H11LME	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 48P Swch Service
H10QQE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 8P POE Swch Service
H10NDE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 8P Swch Service
H11CFE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 16P Swch Service
H11JCE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 24P POE Swch Service
H11FRE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 24P Swch Service
H11NZE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 48P POE Swch Service
H11RLE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 48P POE+ Swch Service
H11LNE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 48P Swch Service
H10PBE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite EDU/RET 2150 8P Swch Service
H11DCE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite EDU/RET 2150 16P Swch Service
H10QME	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 8P POE Swch Service
H10NBE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 8P Swch Service
H11CCE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 16P Swch Service
H11HZE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 24P POE Swch Service
H11FNE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 24P Swch Service
H11NXE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 48P POE Swch Service
H11RJE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 48P POE+ Swch Service
H11LLE	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 48P Swch Service

H10QRE	HPE Aruba Networking Foundational Care 5Y CTR 2150 8P POE Swch Service
H10NFE	HPE Aruba Networking Foundational Care 5Y CTR 2150 8P Swch Service
H11CGE	HPE Aruba Networking Foundational Care 5Y CTR 2150 16P Swch Service
H11JDE	HPE Aruba Networking Foundational Care 5Y CTR 2150 24P POE Swch Service
H11FSE	HPE Aruba Networking Foundational Care 5Y CTR 2150 24P Swch Service
H11PBE	HPE Aruba Networking Foundational Care 5Y CTR 2150 48P POE Swch Service
H11RME	HPE Aruba Networking Foundational Care 5Y CTR 2150 48P POE+ Swch Service
H11LQE	HPE Aruba Networking Foundational Care 5Y CTR 2150 48P Swch Service
H10QSE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 8P POE Swch Service
H10NGE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 8P Swch Service
H11CHE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 16P Swch Service
H11JFE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 24P POE Swch Service
H11FTE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 24P Swch Service
H11PCE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 48P POE Swch Service
H11RNE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 48P POE+ Swch Service
H11LRE	HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 48P Swch Service
H11DDE	HPE Aruba Networking Foundational Care 5Y CTR EDU/RET 2150 16P Swch Service
H11PYE	HPE Aruba Networking Foundational Care 5Y CTR EDU/RET 2150 48P POE Swch Service
H11SKE	HPE Aruba Networking Foundational Care 5Y CTR EDU/RET 2150 48P POE+ Swch Service
H10QGE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 8P POE Swch Service
H10MVE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 8P Swch Service
H11BWE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 16P Swch Service
H11HTE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 24P POE Swch Service
H11FHE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 24P Swch Service
H11NRE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 48P POE Swch Service
H11RCE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 48P POE+ Swch Service
H11LFE	HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 48P Swch Service
H10QFE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 8P POE Swch Service
H10MTE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 8P Swch Service
H11BVE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 16P Swch Service
H11HSE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 24P POE Swch Service
H11FGE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 24P Swch Service
H11NQE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 48P POE Swch Service
H11RBE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 48P POE+ Swch Service
H11LDE	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 48P Swch Service
H10QJE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 8P POE Swch Service

H10MXE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 8P Swch Service
H11BYE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 16P Swch Service
H11HWE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 24P POE Swch Service
H11FKE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 24P Swch Service
H11NTE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 48P POE Swch Service
H11RFE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 48P POE+ Swch Service
H11LHE	HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 48P Swch Service
H10QKE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 8P POE Swch Service
H10MYE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 8P Swch Service
H11BZE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 16P Swch Service
H11HXE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 24P POE Swch Service
H11FLE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 24P Swch Service
H11NVE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 48P POE Swch Service
H11RGE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 48P POE+ Swch Service
H11LJE	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 48P Swch Service
H11JXE	HPE Aruba Networking Foundational Care 5Y NBD Onsite EDU/RET 2150 24P POE Swch Service
H11PVE	HPE Aruba Networking Foundational Care 5Y NBD Onsite EDU/RET 2150 48P POE Swch Service

HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

Advisory & Professional services

Experts can help you map out your path to hybrid cloud and optimize your operations.

Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

Support services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

— **HPE Complete Care Service:** a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.

— **HPE Tech Care Service:** the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.

— **HPE Multivendor Services:** Single point of accountability for managing on-site hardware and software support for multivendor products. HPE experts help manage your IT across technologies and platforms for HPE and non-HPE technologies, acting as the single point of contact for your IT operational needs.

Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options

Defective Media Retention is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

GreenLake

GreenLake is the cloud to run and manage your entire hybrid landscape—private, public, and edge. It helps you to:

— Streamline IT Operations across compute, storage, and networking without the chaos

— Unify and secure data, as you move faster

— Accelerate AI, from pilot to production

The result: greater operational efficiency, lower TCO, and faster AI delivery—all from one unified, intelligent platform built for today's hybrid enterprise.

For additional technical information, available models and options, please reference the QuickSpecs

Visit HPE.com

Chat now

© Copyright 2026 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Arm is a registered trademark of Arm Limited.
All third-party marks are property of their respective owners.

Image may differ from the actual product.

PSN1014925906IEEN, August, 2026.

HEWLETT PACKARD ENTERPRISE

hpe.com