# HPE Networking CW 2150 Switch Series



### What's new

- Enterprise-class, fully managed, stackable Layer 3 switch series with 8, 16, 24, and 48port Class 4 PoE and nonPoE models, four 1G/10G SFP+ uplinks, and up to 770W of Class 4 PoE
- Up to 176 Gbps in nonblocking bandwidth, 130 Mpps in forwarding, and up to 9switch IRF stack
- Flexible connectivity options with four 1G/10G SFP+ uplinks in the 16, 24, and 48port models and two 1G SFP and two 1G/10G SFP+ uplinks in the 8port model
- Advanced Quality of Service (QoS), IPv6, and dynamic L3 protocols (RIP and OSPF) for reliable connectivity

## Overview

HPE Networking CW 2150 Switch Series empowers your business with reliable, high-performance networking tailored for small and medium-sized businesses and branch offices. These fully managed, stackable Layer 3 switches deliver enterprise-grade features without the complexity or high cost. With CW 2150 series, you get seamless management, robust security, and flexibility to scale as your needs grow. Designed for today's evolving networks, these switches provide affordable excellence—enabling you to connect and protect your business with confidence. Upgrade to the CW 2150 series and experience secure, simple, and powerful networking for your organization.

– Fanless design in the 8port and 24/48port nonPoE models. Supports IEEE 802.3az standard for Energy Efficient Ethernet (EEE)

– Managed by Web GUI, CLI, Smart Management Center (SmartMC) web dashboard, HPE Intelligent Management Center (IMC), SNMP, and REST APIs

# Features

### Enterprise-class secure and reliable connectivity

The HPE Networking CW 2150 Switch Series delivers up to 176Gbps of nonblocking bandwidth and up to 131Mpps forwarding, with nine unit IRF stacking for resilient availability and link redundancy.

The CW 2150 series offers flexible connectivity with four 1G/10G SFP+ uplinks on the 16, 24, and 48 port models, and two 1G SFP plus two 1G/10G SFP+ uplinks on the 8 port model. The 24 port model adds four SFP combo ports.

Advanced Quality of Service (QoS), Internet Protocol version 6 (IPv6) and dynamic L3 protocols (RIP and OSPF) for reliable connectivity

It supports IEEE802.3az Energy Efficient Ethernet and offers a fanless design on the 8, 24, and 48port nonPoE models.

Builtin 6kV serviceport surge protection helps reduce the risk of power strikes in demanding environments such as construction sites.

### Powerful PoE capabilities

The HPE Networking CW2150 Switch Series provides 125W, 248W, 405W, 390W, and 770W Class4 PoE across the 8, 16, 24, and 48port models.

It supports advanced PoE features, including fast PoE that delivers power within seconds of system startup.

Perpetual PoE supports enddevice state monitoring to help maintain power during a powersource reboot.

The PoE Watchdog function automatically removes power from a port when the connected device is no longer active.

### Comprehensive security control

The HPE Networking CW2150 Switch Series provides security features and network management for modern SMB environments. Secure boot verifies digital signatures to help prevent unauthorized or malicious software from loading at startup.

With HPE IMC, the CW2150 series supports EAD by integrating terminalsecurity policies, networkaccess control, and accessrights enforcement into a unified security framework.

It delivers multilayer access protection with granular ACLs (IPv4/IPv6, VLAN, portbased), identitydriven policies, and authentication options including 802.1X, MAC, Web, RADIUS, TACACS+, plus Guest VLAN detection and dualNIC detection with IMC.

The CW2150 series provides encrypted access using SSHv2, SSL, SNMPv3, and TLS, along with rolebased privileges and audit logging.

Threatprevention features include Control Plane Policing (DoS protection), ARP and DHCP protection, ICMP throttling, port security, and sourceport filtering.

### Simple and flexible management

The HPE Networking CW2150 Switch Series offers Web GUI, industrystandard CLI management and can be managed with other CW switches through a built-in dashboard for simplified deployment and centralized management.

Advanced management options include HPE Intelligent Management Center (IMC), HPE Networking Management Software (AirWave), SNMP managers, and REST APIs for integration with existing customer dashboards.

| Technical specifications | HPE Networking CW 2150 Switch Series |
|---|---|
| **Power consumption** | No load: 16–35W, single AC<br>Typical: 8–54W, single AC |
| **Heat dissipation** | 119–3306 BTU/hr depending on configuration |
| **Input voltage** | Rated voltage range: 100–240V AC at 50 Hz or 60 Hz<br>Maximum voltage range: 90–264V AC at 47 Hz to 63 Hz |
| **Ports** | 8-port model: 8x 10/100/1000BASE-T, 2x 1000BASE-X SFP ports and 2x 1/10GBASE-X SFP+ ports, or 8x 10/100/1000BASE-T PoE+, 2x 1000BASE-X SFP ports and 2x 1/10GBASE-X SFP+ ports<br><br>16-port model: 16x 10/100/1000BASE-T PoE+ (125W) ports and 4x 1/10GBASE-X SFP+ ports<br><br>24-port model: 24x 10/100/1000BASE-T ports, or 24x 10/100/1000BASE-T PoE+ and 4x 100/1000BASE-X SFP Combo ports, and 4x 1/10GBASE-X SFP+ ports<br><br>48-port model: 48x 10/100/1000BASE-T ports, or 48x 10/100/1000BASE-T PoE+ (390W) ports, or 48x 10/100/1000BASE-T PoE+ (770W) ports, and 4x 1/10GBASE-X SFP+ ports<br><br>Management ports: 1x RJ-45 console, 1x USB Type-C console, 1x USB and 1x OOBM management |
| **Latency** | 1 GE: < 5µs<br>10 GE: < 3µs (64-byte packets) |
| **Switching capacity** | 60–176 Gbps depending on model |
| **Stacking capabilities** | 9 member IRF stack |
| **Throughput** | 44–131 Mpps depending on model |
| **Memory and processor** | CPU: Dual-core Arm® at 1.2 GHz<br>Flash: 512 MB<br>SDRAM: 1 GB |
| **Power supply** | Fixed, 90–264V, single AC |
| **PoE capability** | 125–770W depending on model |
| **Management features** | Web GUI Command Line Interface (CLI)<br>Smart Management Center (SmartMC)<br>HPE Intelligence Management Center (IMC)<br>HPE Networking Management Software (AirWave)<br>REST API<br>SNMP |
| **Operating temperature** | -5°C–50°C (23°F–122°F) |
| **Warranty** | Limited lifetime hardware warranty. See the warranty duration. |

## SKU comparison

| | HPE Networking CW 2150 16p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 248W Switch (S6X55A) | HPE Networking CW 2150 24p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X50A) | HPE Networking CW 2150 24p 10M/100M/1G PoE+ 4p SFP 1G Combo 4p SFP+ 1G/10G 405W Switch (S6X51A) | HPE Networking CW 2150 48p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X52A) | HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 390W Switch (S6X53A) |
|---|---|---|---|---|---|
| **Differentiator** | 16p 10M/100M/1000M, 4p SFP+, 248W PoE+ | 24p 10M/100M/1000M, 4p SFP+ | 24p 10M/100M/1000M, 4p SFP 4p SFP+ Copper and Fiber Combo ports, 405W PoE+ | 8p 10M/100M/1000M, 4p SFP+ | 48p 10M/100M/1000M, 4p SFP+, 390W PoE+ |
| **Power consumption** | Idle: 25W<br>Typical: 38W<br>Full load: 317W (PoE 248W) | Idle: 6W<br>Typical: 16W<br>Full load: 21W | Idle: 23W<br>Typical: 35W<br>Full load: 465W (PoE 405W) | Idle: 13W<br>Typical: 31W<br>Full load: 42W | Idle: 29W<br>Typical: 54W<br>Full load: 512W (PoE 390W) |
| **Heat dissipation** | 85–1982 BTU/hr depending on configuration | 28–65 BTU/hr depending on configuration | 78–1587 BTU/hr depending on configuration | 44–143 BTU/hr depending on configuration | 99–1747 BTU/hr depending on configuration |
| **Input voltage** | Rated voltage range: 100–240V AC at 50 Hz or 60 Hz<br>Maximum voltage range: 90–264V AC at 47 Hz to 63 Hz | | | | |
| **Ports** | 16 x 10/100/1000BASE-T PoE+ ports<br>4 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management | 24 x 10/100/1000BASE-T ports<br>4 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management | 24 x 10/100/1000BASE-T PoE+ ports<br>4 x 100/1000BASE-X SFP Combo ports<br>4 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management | 48 x 10/100/1000BASE-T ports<br>4 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management | 48 x 10/100/1000BASE-T PoE+ ports<br>4 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management |
| **Latency** | 1 GE: < 5µs<br>10 GE: < 3µs (64-byte packets) | | | | |
| **Switching capacity** | 112 Gbps | 128 Gbps | 128 Gbps | 176 Gbps | 176 Gbps |
| **Stacking capabilities** | 9 member IRF stack | | | | |

| | HPE Networking CW 2150 16p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 248W Switch (S6X55A) | HPE Networking CW 2150 24p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X50A) | HPE Networking CW 2150 24p 10M/100M/1G PoE+ 4p SFP 1G Combo 4p SFP+ 1G/10G 405W Switch (S6X51A) | HPE Networking CW 2150 48p 10M/100M/1G 4p SFP+ 1G/10G Switch (S6X52A) | HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 390W Switch (S6X53A) |
|---|---|---|---|---|---|
| **Throughput** | 83 Mpps | 95 Mpps | 95 Mpps | 130 Mpps | 130 Mpps |
| **Memory and processor** | CPU: Dual-core Arm® at 1.2 GHz<br>Flash: 512 MB<br>SDRAM: 1 GB | | | | |
| **Power supply** | Fixed, 90–264V, single AC | | | | |
| **PoE capability** | 248W | non-PoE | 405W | non-PoE | non-PoE |
| **Management features** | Web GUI Command Line Interface (CLI)<br>Smart Management Center (SmartMC)<br>HPE Intelligence Management Center (IMC)<br>HPE Networking Management Software (AirWave)<br>REST API<br>SNMP | | | | |
| **Operating temperature** | -5°C–50°C (23°F–122°F) | | | | |
| **Warranty** | Limited lifetime hardware warranty. See the warranty duration. | | | | |

| | HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 770W Switch (S6X54A) | HPE Networking CW 2150 8p 10M/100M/1G 2p SFP 1G 2p SFP+ 1G/10G Switch (S6X56A) | HPE Networking CW 2150 8p 10M/100M/1G PoE+ 2p SFP 1G 2p SFP+ 1G/10G 125W Switch (S6X57A) |
|---|---|---|---|
| **Differentiator** | 48p 10M/100M/1000M, 4p SFP+, 770W PoE+ | 8p 10M/100M/1000M, 2p SFP, 2p SFP+ | 8p 10M/100M/1000M, 2p SFP, 2p SFP+ 125W PoE+ |
| **Power consumption** | Idle: 35W<br>Typical: 56W<br>Full load: 969W (PoE 770W) | Idle: 5W<br>Typical: 8W<br>Full load: 16W | Idle: 8W<br>Typical: 10W<br>Full load: 152W (PoE 125W) |
| **Heat dissipation** | 119–3306 BTU/hr depending on configuration | 17–55 BTU/hr depending on configuration | 27–519 BTU/hr depending on configuration |
| **Input voltage** | Rated voltage range: 100–240V AC at 50 Hz or 60 Hz<br>Maximum voltage range: 90–264V AC at 47 Hz to 63 Hz | | |
| **Ports** | 48 x 10/100/1000BASE-T PoE+ ports<br>4 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management | 8 x 10/100/1000BASE-T ports<br>2 x 1000BASE-X SFP ports<br>2 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management | 8 x 10/100/1000BASE-T PoE+ ports<br>2 x 1000BASE-X SFP ports<br>2 x 1/10GBASE-X SFP+ ports<br><br>1 x RJ-45 console, 1 x USB Type-C console, 1 x USB and 1 x OOBM management |
| **Latency** | 1 GE: < 5µs<br>10 GE: < 3µs (64-byte packets) | | |
| **Switching capacity** | 176 Gbps | 60 Gbps | 60 Gbps |
| **Stacking capabilities** | 9 member IRF stack | | |
| **Throughput** | 130 Mpps | 44 Mpps | 44 Mpps |
| **Memory and processor** | CPU: Dual-core Arm® at 1.2 GHz<br>Flash: 512 MB<br>SDRAM: 1 GB | | |
| **Power supply** | Fixed, 90–264V, single AC | | |
| **PoE capability** | 770W | non-PoE | 125W |

| | HPE Networking CW 2150 48p 10M/100M/1G PoE+ 4p SFP+ 1G/10G 770W Switch (S6X54A) | HPE Networking CW 2150 8p 10M/100M/1G 2p SFP 1G 2p SFP+ 1G/10G Switch (S6X56A) | HPE Networking CW 2150 8p 10M/100M/1G PoE+ 2p SFP 1G 2p SFP+ 1G/10G 125W Switch (S6X57A) |
|---|---|---|---|
| **Management features** | Web GUI Command Line Interface (CLI)<br>Smart Management Center (SmartMC)<br>HPE Intelligence Management Center (IMC)<br>HPE Networking Management Software (AirWave)<br>REST API<br>SNMP | | |
| **Operating temperature** | -5°C–50°C (23°F–122°F) | | |
| **Warranty** | Limited lifetime hardware warranty. See the warranty duration. | | |

# Related Options

The following options are available for these series:

| SKU | Description |
|---|---|
| **Kabel/Kabelkits** | |
| JD095C | HPE Networking X240 10G SFP+ SFP+ 0.65m DAC Cable |
| JD096C | HPE Networking X240 10G SFP+ SFP+ 1.2m DAC Cable |
| JD097C | HPE Networking X240 10G SFP+ SFP+ 3m DAC Cable |
| JG081C | HPE Networking X240 10G SFP+ SFP+ 5m DAC Cable |
| **Montagekits** | |
| R8M91A | HPE Networking Comware 5140 Rack Mount Kit |
| **Transceiver** | |
| JL290A | HPE Networking X2A0 10G SFP+ to SFP+ 7m Active Optical Cable |
| JL291A | HPE Networking X2A0 10G SFP+ to SFP+ 10m Active Optical Cable |
| JL292A | HPE Networking X2A0 10G SFP+ to SFP+ 20m Active Optical Cable |
| JD099B | HPE Networking X120 1G SFP LC BX 10-D Transceiver |
| JD098B | HPE Networking X120 1G SFP LC BX 10-U Transceiver |
| JD103A | HPE Networking X120 1G SFP LC LH100 Transceiver |
| JD119B | HPE Networking X120 1G SFP LC LX Transceiver |
| JD118B | HPE Networking X120 1G SFP LC SX Transceiver |
| JD089B | HPE Networking X120 1G SFP RJ45 T Transceiver |
| JL738A | HPE Networking X130 10G SFP+ LC BiDi 10km-Downlink Transceiver |
| JL737A | HPE Networking X130 10G SFP+ LC BiDi 10km-Uplink Transceiver |
| JL740A | HPE Networking X130 10G SFP+ LC BiDi 40km-Downlink Transceiver |
| JL739A | HPE Networking X130 10G SFP+ LC BiDi 40km-Uplink Transceiver |
| JG234A | HPE Networking X130 10G SFP+ LC ER 40km Transceiver |
| JG915A | HPE Networking X130 10G SFP+ LC LH 80km Transceiver |
| JD094B | HPE Networking X130 10G SFP+ LC LR Transceiver |
| JD092B | HPE Networking X130 10G SFP+ LC SR Transceiver |

# Related Services

The following services are available for these series:

| SKU | Description |
|---|---|
| **Technology Services** | |
| H10PGE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 8P POE Swch Service |
| H10LVE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 8P Swch Service |
| H10ZWE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 16P Swch Service |
| H11GTE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 24P POE Swch Service |
| H11DHE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 24P Swch Service |
| H11MRE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 48P POE Swch Service |
| H11QCE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 48P POE+ Swch Service |
| H11KFE | HPE Aruba Networking Foundational Care 1Y 4HR Exch 2150 48P Swch Service |
| H11RRE | HPE Aruba Networking Foundational Care 1Y 4HR Exch EDU/RET 2150 48P POE+ Swch Service |
| H10PLE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 8P POE Swch Service |
| H10LZE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 8P Swch Service |
| H11BBE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 16P Swch Service |
| H11GYE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 24P POE Swch Service |
| H11DME | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 24P Swch Service |
| H11MWE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 48P POE Swch Service |
| H11QHE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 48P POE+ Swch Service |
| H11KKE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite 2150 48P Swch Service |
| H10PME | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 8P POE Swch Service |
| H10MBE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 8P Swch Service |
| H11BCE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 16P Swch Service |
| H11GZE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 24P POE Swch Service |
| H11DNE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 24P Swch Service |
| H11MXE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 48P POE Swch Service |
| H11QJE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 48P POE+ Swch Service |
| H11KLE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 2150 48P Swch Service |
| H10NLE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite EDU/RET 2150 8P Swch Service |
| H11CME | HPE Aruba Networking Foundational Care 1Y 4HR Onsite EDU/RET 2150 16P Swch Service |
| H11RTE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite EDU/RET 2150 48P POE+ Swch Service |
| H10PKE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 8P POE Swch Service |
| H10LYE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 8P Swch Service |
| H10ZZE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 16P Swch Service |
| H11GXE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 24P POE Swch Service |
| H11DLE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 24P Swch Service |

| | |
|---|---|
| H11MVE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 48P POE Swch Service |
| H11QGE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 48P POE+ Swch Service |
| H11KJE | HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 2150 48P Swch Service |
| H10PNE | HPE Aruba Networking Foundational Care 1Y CTR 2150 8P POE Swch Service |
| H10MCE | HPE Aruba Networking Foundational Care 1Y CTR 2150 8P Swch Service |
| H11BDE | HPE Aruba Networking Foundational Care 1Y CTR 2150 16P Swch Service |
| H11HBE | HPE Aruba Networking Foundational Care 1Y CTR 2150 24P POE Swch Service |
| H11DQE | HPE Aruba Networking Foundational Care 1Y CTR 2150 24P Swch Service |
| H11MYE | HPE Aruba Networking Foundational Care 1Y CTR 2150 48P POE Swch Service |
| H11QKE | HPE Aruba Networking Foundational Care 1Y CTR 2150 48P POE+ Swch Service |
| H11KME | HPE Aruba Networking Foundational Care 1Y CTR 2150 48P Swch Service |
| H10PQE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 8P POE Swch Service |
| H10MDE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 8P Swch Service |
| H11BFE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 16P Swch Service |
| H11HCE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 24P POE Swch Service |
| H11DRE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 24P Swch Service |
| H11MZE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 48P POE Swch Service |
| H11QLE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 48P POE+ Swch Service |
| H11KNE | HPE Aruba Networking Foundational Care 1Y CTR CDMR 2150 48P Swch Service |
| H10QYE | HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 8P POE Swch Service |
| H11CNE | HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 16P Swch Service |
| H11PJE | HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 48P POE Swch Service |
| H11RVE | HPE Aruba Networking Foundational Care 1Y CTR EDU/RET 2150 48P POE+ Swch Service |
| H10PDE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 8P POE Swch Service |
| H10LSE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 8P Swch Service |
| H10ZTE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 16P Swch Service |
| H11GRE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 24P POE Swch Service |
| H11DFE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 24P Swch Service |
| H11MNE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 48P POE Swch Service |
| H11PZE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 48P POE+ Swch Service |
| H11KCE | HPE Aruba Networking Foundational Care 1Y NBD Exch 2150 48P Swch Service |
| H11RQE | HPE Aruba Networking Foundational Care 1Y NBD Exch EDU/RET 2150 48P POE+ Swch Service |
| H10PFE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 8P POE Swch Service |
| H10LTE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 8P Swch Service |
| H10ZVE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 16P Swch Service |
| H11GSE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 24P POE Swch Service |

| | |
|---|---|
| H11DGE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 24P Swch Service |
| H11MQE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 48P POE Swch Service |
| H11QBE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 48P POE+ Swch Service |
| H11KDE | HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 2150 48P Swch Service |
| H10PHE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 8P POE Swch Service |
| H10LWE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 8P Swch Service |
| H10ZXE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 16P Swch Service |
| H11GVE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 24P POE Swch Service |
| H11DJE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 24P Swch Service |
| H11MSE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 48P POE Swch Service |
| H11QDE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 48P POE+ Swch Service |
| H11KGE | HPE Aruba Networking Foundational Care 1Y NBD Onsite 2150 48P Swch Service |
| H10PJE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 8P POE Swch Service |
| H10LXE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 8P Swch Service |
| H10ZYE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 16P Swch Service |
| H11GWE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 24P POE Swch Service |
| H11DKE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 24P Swch Service |
| H11MTE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 48P POE Swch Service |
| H11QFE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 48P POE+ Swch Service |
| H11KHE | HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 2150 48P Swch Service |
| H11JJE | HPE Aruba Networking Foundational Care 1Y NBD Onsite EDU/RET 2150 24P POE Swch Service |
| H11PGE | HPE Aruba Networking Foundational Care 1Y NBD Onsite EDU/RET 2150 48P POE Swch Service |
| H10PTE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 8P POE Swch Service |
| H10MHE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 8P Swch Service |
| H11BJE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 16P Swch Service |
| H11HGE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 24P POE Swch Service |
| H11DVE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 24P Swch Service |
| H11NDE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 48P POE Swch Service |
| H11QQE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 48P POE+ Swch Service |
| H11KSE | HPE Aruba Networking Foundational Care 3Y 4HR Exch 2150 48P Swch Service |
| H11LZE | HPE Aruba Networking Foundational Care 3Y 4HR Exch EDU/RET 2150 48P Swch Service |
| H10PZE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 8P POE Swch Service |
| H10MNE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 8P Swch Service |
| H11BQE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 16P Swch Service |
| H11HME | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 24P POE Swch Service |
| H11FBE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 24P Swch Service |

| | |
|---|---|
| H11NKE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 48P POE Swch Service |
| H11QWE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 48P POE+ Swch Service |
| H11KYE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite 2150 48P Swch Service |
| H10QBE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 8P POE Swch Service |
| H10MQE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 8P Swch Service |
| H11BRE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 16P Swch Service |
| H11HNE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 24P POE Swch Service |
| H11FCE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 24P Swch Service |
| H11NLE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 48P POE Swch Service |
| H11QXE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 48P POE+ Swch Service |
| H11KZE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 2150 48P Swch Service |
| H10NTE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite EDU/RET 2150 8P Swch Service |
| H10PYE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 8P POE Swch Service |
| H10MME | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 8P Swch Service |
| H11BNE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 16P Swch Service |
| H11HLE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 24P POE Swch Service |
| H11DZE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 24P Swch Service |
| H11NJE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 48P POE Swch Service |
| H11QVE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 48P POE+ Swch Service |
| H11KXE | HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 2150 48P Swch Service |
| H10QCE | HPE Aruba Networking Foundational Care 3Y CTR 2150 8P POE Swch Service |
| H10MRE | HPE Aruba Networking Foundational Care 3Y CTR 2150 8P Swch Service |
| H11BSE | HPE Aruba Networking Foundational Care 3Y CTR 2150 16P Swch Service |
| H11HQE | HPE Aruba Networking Foundational Care 3Y CTR 2150 24P POE Swch Service |
| H11FDE | HPE Aruba Networking Foundational Care 3Y CTR 2150 24P Swch Service |
| H11NME | HPE Aruba Networking Foundational Care 3Y CTR 2150 48P POE Swch Service |
| H11QYE | HPE Aruba Networking Foundational Care 3Y CTR 2150 48P POE+ Swch Service |
| H11LBE | HPE Aruba Networking Foundational Care 3Y CTR 2150 48P Swch Service |
| H10QDE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 8P POE Swch Service |
| H10MSE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 8P Swch Service |
| H11BTE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 16P Swch Service |
| H11HRE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 24P POE Swch Service |
| H11FFE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 24P Swch Service |
| H11NNE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 48P POE Swch Service |
| H11QZE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 48P POE+ Swch Service |
| H11LCE | HPE Aruba Networking Foundational Care 3Y CTR CDMR 2150 48P Swch Service |

| | |
|---|---|
| H11CWE | HPE Aruba Networking Foundational Care 3Y CTR EDU/RET 2150 16P Swch Service |
| H10PSE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 8P POE Swch Service |
| H10MGE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 8P Swch Service |
| H11BHE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 16P Swch Service |
| H11HFE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 24P POE Swch Service |
| H11DTE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 24P Swch Service |
| H11NCE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 48P POE Swch Service |
| H11QNE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 48P POE+ Swch Service |
| H11KRE | HPE Aruba Networking Foundational Care 3Y NBD Exch 2150 48P Swch Service |
| H11PKE | HPE Aruba Networking Foundational Care 3Y NBD Exch EDU/RET 2150 48P POE Swch Service |
| H10PRE | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 8P POE Swch Service |
| H10MFE | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 8P Swch Service |
| H11BGE | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 16P Swch Service |
| H11HDE | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 24P POE Swch Service |
| H11DSE | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 24P Swch Service |
| H11NBE | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 48P POE Swch Service |
| H11QME | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 48P POE+ Swch Service |
| H11KQE | HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 2150 48P Swch Service |
| H10PVE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 8P POE Swch Service |
| H10MJE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 8P Swch Service |
| H11BKE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 16P Swch Service |
| H11HHE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 24P POE Swch Service |
| H11DWE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 24P Swch Service |
| H11NFE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 48P POE Swch Service |
| H11QRE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 48P POE+ Swch Service |
| H11KTE | HPE Aruba Networking Foundational Care 3Y NBD Onsite 2150 48P Swch Service |
| H10PWE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 8P POE Swch Service |
| H10MKE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 8P Swch Service |
| H11BLE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 16P Swch Service |
| H11HJE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 24P POE Swch Service |
| H11DXE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 24P Swch Service |
| H11NGE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 48P POE Swch Service |
| H11QSE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 48P POE+ Swch Service |
| H11KVE | HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 2150 48P Swch Service |
| H10NRE | HPE Aruba Networking Foundational Care 3Y NBD Onsite EDU/RET 2150 8P Swch Service |
| H11CSE | HPE Aruba Networking Foundational Care 3Y NBD Onsite EDU/RET 2150 16P Swch Service |

| | |
|---|---|
| H10QHE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 8P POE Swch Service |
| H10MWE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 8P Swch Service |
| H11BXE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 16P Swch Service |
| H11HVE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 24P POE Swch Service |
| H11FJE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 24P Swch Service |
| H11NSE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 48P POE Swch Service |
| H11RDE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 48P POE+ Swch Service |
| H11LGE | HPE Aruba Networking Foundational Care 5Y 4HR Exch 2150 48P Swch Service |
| H11PTE | HPE Aruba Networking Foundational Care 5Y 4HR Exch EDU/RET 2150 48P POE Swch Service |
| H11SFE | HPE Aruba Networking Foundational Care 5Y 4HR Exch EDU/RET 2150 48P POE+ Swch Service |
| H10QNE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 8P POE Swch Service |
| H10NCE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 8P Swch Service |
| H11CDE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 16P Swch Service |
| H11JBE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 24P POE Swch Service |
| H11FQE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 24P Swch Service |
| H11NYE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 48P POE Swch Service |
| H11RKE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 48P POE+ Swch Service |
| H11LME | HPE Aruba Networking Foundational Care 5Y 4HR Onsite 2150 48P Swch Service |
| H10QQE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 8P POE Swch Service |
| H10NDE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 8P Swch Service |
| H11CFE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 16P Swch Service |
| H11JCE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 24P POE Swch Service |
| H11FRE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 24P Swch Service |
| H11NZE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 48P POE Swch Service |
| H11RLE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 48P POE+ Swch Service |
| H11LNE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 2150 48P Swch Service |
| H10PBE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite EDU/RET 2150 8P Swch Service |
| H11DCE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite EDU/RET 2150 16P Swch Service |
| H10QME | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 8P POE Swch Service |
| H10NBE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 8P Swch Service |
| H11CCE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 16P Swch Service |
| H11HZE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 24P POE Swch Service |
| H11FNE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 24P Swch Service |
| H11NXE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 48P POE Swch Service |
| H11RJE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 48P POE+ Swch Service |
| H11LLE | HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 2150 48P Swch Service |

| | |
|---|---|
| H10QRE | HPE Aruba Networking Foundational Care 5Y CTR 2150 8P POE Swch Service |
| H10NFE | HPE Aruba Networking Foundational Care 5Y CTR 2150 8P Swch Service |
| H11CGE | HPE Aruba Networking Foundational Care 5Y CTR 2150 16P Swch Service |
| H11JDE | HPE Aruba Networking Foundational Care 5Y CTR 2150 24P POE Swch Service |
| H11FSE | HPE Aruba Networking Foundational Care 5Y CTR 2150 24P Swch Service |
| H11PBE | HPE Aruba Networking Foundational Care 5Y CTR 2150 48P POE Swch Service |
| H11RME | HPE Aruba Networking Foundational Care 5Y CTR 2150 48P POE+ Swch Service |
| H11LQE | HPE Aruba Networking Foundational Care 5Y CTR 2150 48P Swch Service |
| H10QSE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 8P POE Swch Service |
| H10NGE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 8P Swch Service |
| H11CHE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 16P Swch Service |
| H11JFE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 24P POE Swch Service |
| H11FTE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 24P Swch Service |
| H11PCE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 48P POE Swch Service |
| H11RNE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 48P POE+ Swch Service |
| H11LRE | HPE Aruba Networking Foundational Care 5Y CTR CDMR 2150 48P Swch Service |
| H11DDE | HPE Aruba Networking Foundational Care 5Y CTR EDU/RET 2150 16P Swch Service |
| H11PYE | HPE Aruba Networking Foundational Care 5Y CTR EDU/RET 2150 48P POE Swch Service |
| H11SKE | HPE Aruba Networking Foundational Care 5Y CTR EDU/RET 2150 48P POE+ Swch Service |
| H10QGE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 8P POE Swch Service |
| H10MVE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 8P Swch Service |
| H11BWE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 16P Swch Service |
| H11HTE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 24P POE Swch Service |
| H11FHE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 24P Swch Service |
| H11NRE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 48P POE Swch Service |
| H11RCE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 48P POE+ Swch Service |
| H11LFE | HPE Aruba Networking Foundational Care 5Y NBD Exch 2150 48P Swch Service |
| H10QFE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 8P POE Swch Service |
| H10MTE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 8P Swch Service |
| H11BVE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 16P Swch Service |
| H11HSE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 24P POE Swch Service |
| H11FGE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 24P Swch Service |
| H11NQE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 48P POE Swch Service |
| H11RBE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 48P POE+ Swch Service |
| H11LDE | HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 2150 48P Swch Service |
| H10QJE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 8P POE Swch Service |

| | |
|---|---|
| H10MXE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 8P Swch Service |
| H11BYE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 16P Swch Service |
| H11HWE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 24P POE Swch Service |
| H11FKE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 24P Swch Service |
| H11NTE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 48P POE Swch Service |
| H11RFE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 48P POE+ Swch Service |
| H11LHE | HPE Aruba Networking Foundational Care 5Y NBD Onsite 2150 48P Swch Service |
| H10QKE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 8P POE Swch Service |
| H10MYE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 8P Swch Service |
| H11BZE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 16P Swch Service |
| H11HXE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 24P POE Swch Service |
| H11FLE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 24P Swch Service |
| H11NVE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 48P POE Swch Service |
| H11RGE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 48P POE+ Swch Service |
| H11LJE | HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 2150 48P Swch Service |
| H11JXE | HPE Aruba Networking Foundational Care 5Y NBD Onsite EDU/RET 2150 24P POE Swch Service |
| H11PVE | HPE Aruba Networking Foundational Care 5Y NBD Onsite EDU/RET 2150 48P POE Swch Service |

# HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

### Advisory & Professional services

Experts can help you map out your path to hybrid cloud and optimize your operations.

### Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

### Support services

Optimize your entire IT environment and drive innovation.  Manage day-to-day IT operational tasks while freeing up valuable time and resources.

— **HPE Complete Care Service:** a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.

— **HPE Tech Care Service:** the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.

— **HPE Multivendor Services:** Single point of accountability for managing on-site hardware and software support for multivendor products. HPE experts help manage your IT across technologies and platforms for HPE and non-HPE technologies, acting as the single point of contact for your IT operational needs.

### Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

### HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject.  Schedule training in a way that works best for your business with flexible continuous learning options

**Defective Media Retention** is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

### GreenLake

GreenLake is the cloud to run and manage your entire hybrid landscape—private, public, and edge. It helps you to:

— Streamline IT Operations across compute, storage, and networking without the chaos

— Unify and secure data, as you move faster

— Accelerate AI, from pilot to production

The result: greater operational efficiency, lower TCO, and faster AI delivery—all from one unified, intelligent platform built for today's hybrid enterprise.

For additional technical information, available models and options, please reference the QuickSpecs

Visit HPE.com

Chat now

© Copyright 2026 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Arm is a registered trademark of Arm Limited.
All third-party marks are property of their respective owners.

Image may differ from the actual product.

PSN1014925906AEEN, August, 2026.

HEWLETT PACKARD ENTERPRISE

hpe.com