
Accessories Guide

TC501

Rugged mobile computing reimagined for the AI-powered frontline







Revised January 2026

Table of Contents

Accessories that POWER devices

Cradles

Single-slot ShareCradles 4
Multi-slot ShareCradles Kits 6
Multi-slot ShareCradles 8
Legacy ShareCradle Cups 10
ShareCradle Components 12
Mounting Options for Chargers 13

Batteries

Spare Li-ion Batteries 15
Spare Battery Chargers 16

Power Supplies, Cables, and Adaptors

Power Supply and Cable Matrix 18
Country-Specific AC Line Cords 19

Accessories that PROTECT devices

Soft Goods

Rugged Boot, Hand Strap, and Screen Protector 21
Soft Holster, Stylus, and Tether 22

Accessories that ENABLE devices

Trigger Handles

Electronic Trigger Handle and Wrist Strap 24

Wearable Mounts

Wrist Mounts, Comfort Pad, and Arm Sleeve 26
Replacement Double BOA Wrist Strap 27
Replacement Single BOA Wrist Strap 28

Headsets

Wired Headsets and Accessories for Workforce Connect 30
Wireless Headsets and Accessories for Voice-Directed Picking 31

Third Party Accessories

RAM Vehicle Docks 33

Cradles

Single-slot ShareCradles

Multi-slot ShareCradles Kits

Multi-slot ShareCradles

Legacy ShareCradle Cups

ShareCradle Components

Mounting Options for Chargers

Cradles

Single-slot ShareCradles

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
One-Device ShareCradle Devices WITH a rugged boot: SKU# **CRDCUP-TC5A-1DF-B** Devices WITHOUT a rugged boot: SKU# **CRDCUP-TC5A-1DF** 	**TC501 Fast-Charging ShareCradle for a Single Device.** ▪ Device with standard battery charges from 0–70% in about 45 minutes. ▪ Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
One-Device Ethernet ShareCradle Devices WITH a rugged boot: SKU# **CRD-TC5A-1SE-B** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-1SE** 	**TC501 Ethernet ShareCradle for a Single Device.** ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ There is an Ethernet Port, and spare USB-C port. ▪ Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
Two-Device ShareCradle Devices WITH a rugged boot: SKU# **CRDCUP-TC5A-2D-B** Devices WITHOUT a rugged boot: SKU# **CRDCUP-TC5A-2D** 	**TC501 Charge-Only ShareCradle for Two Devices.** ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)

Cradles

Single-slot ShareCradles

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
One-Device & One-Battery ShareCradle Devices WITH a rugged boot: SKU# **CRD-TC5A-2SC1B-B** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-2SC1B** 	**TC501 Charge-Only ShareCradle for a Single Device and its Spare Battery.** ▪ Device with standard battery charges from 0–70% in about 45 minutes. ▪ Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
One-Device & One Battery Ethernet ShareCradle Devices WITH a rugged boot: SKU# **CRD-TC5A-2SE1B-B** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-2SE1B** 	**TC501 Ethernet ShareCradle for a Single Device and its Spare Battery.** ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ There is an Ethernet Port, and spare USB-C port. ▪ Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX ('XX' in SKU to get the right plug style based on region)

Cradles

Multi-Slot ShareCradles Kits

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Five-Device ShareCradle Kit Devices WITH a rugged boot: SKU# **CRD-TC5AB-5SC5DF-1** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SC5DF-1** 	**TC501 Fast-Charging ShareCradle for Five Devices.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–70% in about 45 minutes. ▪ Includes: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW ▪ Sold Separately: Country-Specific AC Line Cord (listed later in this document).
Five-Device Ethernet ShareCradle Kit Devices WITH a rugged boot: SKU# **CRD-TC5AB-5SE5D-1** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SE5D-1** 	**TC501 Ethernet ShareCradle for Five Devices.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ There is an Ethernet Port, and spare USB-C port. ▪ Includes: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW ▪ Sold Separately: Country-Specific AC Line Cord (listed later in this document).

Cradles

Multi-Slot ShareCradles Kits

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Five-Device & Five-Battery ShareCradle Kit Devices WITH a rugged boot: SKU# **CRD-TC5AB-5SC5D5B-1** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SC5D5B-1** 	**TC501 Charge-Only ShareCradle for Five Devices and Five Spare Batteries.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ Includes: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW. ▪ Sold Separately: Country-Specific AC Line Cord (listed later in this document).
1 0-Device ShareCradle Kit Devices WITH a rugged boot: SKU# **CRD-TC5AB-5SC10D-1** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SC10D-1** 	**TC501 Charge-Only ShareCradle for 10 Devices.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ Includes: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW. ▪ Sold Separately: Country-Specific AC Line Cord (listed later in this document).

Cradles

Multi-Slot ShareCradles

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Five-Device ShareCradle Devices WITH a rugged boot: SKU# **CRD-TC5A-5SC5DF-B** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SC5DF** 	**TC501 Fast-Charging ShareCradle for Five Devices.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–70% in about 45 minutes. ▪ Sold Separately: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW, and Country-Specific AC Line Cord (listed later in this document).
Five-Device Ethernet ShareCradle Devices WITH a rugged boot: SKU# **CRD-TC5A-5SE5D-B** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SE5D** 	**TC501 Ethernet ShareCradle for Five Devices.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ There is an Ethernet Port, and spare USB-C port. ▪ Sold Separately: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW, and Country-Specific AC Line Cord (listed later in this document).

Cradles

Multi-Slot ShareCradles

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Five-Device & Five-Battery ShareCradle Devices WITH a rugged boot: SKU# **CRD-TC5A-5SC5D5B-B** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SC5D5B** 	**TC501 Charge-Only ShareCradle for Five Devices and Five Spare Batteries.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ Sold Separately: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW, and Country-Specific AC Line Cord (listed later in this document).
1 0-Device ShareCradle Devices WITH a rugged boot: SKU# **CRD-TC5A-5SC10D-B** Devices WITHOUT a rugged boot: SKU# **CRD-TC5A-5SC10D** 	**TC501 Charge-Only ShareCradle for 10 Devices.** ▪ Can be mounted on a standard 19-inch rack system using mounting bracket SKU# BRKT-SCRD-SMRK-01. ▪ Device with standard battery charges from 0–90% in about 1½ hours. ▪ Sold Separately: Power Supply with Attached DC Cable SKU# PWR-BGA12V150W1WW, and Country-Specific AC Line Cord (listed later in this document).

Cradles

Legacy ShareCradle Cups

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
One-Device Replacement ShareCradle Cup Devices WITH a rugged boot: SKU# **CRDCUP-NGTC5AB-01** Devices WITHOUT a rugged boot: SKU# **CRDCUP-NGTC5ANB-01** 	**TC501 Replacement Charge-Only Device Cup for One Device** ▪ Enables the use of TC501 devices with Legacy ShareCradles by replacing the existing TC51x/TC56x or TC52x/TC57x series device cup. ▪ Includes a pre-installed TC501 shim.
Five-Device Replacement ShareCradle Cup Devices WITH a rugged boot: SKU# **CRDCUP-NGTC5AB-05** Devices WITHOUT a rugged boot: SKU# **CRDCUP-NGTC5ANB-05** 	**TC501 Replacement Charge-Only Device Cup for Five Devices** ▪ A set of five Charge-Only ShareCradle Cups. ▪ Enables the use of TC501 devices with Legacy ShareCradles by replacing the existing TC51x/TC56x or TC52x/TC57x series device cup. ▪ Includes pre-installed TC501 shims.
One-Device Replacement Ethernet ShareCradle Cup Devices WITH a rugged boot: SKU# **CRDCUP-NGTC5AEB-01** Devices WITHOUT a rugged boot: SKU# **CRDCUP-NGTC5AEN-01** 	**TC501 Replacement Ethernet Device Cup for One Device** ▪ Enables the use of TC501 devices with Legacy ShareCradles by replacing the existing TC51x/TC56x or TC52x/TC57x series device cup. ▪ Includes a pre-installed TC501 shim.
Five-Device Replacement Ethernet ShareCradle Cup Devices WITH a rugged boot: SKU# **CRDCUP-NGTC5AEB-05** Devices WITHOUT a rugged boot: SKU# **CRDCUP-NGTC5AEN-05** 	**TC501 Replacement Ethernet Device Cup for Five Devices** ▪ A set of five Ethernet ShareCradle Cups. ▪ Enables the use of TC501 devices with Legacy ShareCradles by replacing the existing TC51x/TC56x or TC52x/TC57x series device cup. ▪ Includes pre-installed TC501 shims.

Cradles

Legacy ShareCradle Cups

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party

Item/SKU#	Description
TC501 Shim Devices WITH a rugged boot: SKU# **SHIM-CRD-TC5AB** Devices WITHOUT a rugged boot: SKU# **SHIM-CRD-TC5A** 	**TC501 Replacement Shim** • Replaces the TC53x / TC58x shim to make Legacy ShareCradles compatible with TC501 devices.

Cradles

ShareCradle Components

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
TC501 Holder SKU# **HLD-TC5AB-01** 	**TC501 Holder for Devices *WITH* a rugged boot,** ▪ Included in all ShareCradles designed for devices with a rugged boot.
TC501 Holder SKU# **HLD-TC5A-01** 	**TC501 Holder for Devices *WITHOUT* a rugged boot,** ▪ Included in all ShareCradles designed for devices without a rugged boot.
Ethernet Single-Slot ShareCradle Base SKU# **CRD-ETHSNGLEBASE-01** 	**Ethernet Single-Slot ShareCradle Base** ▪ Included in all single-slot Ethernet ShareCradle Configurations.
Fast-Charging ShareCradle Base SKU# **CRD-FCBASE-01** 	**Fast-Charging ShareCradle Base** ▪ Included in all multi-slot ShareCradles except for the Ethernet model.
Ethernet ShareCradle Base SKU# **CRD-ETHBASE-01** 	**Ethernet ShareCradle Base** ▪ Included in the multi-slot Ethernet ShareCradle configuration.

Cradles

Mounting Options for Chargers

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Mounting Bracket SKU# **BRKT-SCRD-SMRK-01** 	**Use five-slot ShareCradle mounting bracket to attach five- slot TC501 cradles to the wall or mount on a 19-inch server rack.** ▪ Offers cable routing slots and removable tray that stores / conceals power supply. ▪ Adjustable orientations: 25º angle for high-density (multi-slot chargers). Horizontal (single-slot or four-slot spare Li-ion charger). ▪ Four 4-slot spare battery chargers can be mounted as shown with mounting bracket. ▪ Compatible with all multi-slot ShareCradles for TC501. ▪ Use to mount to wall or with standard 19-inch server rack for more density and save space.

Batteries

Spare Li-ion Batteries

Spare Battery Chargers

Batteries

Spare Li-ion Batteries

[Cradles](#)

[Batteries](#)

[Power Supplies, Cables and Adaptors](#)


[Soft Goods](#)

[Trigger handles](#)

[Wearable Mounts](#)

[Headsets](#)

[Third Party Accessories](#)

Item/SKU#	Description
Standard Capacity Battery SKU# **BTRY-TC5A7A-SC-01** 	**TC501 Standard Capacity Battery with PowerPrecision Plus.** ▪ Premium-grade battery cells with longer lifecycle and tested to meet rigorous controls and standards. ▪ Obtain advanced battery state of health information including charge level and battery age based on usage patterns.
Extended Capacity Battery SKU# **BTRY-TC5A7A-EC-01** 	**TC501 Extended Capacity Battery with PowerPrecision Plus.** ▪ Premium-grade battery cells with longer lifecycle and tested to meet rigorous controls and standards. ▪ Obtain advanced battery state of health information including charge level and battery age based on usage patterns.
Wireless Charging Battery SKU# **BTRY-TC5A7A-WC-01** 	**TC501 Standard Capacity Battery with Wireless Charging and PowerPrecision Plus.** ▪ Premium-grade battery cells with longer lifecycle and tested to meet rigorous controls and standards. ▪ Obtain advanced battery state of health information including charge level and battery age based on usage patterns.

Batteries

Spare Battery Charger

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Spare Battery Charger SKU# **CRDCUP-TC5A7A-4B** 	**Spare Battery Charger to Charge any Four TC501 Li-ion batteries.** ▪ Can be used standalone or up to 4 chargers can be mounted on Mounting Bracket SKU# BRKT-SCRD-SMRK-01. ▪ Sold separately: USB-C Cable SKU# CBL-EC5X-USBC3A-01, and Country-Specific Power Adaptor SKU# PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)

Power Supply, Cables, and Adaptors

Power Supply and Cable Matrix

Country-Specific AC Line Cords

Power Supply, Cables and Adapters

Power Supply and Cable Matrix

[Cradles](#)

[Batteries](#)

[Power Supplies, Cables and Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Wearable Mounts](#)

[Headsets](#)

[Third Party Accessories](#)

SKU#	Description	Notes
PWR-BGA12V150W1WW 	Level VI AC/DC power supply brick. AC Input: 100–240V, 2.5A. DC Output: 12V, 12.5A, 150W.	Sold Separately. To be used with Country-Specific AC Line Cords.
CBL-EC5X-USBC3A-01 	USB-C to USB-C Communications and Charging Cable, 1M Long, Support 3.0 support speed and fast charge.	Sold separately. Used with PWR-WUA5V45W1XX (Replace 'XX' in SKU to get the right plug style based on region)
PWR-WUA5V45W1US 	USB type C power supply adaptor with United States plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1EU 	USB type C power supply adaptor with European Union plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1GB 	USB type C power supply adaptor with United Kingdom plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1AU 	USB type C power supply adaptor with Australia plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1CN 	USB type C power supply adaptor with China plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1KR 	USB type C power supply adaptor with Korea plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1IN	USB type C power supply adaptor with India plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1AR 	USB type C power supply adaptor with Argentina plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.
PWR-WUA5V45W1BR	USB type C power supply adaptor with Brazil plug. USB PD 3.1 power supply with an input of 100-240VAC and a self-adjusting output ranging from 5V/3A to 20V/2.25A.	Sold separately. Used with USB-C Cable (CBL-EC5X-USBC3A-01) to charge device.

Power supply, cables and adapters

Country-specific AC line cords, Grounded 3-Prong

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

SKU#	Description	
23844-00-00R		**North America (United States, Canada, Mexico)** Commonly used with chargers mounted in server racks; 7.5 feet long
50-16000-678R		**North America (United States, Canada, Mexico)** 0.9 meters (3 feet long)
50-16000-221R		**North America (United States, Canada, Mexico)** 1.8 meters (6 feet long)
50-16000-727R		**Brazil** 1.8 meters (6 feet) long
50-16000-680R		**Argentina** 1.8 meters (6 feet) long
50-16000-217R		**American Samoa, Australia, New Guinea** 1.8 meters (6 feet) long
50-16000-218R		**Japan** 1.8 meters (6 feet) long
50-16000-219R		**Antigua, Bermuda, Burma, Channel Islands, Hong Kong, Iraq, Ireland, Malaysia, North Ireland, Scotland, Singapore, United Kingdom, Wales** 1.8 meters (6 feet) long
50-16000-257R		**China** 1.8 meters (6 feet) long
50-16000-220R		**Europe, Abu Dhabi, Bolivia, Dubai, Egypt, Iran, Korea, Russia, Vietnam** 1.8 meters (6 feet) long
50-16000-671R		**Italy** 1.8 meters (6 feet) long
50-16000-669R		India, South Africa, Africa 1.8 meters (6 feet) long

Soft Goods

Rugged Boot, Hand Strap, and Screen Protector

Soft Holster, Stylus, and Tether

Soft Goods

Rugged Boot, Hand Strap, and Screen Protector

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Rugged Boot SKU# **SG-TC5AEXO-01** 	**TC501 Rugged Boot** ▪ Boot increases drop specification of device to 9 feet to concrete. ▪ Two-piece design provides for an easier installation and snaps together. * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Hand Strap SKU# **SG-TC5A7A-HDSTP-01** 	**TC501 Hand Strap** ▪ Allows device to be easily held in palm of hand. ▪ Attaches directly to device, even with rugged boot installed. ▪ Includes loop for holding optional stylus. ▪ Sold separately: Rugged boot SKU# SG-TC5AEXO1-01. ▪ Also available as a 3-pack — 3 hand straps— SKU# SG-TC5A7A-HDSTP-03 * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Screen Protector SKU# **SG-TC5A7A-SCRNP-01** 	**TC501 Screen Protector** ▪ SKU# SG-TC5A7A-SCRNP-01 ▪ Screen protector - Tempered glass. ▪ Includes alcohol wipes, cleaning cloth, and instructions needed for screen protector installation. ▪ Also available as a 3-pack — 3 screen protectors — SKU# SG-TC5A7A-SCRNP-03. * Please note this accessory is a consumable and may require replacement during the device's lifespan.

Soft Goods

Soft Holster, Stylus, and Tether

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Soft Holster SKU# **SG-NGTC5TC7-HLSTR-01** 	**TC501 Soft Holster** · Vertical orientation with open bucket design to accommodate TC501 with optional pistol-grip trigger handle, and / or hand strap. · Strap on rear of holster allows adjustment for use with the accessory options mentioned above. · Includes loop for storage of optional stylus. Nonrotating for maximum durability. · Holster is leather material and includes cut-out for speaker output. * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Stylus SKU# **SG-STYLUS-TCX-MTL-03** 	**TC501 Stylus** · Heavy-duty and made from stainless steel / brass. No plastic parts — real-pen feel. Can be used in rain. · Micro-knit, hybrid-mesh, fiber tip provides silent, smooth gliding use. 5" length. · Big improvement over rubber-tipped or plastic-tipped stylus. · Compatible with all capacitive touch screen devices. · Tether to device or hand strap using SKU# SG-TC5NGTC7NG-TETHR-03. * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Tether SKU# **SG-TC5NGTC7NG-TETHR-03** 	**TC501 Stylus Tether** · When hand strap is used, tether should attach to hand strap SKU# SG-TC5A7A-HDSTP-01 directly (not to terminal towel bar). · String type tether prevents loss of stylus. · NOTE: Other Zebra coiled tethers are not recommended for use with TC501 as they may interfere with other accessories. * Please note this accessory is a consumable and may require replacement during the device's lifespan.

Trigger Handle

Electronic Trigger Handle and Wrist Strap

Trigger Handle

Electronic Trigger Handle and Wrist Strap

[Cradles](#)

[Batteries](#)

[Power Supplies, Cables and Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Wearable Mounts](#)

[Headsets](#)

[Third Party Accessories](#)

Item/SKU#	Description
Electronic Trigger Handle SKU# **TRG-TC5AB-ELEC-01** 	**TC501 Electronic Trigger Handle WITH Rugged Boot** ▪ The drop specification is 7 feet to concrete. ▪ Uses electrical trigger via contacts on back side of TC501. ▪ Trigger handle accessory offers customers the option of using the product in a gun form factor, ideal for scan-intensive situations. ▪ Requires rugged boot SKU# SG-TC5AEXO1-01 and device for attachment. ▪ Compatible with both standard and extended capacity batteries. ▪ Sold separately: Optional wrist strap SKU# SG-PD40-WLD1-01.
Electronic Trigger Handle SKU# **TRG-TC5A-ELEC-01** 	**TC501 Electronic Trigger Handle WITHOUT Rugged Boot** ▪ The drop specification is 6 feet to tile. ▪ Uses electrical trigger via contacts on back side of TC501. ▪ Trigger handle accessory offers customers the option of using the product in a gun form factor, ideal for scan-intensive situations. ▪ Compatible with both standard and extended capacity batteries. ▪ Sold separately: Optional wrist strap SKU# SG-PD40-WLD1-01.
Wrist Strap SKU# **50-12500-066** 	**Wrist Strap** ▪ Attaches to bottom of Snap-on Trigger Handle SKU# TRG-TC5AB-ELEC-01 or TRG-TC5A-ELEC-01. * Please note this accessory is a consumable and may require replacement during the device's lifespan.

Wearable Mounts

Wrist Mount, Comfort Pad, and Arm Sleeve

Replacement Double BOA Wrist Straps

Replacement Single BOA Wrist Straps

Wearable Mounts

Wrist Mounts, Comfort Pad, Arm Sleeve

[Cradles](#)

[Batteries](#)

[Power Supplies, Cables and Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Wearable Mounts](#)

[Headsets](#)

[Third Party Accessories](#)

Item/SKU#	Description
Arm / Wrist Mount SKU# **SG-TC5A-WMADP1-01** 	**TC501 Arm / Wrist Mount with Standard Double BOA Length** • Swivel design allows device to be viewed in portrait or landscape mode enabling hands-free functionality. • Velcro-free design uses non-absorbent materials that can be wiped down. • Requires rugged boot SKU# SG-TC5AEXO1-01 installed on device. • Includes: Carrier, Comfort pad,, small size double BOA SKU# SG-WT5X6-WSTDS-01 * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Arm / Wrist Mount SKU# **SG-TC5A-WMADP2-01** 	**TC501 Arm / Wrist Mount with Extended Double BOA Length** • Swivel design allows device to be viewed in portrait or landscape mode enabling hands-free functionality. • Velcro-free design uses non-absorbent materials that can be wiped down. • Requires rugged boot SKU# SG-TC5AEXO1-01 installed on device. • Includes: Carrier, Comfort pad, large size double BOA SKU# SG-WT5X6-WSTDL-01 * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Arm Sleeve SKU# **SG-WT4027050-01R** 	**Arm Sleeve – Pack of Five** • Worn under wrist mount strap if worker is in short-sleeved shirt and wants extra sweat wicking / personal layer, comfort and slip-resistance • Material will not snag. One size fits all. • Washable in mild detergent. Should be air dried. * Please note this accessory is a consumable and may require replacement during the device's lifespan.

Wearable Mounts

Replacement Double BOA Wrist Straps

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Replacement Wrist Strap, Small SKU# **SG-WT5X6-WSTDS-01** 	**Replacement Wrist Strap With Double Dial, Small** ▪ Strap length can be adjusted between 128 mm to 191 mm (5 in to 7.5 in) * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Replacement Wrist Strap, Large SKU# **SG-WT5X6-WSTDL-01** 	**Replacement Wrist Strap With Double Dial, Large** ▪ Strap length can be adjusted between 164 mm to 265 mm (6.5 in to 10.5 in). * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Replacement Wrist Strap, Extra-Large SKU# **SG-WT5X6-WSTDX-01** 	**Replacement Wrist Strap With Double Dial, Extra-Large** ▪ Strap length can be adjusted between 218 mm to 375 mm (8.5 in to 14.8 in). * Please note this accessory is a consumable and may require replacement during the device's lifespan.

Wearable Mounts

Replacement Double BOA Wrist Straps

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
Replacement Wrist Strap, Small SKU# **SG-NGWT-WSTPST-01** 	**Replacement Wrist Strap With Single Dial, Small** ▪ White dial and accent color on strap identify size as small. ▪ Strap length can be adjusted between 128 to 191mm (approx. ▪ 5.0 to 7.5"). * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Replacement Wrist Strap, Large SKU# **SG-NGWT-WSTPLN-01** 	**Replacement Wrist Strap With Single Dial, Large** ▪ Black dial and accent color on strap identify size as large. ▪ Strap length can be adjusted between 164 to 265mm (approx. 6.5 to 10.5"). * Please note this accessory is a consumable and may require replacement during the device's lifespan.
Replacement Wrist Strap, Extra-Large SKU# **SG-NGWT-WSTPXL-01** 	**Replacement Wrist Strap With Single Dial, Extra-Large** ▪ Blue dial and accent color on strap identify size as extra-large. ▪ Strap length can be adjusted between 218 to 375 mm (approx. 8.5 to 14.75"). * Please note this accessory is a consumable and may require replacement during the device's lifespan.

Headsets

Close gaps, Open possibilities with Workcloud Sync

Usher in a new era of transformation—one led by your frontline and powered by Zebra Workcloud Sync. One where communication and information flows freely and gaps between teams, workflows and data are closed.

With Workcloud Sync, hindered workers become effective problem solvers, contributing their best. Critical workflows are streamlined in one place, on one device, equipping workers with the information they need, right at their fingertips.

Only Zebra offers the most complete lineup of software and rugged hardware with the scalability, support and service needed to make the greatest impact where it counts—on the frontline.

Learn more about how you can elevate your frontline workers with Zebra Workcloud Sync.

Rugged Bluetooth HD voice headsets for the most demanding industrial environments

When it comes to enabling speech-driven applications and voice communications in warehouses, manufacturing plants and outdoor yards, you need a headset that is specially designed for the job. The HS3100 Bluetooth Headsets are loaded with features that offer everything you need in an industrial headset.

Learn more about how these headsets deliver a superior voice experience

Wireless headsets and accessories for voice-directed picking

Headsets

Wired Headset for Workcloud Sync

[Cradles](#)

[Batteries](#)

[Power Supplies, Cables and Adaptors](#)

[Soft Goods](#)

[Trigger handles](#)

[Wearable Mounts](#)

[Headsets](#)

[Third Party Accessories](#)

Item/SKU#	Description
Wired Headset SKU# **HDST-USBC-PTT1-01** 	**PTT headset with USB-C connector; one-piece solution.** • For Push-To-Talk (PTT) applications with volume up / volume down / PTT buttons. Compatible with PTT Express / PTT Pro. • Rotating earpiece allows for right or left ear configuration. Mono headset with microphone. • Includes clip for attaching PTT button to clothing.

Headsets

Rugged Bluetooth Headset

Cradles

Batteries

Power Supplies, Cables and Adaptors

Soft Goods

Trigger handles

Wearable Mounts

Headsets

Third Party Accessories

Item/SKU#	Description
HS31 00 Bluetooth Headset SKU# **HS3100-OTH** 	**HS3100 Rugged Bluetooth Headset** • HS3100 Rugged Bluetooth Headset Over-The-Head Headband includes HS3100 Boom Module and HSX100 OTH Headband Module
HS31 00 Bluetooth Headset SKU# **HS3100-BTN-L** 	**HS3100 Rugged Bluetooth Headset** • HS3100 Rugged Bluetooth Headset (Behind-the-neck headband left)
HS31 00 Bluetooth Headset SKU# **HS3100-OTH-SB** 	**HS3100 Rugged Bluetooth Headset** • HS3100 Rugged Bluetooth Headset (Over-the-head headband) includes HS3100 Shortened Boom Module and HSX100 OTH headband module
HS31 00 Bluetooth Headset SKU# **HS3100-BTN-LSB** 	**HS3100 Rugged Bluetooth Headset** • HS3100 Rugged Bluetooth Headset (Behind-the-neck headband left) includes HS3100 Shortened Boom Module and HSX100 BTN headband module
HS31 00 Bluetooth Headset SKU# **HS3100-SBOOM-01** 	**HS3100 Rugged Bluetooth Boom Module** • HS3100 Shortened Boom Module (includes microphone boom, battery and wind screen)

Third Party Accessories

RAM Vehicle Docks



RAM® Vehicle Docks for Zebra TC501

Key Features



Pogo Pin Charging

Uses integrated pogo pins and device docking contacts to protect the charge port and enhance ruggedness.



USB-C Connectivity

Integrated USB-C connector supports charging, data transfer, and Workstation Connect, enabling fast, confident docking while reducing connector wear.



Removable Inserts

Custom inserts, or "shims", ensure a secure fit and smooth, fumble-free docking.



Wireless Charger Compatible

Add a RAM® Wireless Charger directly to the dock when a Wireless Charging Battery is installed for seamless wireless charging.

Compatible Docks

3PTY-RAM-HOL-ZE41-2U
RAM® Powered Dock with Pogo Pins for TC501

3PTY-RAM-HOL-ZE41L-2U
RAM® Locking Powered Dock with Pogo Pins for TC501

3PTY-RAM-HOL-ZE41C-2U
RAM® Powered Dock with USB-C for TC501

3PTY-RAM-HOL-ZE41KL-C-2U
RAM® Locking Powered Dock with USB-C for TC501

3PTY-RAM-HOL-ZE41-NPU
RAM® Cradle for TC501/TC701

3PTY-RAM-HOL-ZE41KL-NPU
RAM® Locking Cradle for TC501/TC701

Hardwire Chargers



3PTY-RAM-GDS-CHARGE-V3C-3U
GDS® 10-30V Power Delivery Hardwire Charger with Male USB Type-C

3PTY-RAM-GDS-CHARGE-M55-V7B1U
GDS® 10-30V Hardwire Charger with USB-A to DC Cable