OVERVIEW



1. Power connector	4. DisplayPort 1.4
2. HDMI 2.1 TMDS	5. Audio-out (3.5mm)
3. HDMI 2.1 TMDS	

PERFORMANCE

Panel

Panel

4-sided Ultra Thin, QD-OLED

Display Size

26.5 inches

Max View Area

- Active Area: 590.4 x 333.7 mm
- Screen Dimension: 609.8 x 350.2 mm

Resolution

2560 x 1440

Aspect Ratio

16:9

Pixel Pitch

0.2292 x 0.2292 mm

Dot / Pixel Per Inch

110 dpi

Brightness

- Peak: 400 cd/m²
- Typical: 200 cd/m²

Contrast Ratio

- Contrast Ratio: 1500000:1
- Dynamic Contrast Ratio (Typical): 1500000:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

G to G: 0.03 ms

Refresh Rate

240Hz

Color Gamut

- Coverage Ratio: 99% sRGB (CIE 1931)
- Coverage Ratio: 99% DCI-P3 (CIE 1976)

Color Support

1.07 Billion

Color Depth

True 10-bit

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Operating System

Operating System

- Windows® 11 Support
- Windows® 10 Support

Power Supply

Power Consumption

- Typical / Max: 41W / 67W
- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- Internal Power Supply

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- HDR10 Compliance
- ClearMR 13000
- Factory Calibration: Avg. Delta E<2 at sRGB
- AMD FreeSync™ Premium
  AMD FreeSync™ technology only can work with AMD Radeon™ series graphics card
- VESA Adaptive Sync
- Lenovo® Artery (Lenovo® Accessories and Display Manager) Support
  Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems)
  Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center
- Legion Space
- Mirrored Power Button
- Natural Low Blue Light

DESIGN

Mechanical

ThinkCentre® M Series Support

None

Bezel Width

- Thickness of Head: 3.9mm (Minimum)
- Side: 1.0mm
- Top / Bottom: 1.0mm / 12.7mm

Cable Management

Support

Case Color

Black

Dimensions (WxDxH)[1]

Models	Dimensions
Lowest Position	609.3 x 214.0 x 389.2 mm (23.99 x 8.43 x 15.32 inches)
Highest Position	609.3 x 214.0 x 524.2 mm (23.99 x 8.43 x 20.64 inches)
Head Only	609.3 x 40.5 x 354.3 mm (23.99 x 1.59 x 13.95 inches)

Packaging Dimensions (WxDxH)

800.0 x 139.0 x 480.0 mm (31.50 x 5.48 x 18.90 inches)

Weight[2]

Models	Weight
Monitor With Stand	6 kg (13.2 lbs)
Monitor Head Only	3.8 kg (8.4 lbs)

Packaging Weight

- EPS: 8 kg (17.6 lbs)
- Pulp: 9.0 kg (19.8 lbs)

Mounting

Supports VESA mount 100 x 100 mm

Stand

Supports -5° to +22° tilt, left & right 30° swivel, -90° to +90° pivot, up to 135mm lift

In the Box

- Monitor with stand
- 1x DP cable (1.8m)
- 1x Power cable (1.8m)

- 4x Screws
- Quick setup guide
- Warranty booklet

Notes:

[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Ports[1]

Rear Ports

- 2x HDMI® 2.1 TMDS[2]
- 1x DisplayPort™ 1.4 (HBR3)[3]
- 1x audio-out (3.5mm)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s.
Thunderbolt™ 5: 80 Gbit/s (bidirectional), up to 120 Gbit/s in bandwidth boost mode for video-intensive applications.
[2] Supports 2560 x 1440 @ 144Hz as specified in HDMI® 2.1 TMDS.
[3] Supports max. bandwidth 32.4 Gbps.

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Security Slot™ (3 mm x 7 mm)

SERVICE

Warranty

Base Warranty

3-year limited warranty

OPERATING REQUIREMENTS

Operating Environment

Temperature

Operating: 0°C to 40°C (32°F to 104°F)
Storage: -20°C to 60°C (-4°F to 140°F)
Transport: -20°C to 60°C (-4°F to 140°F)

Relative Humidity

Operating: 10% to 80% non-condensing
Storage: 5% to 95% non-condensing
Transport: 5% to 95% non-condensing

CERTIFICATIONS

Green Certifications[1]

Green Certifications

- EU Energy Label (E-class)
- RoHS (2011/65/EU)

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit https://compliance.lenovo.com.

Other Certifications

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS", WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.


Lenovo
LEGION


Lenovo
LEGION


LEGION
Lenovo






LEGION
Lenovo