

Specifications



Eaton TLP118DBTELV

Protect It! 11-Outlet Surge Protector - 5-15R Outlets, 4200 Joules, Phone/Modem/Coax Protection, 8 ft. (2.4 m) Braided Cord, Black

General specifications

PRODUCT NAME	Eaton Tripp Lite series surge protector
CATALOG NUMBER	TLP118DBTELV
UPC	037332294050
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	1.42 in
PRODUCT WIDTH	4.8 in
PRODUCT WEIGHT	1.2 lb
CERTIFICATIONS	CSA C22.2. CSA Std. C22.2 UL Listed UL 1449
GLOBAL CATALOG	TLP118DBTELV
PRODUCT TYPE	Surge protector



Powering Business Worldwide

Product specifications

OPERATING TEMPERATURE	0° to 40°C
STORAGE HUMIDITY RANGE	0% to 90% RH
SURGE STYLE	ST - STRIP
SWITCHES	Combination AC circuit breaker and 2 position red illuminated on/off power switch
VOLTAGE COMPATIBILITY (VAC)	120
OUTLETS	11
CIRCUIT BREAKER	15
FREQUENCY RATING	50/60 Hz
DIAGNOSTIC LED DETAILS	Built-in LED confirms suppressor "protection present" (green) status
EMI / RFI FILTERING	Yes
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OVERLOAD PROTECTION	15A resettable illuminated combo switch / circuit breaker
PROTECTION MODES	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
RECEPTACLE COLOR	BLACK
RECOMMENDED ELECTRICAL SERVICE	120V (110-125V)
STORAGE TEMPERATURE RANGE	5° to 104°F (-15° to 40°C)
TRANSFORMER ACCOMMODATION	Transformer Accommodation
UL1449 LET THROUGH RATING	500V
INPUT CORD DETAILS	SJT
INPUT CORD GAUGE (AWG)	14
CORD LENGTH	8 Foot
POWER CORD COLOR	Black
HOUSING COLOR	Black
OUTLET ORIENTATION	two rows of 11 outlets total
MATERIAL	Plastic
INPUT PLUG TYPE	NEMA 5-15P
PRODUCT CATEGORY	Surge Protector

Resources

OUTPUT RECEPTACLES	5-15R
PACKAGE CONTENTS	TLP118DBTELV 11-Outlet Surge Protector Owner's manual
INPUT NOMINAL VOLTAGE	120 VAC
PRODUCT FEATURES	Automatic Shut-Off Telephone/DSL Protection Mounting Holes or Slots Cable (Coax) Protection Diagnostic LED(s) UL Certified
PRODUCT HIGHLIGHTS	11 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment 4200 joules protect your valuable electronics against dangerous surges and spikes USB ports share 4A for fast charging of phones, tablets and other mobile devices 8 ft. braided input cord with NEMA 5-15P plug connects to compatible AC wall outlet On/off switch with circuit breaker allows one-touch control over connected equipment
PLUG COLOR	White Blue
AC SUPPRESSION JOULE RATING	4200
AC SUPPRESSION RESPONSE TIME	< 1 ns
CORD GAUGE TYPE	<ul style="list-style-type: none"> • 14 gauge • SJT
MAXIMUM SURGE AMPS	4200
OPERATING HUMIDITY RANGE	20% to 85% RH
TOTAL OUTLETS	11

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

