HP 65W GaN Wall Charger (C90CKUT)



Overview

Powerful, portable charging for life on the go.

Power your day with the HP 65W GaN Wall Charger. Smaller, lighter,[6] and designed for efficient, safe charging,[5] it delivers reliable power for most USB-C® devices and protects against surge, overcurrent, overvoltage, and overtemperature.

Powerful, safe USB-C® charging

Experience powerful charging safely. With GaN technology for high efficiency,[1] PD 3.0 compliance, and up to 65W of adaptive power,[2] this charger keeps your USB-C® devices[3,4] running safely and reliably with built-in protection[5] against surges, overheating, and overcharging—all following the latest safety standards.

Extra length. Extra flexibility.

Start charging straight out of the box. This charger includes a 2 m USB-C® cable, giving you extra length and flexibility, and skipping the extra purchase. Everything you need, included.

Smaller design, easier to carry

Travel-ready charging. Built on GaN technology, this adapter is 35% smaller and 15% lighter than before[6], and it includes a detachable plug to pack easily in your bag or pocket and get local compatibility.

Designed with purpose

The better choice for a brighter tomorrow, this charger contains at least 90% post-consumer recycled plastic (PCR)[7], includes a low-halogen 2m USB-C® cable[8,9], and comes in FSC®-certified packaging[8].

Features

Detachable plug for local compatibility

Includes a detachable plug for local compatibility, so you can charge your devices wherever you go. Have power and adaptability without limits.

Power that adjusts to your needs

Experience smart charging and get just the right amount of power for your device—providing efficient, safe, and adaptive charge.[2]

Compatible with most USB-C® devices

One charger for your essentials. Compatible with most USB-C® devices, this charger delivers reliable charging for laptops, smartphones, and tablets—designed for everyday versatility.[10]

Built-in hardware protection

Built-in protection against surge, overcurrent, overvoltage and overtemperature.[5]

2 m USB-C® cable included

The 2 m detachable low-halogen 2 m USB-C® cable offers flexibility to charge from your desk, couch, or wherever's convenient.[9]

Get peace of mind with 1-year limited warranty

Experience HP quality and reliability. For added peace of mind, this charger comes with a 1-year limited warranty.[11]

---

[1] Compliant with EU Lot7 power efficiency.

[2] Adaptive power output(15W/27W/45W/65W)

[3] Supports USB-C® PD protocol.

[4] Up to 65W max output.

[5] Compliant with the latest safety standards (IEC 62368-1).

[6] Based on dimensions from prior generation product HP 65W USB-C Laptop Charger: L 97 x W 53.5 x H 21 mm. Weight specs exclude detachable plug.

[7] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT® standard for computers, IEEE 1680.1-2018 EPEAT® standard.

[8] Forest Stewardship Council® (FSC) Certified, meaning all components of our packaging come from responsibly managed forests to provide environmental benefits.

[9] Low-halogen material complies with IEEE 1680.1-2018 Bromine and Chlorine requirement.

[10] Compatible with most devices that charge using USB-C®.

Specifications

Product Dimensions (metric)	65 x 32 x 32 mm
Product Dimensions (imperial)	2.56 x 1.26 x 1.26 in
Weight (metric)	115 g
Weight (imperial)	0.24 lb
Package Dimensions (metric)	131 x 117 x 56 mm
Package Weight (metric)	270 g
Sustainability Specifications	FSC Certified Packaging; 90% post-consumer recycled plastic
System Requirements, Minimum	USB Type-C® port
UPC Number	(AB0) 199896947626; (AB1) 199642432307; (AB2) 199642432314; (ABA) 821844102510; (ABB) 199642432321; (ABG) 199642432338; (ABJ) 821844012130; (ABM) 199896947633; (ABU) 199642432345; (AC4) 199642432352; (AC8) 199642432369; (ACJ) 199642432376; (ACQ) 199642432383; (AKH) 199642432390; (AKL) 885981038385; (AR6) 199642432406; (UUF) 199642432413
Manufacturer Warranty	HP standard one-year limited warranty
What Is In The Box	AC power adapter; USB Type-C® cable, Product notice; Warranty card; Quick start guide

Additional specifications

Cable Length (imperial)	6.56 ft
Cable Length (metric)	2 m
Certifications and Compliances	CE Mark; IEC 60950-1; C-UL-US; FCC Class B; CISPR 32 Class B; CCC; NOM-1 NYCE; S Mark; BSMI; ISC; PSE; PSB; EN55032 Class B; EN62368-1; UL62368-1; BIS; CECP; TUV/PSE; EAC; EAEU; KCC; K-MEPS; NRCan; NRCS; SEC; Argentina S-Mark; UAE; UKCA DoC
Compatibility Statement	Supports up to 65 W power delivery
Connection Type	USB Type-C®
Datasheet Photo 01	https://prismpui-int.inc.hpicorp.net/PRO.Crystal.1/DAMHandler/Accessories/26C1_HP%2065W%20GaN%20Wall%20Charger_WW_Product-Only_TransparentBG_RearLeft_5101852.png
Hold-up Time	100% load 5 ms at 115 VAC input
Input Efficiency	89% min at 115 VAC/230 VAC at 20V/3.25A
Input Frequency	47-63 Hz
Input Operating Current	1.6 A at 90 VAC max
Non-operating Humidity Range	10 to 95% RH
Non-operating Temperature - Celsius	-20°C to 85°C
Non-operating Temperature - Fahrenheit	-4 to 185°F
Operating Humidity Range	20 to 95% RH
Operating Temperature Range (celsius)	0 to 35°C
Operating Temperature Range (fahrenheit)	32 to 95°F
Output Power	65 W
Output Voltages	5V/9V/15V/20V
Package Dimensions (imperial)	5.1 x 4.6 x 2.2 in
Package Weight (imperial)	0.6 lb

Storage Temperature Range (celsius)	-20 to 85°C
Storage Temperature Range (fahrenheit)	-4 to 185°F
UNSPSC Code	39121006

Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jul 12, 2026 8:54 PM UTC+0000