





Overview

Dimensions	122.5 x 107.1 x 28 mm (4.8 x 4.2 x 1.1")
Port Layout	5 (4 PoE+; 1 PoE++) (1G/100M/10M)
Max. PoE Output	Up to PoE+
Total PoE Availability	46W
Form Factor	Compact desktop, wall, pole

Performance

Switching Capacity	10 Gbps
Total Non-Blocking Throughput	5 Gbps
Forwarding Rate	7 Mpps
Supported VLANs	1,000
MAC Address Table Size	2,000

Layer 2 Features

Egress Rate Limit	✓
Flow Control	✓
Port Isolation	✓
Port Mirroring	✓
Jumbo Frames	✓

Hardware

PoE Ports	4 PoE+ 1 PoE++
Max. PoE Wattage per Port by PSE	PoE+ 25W
Max. Power Consumption	5W (Excluding PoE Output) 51W (Including PoE Output)
Power Method	PoE++
Power Input Method	PoE
Supported Voltage Range	50—57V PoE
Management	Ethernet
Heat Dissipation	17.1 BTU/hr (Excluding PoE Output)
Outdoor Ready	✓
Weight	230 g (8.1 oz)
ESD Protection	Air/contact: ± 16kV
Ambient Operating Temperature	46W PoE output: -40 to 55° C (-40 to 131° F) 25W PoE output: -40 to 65° C (-40 to 149° F)
Ambient Operating Humidity	5 to 95% noncondensing
NDA compliant	✓
Certifications	CE, FCC, IC, Anatel: 14502-20-08356

Software

Application Requirements	UniFi Network Version 5.10.3 and later
--------------------------	---