

Flex Mini 2.5G


USW-Flex-2.5G-5

Datasheet

In The Box

Marketing Images

Installation Guide



Overview

Dimensions	117.1 x 90 x 21.2 mm (4.6 x 3.5 x 0.8")
Port Layout	5 2.5 GbE RJ45
Form Factor	Compact desktop

Performance

Switching Capacity	25 Gbps
Total Non-Blocking Throughput	12.5 Gbps
Forwarding Rate	19 Mpps
Supported VLANs	256
MAC Address Table Size	4,000

Layer 2 Features

STP & RSTP	✓
Egress Rate Limit	✓
Flow Control	✓
Storm Control	✓
Multicast & Broadcast Rate Limiting	✓
Port Isolation	✓
Port Mirroring	✓
Jumbo Frames	✓
Loop Protection	✓

Hardware

Max. Power Consumption	5W (AC/DC Input) 6.4W (PoE Input)
Power Method	(1) USB Type-C, 5V DC, 1A (1) PoE
Power Input Method	USB Input PoE
Power Supply	AC/DC, external, 5W
Supported Voltage Range	4.8—5.2V DC/USB 44V—57V PoE
Management	Ethernet
Weight	206 g (7.3 oz)
Enclosure Material	Polycarbonate
Ambient Operating Temperature	-20 to 45° C (-4 to 113° F)
Ambient Operating Humidity	10 to 90% noncondensing
NDAA Compliant	✓
Certifications	CE, FCC, IC, Anatel

Software

Application Requirements	UniFi Network Version 8.6.9 and later
--------------------------	--

Company

Blog

Case Studies

Careers

Trust Center

Contact Us

Investors

Compliance

Training

Courses

Calendar

Trainers

Become a Trainer

Buy Now

Ubiquiti Store

Find a Distributor

Become a Distributor

Tools

WiFiMan

UISP

UniFi Design Center

UISP Design Center

Downloads

Stay In Touch

Email

Subscribe

f

X

▶

📷