

3ft (0.9m) TAA-Compliant USB 2.0 A Male to A Female Extension Cable **SKU: C2G68011**



When you need just a little more distance, this cable will extend the reach of your existing USB A/B cable. Foil and braid shielding reduce EMI/RFI interference and twisted pair construction helps reduce crosstalk for a high speed, error-free data transfer. USB 2.0 compatible. PC and Mac compatible.

Please Note: Not for use beyond a total extended single length of 16 feet. For longer lengths or high-powered devices, please consider using one of our Superbooster® or other USB extension products.

Features and Benefits

- Extends an existing USB cable or device
- Support USB 2.0 speeds
- Shielded to protect from interference
- TAA-Compliant

Specifications

Dimensions &

Measurements

Bend Radius	47 mm (1.9 in)
Cable Diameter	4.7 mm (0.2 in)
Cable Length	0.91 m (3 ft)
Operating Humidity Max	90% RH (Non-Condensing)
Operating Humidity Min	20% RH (Non-Condensing)
Operating Temperature	23° - 113°F (-5° - 45°C)
Shipping Weight	0.04 kg (0.1 lbs)
Storage Humidity Max	90% RH (Non-Condensing)
Storage Humidity Min	20% RH (Non-Condensing)
Storage Temperature Max	65 Celsius (149 Fahrenheit)
Storage Temperature Min	-40 Celsius (-40 Fahrenheit)
Wire Gauge	24

Characteristics & Features

Cable Type	<ul style="list-style-type: none">• Extension• USB 2.0
Color	Black
Connector 1	(1) USB-A Male
Connector 2	(1) USB-A Female
Product Type	Cable
Signal Type	Bidirectional
TAA Compliant	Yes

Certifications & Warranties

Certifications

- NDAA 889
- Prop 65
- REACH
- RoHS
- TAA
- TSCA

Data Transfer Rate

480 MBPS

Jacket Material

PVC

Warranty

Lifetime

Source: https://www.legrandav.com/products/cables_and_connectivity/usb_cables/usb-2_0-a-male-to-a-female-extension-cable-black/c2g68011