




Anywhere.
Everyday.



Product Range
2026



verbatim

CONTENTS

ABOUT VERBATIM

ABOUT VERBATIM	2
ACCESSORIES	3
PORTABLE MONITORS	4
WEBCAMS	7
MICE	8
KEYBOARDS	9
HEADSETS	10
HEADPHONES	13
SYNC & CHARGE CABLES	14
MULTIPORT HUBS	18
CARD READERS	21
SHARE MY SCREEN	22
WIRELESS PRESENTER	23
GAN CHARGERS	24
CAR CHARGERS	25
WIRELESS CHARGERS	25
WALL CHARGERS	25
POWER BANKS	26
MY FINDER	28
BACKING-UP AND ARCHIVING	30
DVD & CD WRITERS	32
LIFETIME OF DATA STORAGE FORMATS	33
USB DRIVES	34
UNDERSTANDING USB STANDARDS	35
USB-C®	36
USB 3.2 GEN 1	37
USB 2.0	39
MEMORY CARDS	40
EXTERNAL SSD	43
HARD DRIVES	47
OPTICAL TECHNOLOGY	49
BLU-RAY	51
MDISC	52
DVD	53
CD	55
KEY MILESTONES	56
ETHICAL SOURCING & SUSTAINABILITY	57



OUR BRAND STORY

At Verbatim, we believe that technology is about improving your everyday life. For over 50 years, we have worked to build a future that seamlessly integrates technology in ways that improve how people everywhere live, work and play.

Throughout those 50 plus years, we have continued to innovate and develop not only our products but also our brand experience. Now, in 2026, it is time to continue that evolution. Our new brand is designed to have true global relevance for the digital era.

The idea behind the new brand was to provide a modern, clean and functional logo and V symbol, fit for the digital first world. We chose a geometric typeface, and strong colour scheme, evolving from the red and blue used in the Verbatim logo throughout the years.

Along with the brand mark, we have also developed our tagline. Technology you can Trust is still key to our company ethos, but 'Anywhere. Everyday.' gets to the heart of the Verbatim product offering. We aim to create a positive connection to everyday life for our consumers. By making this connection we are also delivering on the promise of 'trust' by showing that customers can rely on us as part of their everyday life. New imagery and messaging follow this example. Focusing on showing everyday modern life at work and play and the human emotion which the product provides. These are simple and impactful, getting the message across quickly. Ideal for the digital world.

We hope you like our new branding, building on our core values for an exciting future.





ACCESSORIES

Verbatim offers an extensive line of innovative, reliable, and affordable accessories designed to enhance the experience of your favourite devices and to enable work on the go.



PORTABLE MONITORS

Portable Touchscreen Monitor Full HD 1080p

- Portable monitor with Full HD resolution of 1920 x 1080 and 16.7M colours
- Supports capacitive 10-point multi-touch; simply connect the monitor to your device using a USB-C® cable
- IPS Panel incl. full viewing angle of 178° and 16:9 screen ratio
- Solid and durable aluminium housing
- HDR technology improves picture quality creating a fantastic viewing experience
- Great compatibility for work/traveling/gaming: Connect the portable monitor to your PC/Mac/Tablet/Phones/Consoles with USB-C or HDMI

PART NO	DESCRIPTION
49591	PMT-14 Portable Touchscreen Monitor - 14"
49592	PMT-15 Portable Touchscreen Monitor - 15.6"
49593	PMT-17 Portable Touchscreen Monitor - 17.3"

Portable Monitor Full HD 1080p

- Portable 14" monitor with Full HD resolution of 1920 x 1080 and 16.7M colours
- IPS Panel incl. full viewing angle of 178° and 16:9 screen ratio
- HDR technology improves picture quality creating a fantastic viewing experience
- Great compatibility for work/traveling/gaming: Connect the portable monitor to your PC/Mac/Tablet/Phones/Consoles with USB-C or HDMI
- One Cable Solution: Plug and play setup of compatible devices via USB-C connection

PART NO	DESCRIPTION
49590	PM-14 Portable Monitor - 14"





Portable Monitors - Light Series

- IPS panel with ultra-wide 178° viewing angles and 16:9 aspect ratio
- HDR technology for enhanced picture clarity
- Lightweight and ultra-slim for maximum portability
- USB-C plug & play – one cable for video, touch, and power
- Integrated stereo speakers and 3.5mm audio jack
- Foldable stand for convenient setup and flexible viewing angles
- Compatible with PCs, smartphones, tablets, and more
- Capacitive 10-point multi-touch for intuitive control (32405, 32406)
- Non-touch model (32406)
- Perfect for mobile professionals, hybrid workers, and students who need a lightweight, travel-ready dual-screen solution

PART NO DESCRIPTION

32405	Portable Touchscreen Monitor Light Series - 14"
32407	Portable Touchscreen Monitor Light Series - 15.6"
32406	Portable Monitor Light Series - 15.6"

Dual Portable Monitor 15.6"

- Dual Full HD 15.6" IPS screens (1920 × 1080 resolution each)
- 178° wide viewing angle with 16:9 aspect ratio
- HDR support for improved contrast and colour accuracy
- Ultra-slim design with integrated 1W stereo speakers
- Supports Extend*, Duplicate, and Ultra Display modes (*Windows only)
- VESA 75x75 mm mount compatible
- Auto-rotation support for top screen when folded
- Lightweight and portable with protective neoprene sleeve
- USB-C and Mini HDMI connectivity
- Ideal for multitasking, presentations, and remote work setups

PART NO DESCRIPTION

32408	Dual Portable Monitor - 15.6"
-------	-------------------------------





Portable Touchscreen Monitor 13.3" WUXGA Resolution with Wireless Power Display

- Portable Touchscreen Monitor with WUXGA Resolution of 1920 x 1200 and 16.7M colours
- Wireless Power Supply with 5000mAh Power Bank
- IPS Technology – full viewing angle of 178° and 16:10 screen ratio
- High Dynamic Range (HDR) – Enhanced contrast and brightness for more realistic content
- Sleek, durable aluminium housing
- Integrated Speaker
- Multi-Touch Display – Intuitive touch control for seamless interaction.



PART NO	DESCRIPTION
32087	Portable Touchscreen Monitor WUXGA Resolution & Wireless Power - 13.3"

Portable Touchscreen Monitor 14" Full HD 1080p with Wireless Power Supply

- Portable Touchscreen Monitor with wireless power supply including a 5000mAh Power Bank
- Full HD Resolution 1920 x 1080p and 16.7 million colours
- IPS Technology – full viewing angle of 178° and 16:9 screen ratio
- High Dynamic Range (HDR) – Enhanced contrast and detail for more lifelike content
- Lightweight housing, ideal for travel
- Integrated Speaker
- Multi-Touch Display – Smooth, responsive touch interaction for effortless control



PART NO	DESCRIPTION
32088	Portable Touchscreen Monitor Full HD 1080p & Wireless Power - 14"





WEBCAMS

1080p Full HD Webcam

- Full HD 1080p resolution
- Built-in full directional high sensitivity and low noise microphone
- Manual focus from 30cm to infinity
- Integrated microphone
- USB Plug & Play

PART NO	DESCRIPTION
---------	-------------

66614	Full HD 1080p Webcam
-------	----------------------



1080p Full HD Auto Focus Webcam

- Full HD 1080p resolution
- Autofocus from 7cm to infinity with auto white balance
- USB Plug & Play
- Integrated microphone
- Automatic low light correction

PART NO	DESCRIPTION
---------	-------------

66631	Full HD 1080p Autofocus Webcam
-------	--------------------------------



MICE

Silent Ergonomic Wireless LED Mouse

- Truly silent mouse featuring Silent Technology, silent click switches, and rubber covers
- Ergonomic design with thumb support lets you work all day with ease
- Adjustable DPI button – easily switch between 800, 1300 and 1600 DPI
- Side back/forward buttons – easily navigate between pages in your browser
- 2.4Ghz wireless connection for lag-free performance
- Blue LED technology allows for use on virtually any surface with precision and control
- Plug-and-forget nano receiver connects mouse to computer

Colours available:



PART NO	DESCRIPTION
70242	Silent Ergonomic Wireless LED Mouse - Graphite
70243	Silent Ergonomic Wireless LED Mouse - Red
70244	Silent Ergonomic Wireless LED Mouse - Blue



Silent Wireless LED Mouse

- Truly silent mouse featuring Silent Technology, silent click switches, and rubber covers
- 2.4Ghz wireless connection for lag-free performance
- Blue LED technology allows for use on virtually any surface with precision and control
- Ergonomic design and comfort grip for ease-of-use
- Plug-and-forget nano receiver connects mouse to computer

Colours available:



PART NO	DESCRIPTION
99769	Silent Wireless LED Mouse - Graphite
99770	Silent Wireless LED Mouse - Blue
99777	Silent Wireless LED Mouse - Silver
99780	Silent Wireless LED Mouse - Red



GO NANO Wireless Mouse

- 1600 dpi three button Nano wireless mouse
- Plug-in Nano receiver – small enough to leave connected
- 2.4GHz RF wireless technology
- Smooth, contoured design provides comfort and control
- Available in three colours – Black, Hot Pink and Caribbean Blue

Colours available:



PART NO	DESCRIPTION
49042	GO NANO Wireless Mouse Black
49043	GO NANO Wireless Mouse Hot Pink
49044	GO NANO Wireless Mouse Caribbean Blue



KEYBOARDS

Wireless Keyboard & Mouse Combo

Compact Wireless Keyboard and Mouse Combo - 32412

- Silent keyboard keys and silent mouse clicks
- Compact 81-key keyboard with low-profile design
- Blue LED optical mouse with 1600 DPI precision
- One 2.4GHz nano receiver connects keyboard and mouse
- Receiver storage inside mouse for easy transport
- Made with recycled plastic (keyboard 65%, mouse 85%)
- Plug-and-play via USB-A receiver
- Compatible with Windows, macOS, Chrome OS and Linux



Silent Wireless Keyboard and Mouse - 32413

- 104-key layout with multimedia hotkeys for quick control
- 4-button design with 3-level DPI (800/1200/1600) for easy sensitivity switching
- A single nano USB receiver connects both devices; stable range up to 10 m. Receiver stores inside the mouse for travel.
- Keyboard and mouse housings made with 85% recycled plastic
- Auto sleep after 10 sec. of inactivity
- Plug-and-play on Windows, macOS, and Linux



PART NO	DESCRIPTION
---------	-------------

32412	2.4GHz Wireless Keyboard and Mouse Combo
-------	--

32413	Silent Wireless Keyboard and Mouse Combo
-------	--





For work.



For play.



Headsets & Headphones

Verbatim's range of quality headsets let you upgrade your audio experience without breaking the bank. Whether you're a gamer, music lover, remote worker, or a student, we've got the perfect headset to match your needs. Say goodbye to compromising on quality and comfort – Verbatim headsets offer the best of both worlds.

Why choose Verbatim headsets?

Crystal Clear Sound: Immerse yourself in rich, detailed audio that brings your entertainment to life. From heart-pounding bass to crisp highs, you won't miss a single beat.

Gamer's Delight: Gain a competitive edge with precise audio cues that help you locate enemies and enhance your gaming strategy. Your victories have never sounded so sweet!

Seamless Communication: Stay connected with friends, colleagues, and teammates. Our headsets boast high-quality microphones, making your voice come through loud and clear.

Smart Features: Enjoy convenient features like in-line controls, adjustable headbands, and comfortable ear cushions that make extended wear a breeze.

Universal Compatibility: Whether you're gaming on a console, working on a laptop, or streaming content on your phone, our headsets work seamlessly across devices.

Unbeatable Value: Elevate your audio experience without straining your budget. Our headsets offer premium features at prices that won't break the bank.

Don't compromise on quality or comfort when you can have it all. Check out our full range and immerse yourself in a world of audio excellence without the hefty price tag.

Anywhere. Everyday.



HEADSETS

Classic Headset with USB-C

- USB-C Connectivity
- Lightweight body
- In-line microphone
- 3.5mm audio jack connector
- Great bass and treble reproduction
- Soft foam ear cushions
- Modern design and colour options

Classic Stereo Headset

- Lightweight body
- In-line microphone
- 3.5mm audio jack connector
- Great bass and treble reproduction
- Soft foam ear cushions
- Modern design and colour options



Multimedia Headset with Microphone

- Perfect for multimedia applications including internet voice chat and video conferencing
- Adjustable built-in microphone
- Smart, adjustable in-line volume control
- 3.5mm jack connection
- Soft foam ear cushions provide a comfortable and ergonomic fit



PART NO DESCRIPTION

67031	Classic Stereo Headset with USB-C - Black
-------	---

PART NO DESCRIPTION

65066	Classic Stereo Headset - Black
-------	--------------------------------

PART NO DESCRIPTION

41646	Multimedia Headset with Microphone
-------	------------------------------------



Headset with Inline Microphone

- 3.5mm audio jack connector
- Inline microphone and volume control
- Lightweight and adjustable headband
- Soft foam ear cushions
- Excellent bass & treble reproduction
- Wide frequency stereo output



Multimedia USB Headset with Microphone

- USB connectivity
- Gooseneck boom mic for flexible positioning
- Inline volume control panel with mic mute button and lapel clip
- Lightweight & adjustable headband
- Excellent bass & treble reproduction



PART NO DESCRIPTION

66332	Multimedia Headset with Inline Microphone
-------	---

PART NO DESCRIPTION

66556	Multimedia USB Headset with Boom Microphone
-------	---

NOISE-CANCELLING

Clarity Sound Headset with Noise-Cancelling Mic

- Plug-and-play convenience with USB-C enabled devices.
- High-fidelity sound for music, videos, and calls.
- Soft, padded ear cups and an adjustable headband provide a perfect fit for extended wear.
- Noise cancelling mic for clear, crisp communication, even with background noise
- Effortlessly manage play/pause, and calls with the built-in microphone and control button.
- Durable and Lightweight Build
- Ideal for remote work, online learning, gaming, and entertainment.

PART NO	DESCRIPTION
30195	Clarity Sound Headset with Noise Cancelling Mic

Headset with ANC & Noise-Cancelling Boom Mic

- Active Noise Cancelling reduces ambient noise
- Noise Cancelling Mic reduces background noise
- Ideal for work, school & travel
- Gooseneck boom mic for flexible positioning
- Over-ear, cushioned ear pads for comfort
- Up to 8hrs of battery life with ANC on
- MicroUSB charging cable included
- Convenient single 3.5mm audio jack connector

PART NO	DESCRIPTION
66706	Headset with Active Noise Cancelling & Noise Cancelling Boom Mic

Headset with Noise-Cancelling Boom Mic

- Noise Cancelling Mic reduces background noise
- Ideal for work, school & travel
- Gooseneck boom mic for flexible positioning
- Over-ear, cushioned ear pads for comfort
- Convenient single 3.5mm audio jack connector
- Easy to use scroll-wheel inline volume control
- Excellent bass & treble reproduction
- Wide frequency stereo output for gaming

PART NO	DESCRIPTION
66705	Headset with Noise Cancelling Boom Mic



HEADPHONES

Multimedia Headphones with Volume Control

- Contemporary, streamlined design: lightweight and portable
- Ideal for connecting to your laptop, tablet or music player
- In-line volume control
- Great bass and treble reproduction
- Soft foam ear cushions provide a comfortable and ergonomic fit, even for extended use

PART NO	DESCRIPTION
41645	Multimedia Headphones with Volume Control

On-Ear Kid's Headphones

- Volume-limiting headphones specifically recommended for children
- Restricted sensitivity of 85dB to protect little ears
- Adjustable, sturdy headband provides a secure fit for smaller heads
- Designed to allow ambient noise in so kids can be aware of their surroundings during active use
- Ideal for school and play

PART NO	DESCRIPTION
65530	On-Ear Kid's Headphones

EARBUDS

Earbud Headphones

- Lightweight and convenient for everyday use
- Enjoy stereo sound on the go
- Budget-friendly
- Compatible with devices that have a 3.5mm output jack, including mobile phones, tablets, audio devices and laptops

PART NO	DESCRIPTION
65062	Earbud Headphones




Redefine the way you sync and charge.

SYNC & CHARGE CABLES

Essentials Sync & Charge 3-in-1 Cable

- One cable, 3 connectors- interchange USB-C, Lightning and microUSB connectors
- 18W fast charging
- Up to 480 Mbps for transferring photos, videos, and files
- 1m length ideal for home, office and travel



PART NO	DESCRIPTION
---------	-------------

32394	Essential Sync & Charge Cable USB-C®/Lighting/microUSB to USB-A 100cm
-------	---

Sync & Charge 2-in-1 USB-C®/Lighting to USB-C® Cable

- 2-in-1, USB-C®/Lighting to USB-C® Cable
- Innovative slide mechanism
- Supports PD fast-charging up to 60W (PPS up to 25W)
- DuPont™ Kevlar® inside



PART NO	DESCRIPTION
---------	-------------


66974	Sync & Charge Cable USB-C®/Lighting to USB-C® 120cm
-------	---

C-TO-C CABLES

Sync & Charge USB4 Cables



- USB-C® to USB-C® USB4 Cable
- Supports PD 3.1 charging up to 240W
- Data transfer up to 40Gbps
- DuPont™ Kevlar® inside



PART NO	DESCRIPTION
31847	Sync & Charge Cable USB-C® to USB-C® USB4 240W 40Gbps 120cm
31849	Sync & Charge Cable USB-C® to USB-C® USB4 Display 240W 40Gbps 120cm

Sync & Charge Magnetic Cables



- USB-C® to USB-C® Cable
- Magnetic design keeps cables tidy and tangle-free
- High-Speed Data Transfer: Transfer files, photos, and videos in seconds with up to 480Mbps speed
- Supports PD charging up to 100W



Colours available:



PART NO	DESCRIPTION
31854	Sync & Charge Magnetic Cable USB-C® to USB-C® 100W 120cm Grey
31863	Sync & Charge Magnetic Cable USB-C® to USB-C® 100W 120cm Black

C-TO-A CABLES

Sync & Charge USB-C® to USB-A Cables

- USB-C® to USB-A Cable
- Supports 18W Quick Charge (QC 3.0)
- High-Speed Data Transfer: Transfer files, photos, and videos in seconds with up to 480Mbps speed
- DuPont™ Kevlar® inside




PART NO	DESCRIPTION
31843	Sync & Charge Cable USB-C® to USB-A 18W 120cm

Sync & Charge USB-C® to USB-C® Cables




- USB-C® to USB-C® Cable
- Supports PD charging up to 100W / 240W
- DuPont™ Kevlar® inside



PART NO	DESCRIPTION
31848	Sync & Charge Cable USB-C® to USB-C® 100W Power Display 120cm
66820	Sync & Charge Cable USB-C® to USB-C® 240W 120cm
66821	Sync & Charge Cable USB-C® to USB-C® 240W 200cm

Essential Sync & Charge USB-C® to USB-C® Cables

- USB-C® to USB-C® Cable
- up to 60W fast charging
- High-Speed Data Transfer: Transfer files, photos, and videos in seconds with up to 480Mbps speed
- 1m cable offers reach without clutter



PART NO	DESCRIPTION
32391	Essential Sync & Charge USB-C® to USB-C® Cable 100cm 2pk- Black & White

Essential Sync & Charge USB-C® to USB-A Cables

- USB-C® to USB-A® Cable
- up to 18W fast charging
- High-Speed Data Transfer: Transfer files, photos, and videos in seconds with up to 480Mbps speed
- 1m cable offers reach without clutter



PART NO	DESCRIPTION
32393	Essential Sync & Charge USB-C® to USB-A® Cable 100cm 2pk- Black & White

LIGHTNING CABLES

USB-C® to USB-A Cables


- Compatible with Type C devices
- Supports up to 3A current charging
- Supports QC 2.0 and 3.0
- Data transfer rate up to 480Mbps
- Material: PVC.



PART NO	DESCRIPTION
66584	Sync & Charge USB-C to A Cable 1m - White

Sync & Charge USB-C® to Lightning Cables


- USB-C® to Lightning Cable
- Apple MFi certified
- Supports 60W PD Fast charging
- High-Speed Data Transfer: Transfer files, photos, and videos in seconds with up to 480Mbps speed
- DuPont™ Kevlar® inside



PART NO	DESCRIPTION
31844	Sync & Charge Cable USB-C® to Lightning 60W 120cm

Lightning to USB-A Cables

- Durable, soft-touch rubber coating
- Apple MFi certification ensures quality and charge compatibility with applicable Apple devices.
- Compatible with iOS devices with Lightning connector
- 12W fast charging
- Data transfer rate up to 480Mbps




PART NO	DESCRIPTION
66581	Sync & Charge Lightning Cable 1m - White
31865	Sync & Charge Lightning Cable 1.5m - White

MICRO USB CABLES

USB-A to microUSB Cables

- Compatible with microUSB devices
- Supports up to 3A current charging
- Supports QC 2.0 and 3.0
- Data transfer rate up to 480Mbps
- Material: PVC.



PART NO	DESCRIPTION
66579	Sync & Charge USB-A to microUSB Cable 1m - White

Essential Sync & Charge USB-C® to Lightning Cables

- USB-C® to Lightning Cable
- up to 27W PD fast charging
- High-Speed Data Transfer: Transfer files, photos, and videos in seconds with up to 480Mbps speed
- 1m cable offers reach without clutter



PART NO	DESCRIPTION
32392	Essential Sync & Charge USB-C® to Lightning Cable 100cm 2pk- Black & White

HDMI Cable

- Supports 4K and Full HD 1080p – Crisp, clear visuals with high-resolution support.
- High-Speed Data Transfer – Ensures smooth video playback and low-latency performance.
- Gold-Plated Connectors – Enhances signal strength and prevents corrosion.
- Universal Compatibility – Works with TVs, monitors, gaming consoles, and streaming devices.



PART NO	DESCRIPTION
66577	HDMI Cable 100cm 1.4b - Black

PAIR THE RIGHT CABLE WITH YOUR DEVICE

When it comes to charging your devices or transferring data, the quality of your USB-C cable, charger, and digital device can make or break your experience. A mismatched setup can lead to slow charging, poor efficiency, and reduced data speeds.

THE IMPACT OF A POORLY MATCHED CABLE

If you've ever been frustrated by slow charging, it's likely that your charger and cable weren't working in sync. Here's what happens when they don't match:

Slow charging | Overheating and wear | Inefficient power delivery

If you're using an External SSD for video editing, gaming, or backups, your USB-C cable also plays a critical role in data speeds. A poorly matched cable can result in:

Slow file transfers | Reduced performance

THE RIGHT PAIRING: USB-C CABLES AND GAN CHARGERS

- For high-powered laptops and gaming setups, pair a 100W or 240W USB-C Cable with a 100W GaN Charger to ensure fast, efficient charging.
- For multi-device charging, go with a 100W or 65W GaN Charger. Pair it with several USB-C 100W Cables to ensure your devices are charging at optimal speeds.
- For reduced cable clutter and stress-free travel, try the 100W Magnetic USB-C to USB-C Cable. Its magnetic design allows the cable to coil neatly, making storage effortless.

THE BEST SETUP FOR MAXIMUM DATA TRANSFER SPEEDS

- Use a high-speed USB-C cable (such as the 240W USB-C to USB-C Cable) with a USB 3.2 Gen 2×2 external SSD (such as Verbatim's Metal Mini SSD) to achieve blazing-fast transfer speeds.
- Pair with a powerful 100W GaN charger to ensure uninterrupted power delivery for your laptop during data transfers.
- Future-proof your setup by choosing a USB4 Sync & Charge Cable to ensure compatibility with multiple devices for seamless backups and storage expansion.






MULTIPOINT HUBS



USB-C® Pro Multiport Hub - 5 Ports



- Transform a single USB-C port into five versatile ports to connect to a wide range of devices
- 1 x HDMI, 1 x RJ45, 2 x USB-A 3.2 Gen1, 1 x USB-C PD
- USB 3.2 Gen 1 technology ensures fast data transfer speeds
- HDMI interface supports up to 4K output video from your computer to a 4K monitor
- Provides USB-C power charging - easily charge your USB-C device whilst still using other ports



PART NO	DESCRIPTION
32150	USB-C® Pro Multiport Hub CMH-05 5 Ports HDMI RJ45 2 x USB-A USB-C PD



USB-C® Pro Multiport Hub - 8 Ports

- Transform a single USB-C port into eight ports including HDMI and SD card readers for comprehensive connectivity
- 2 x HDMI, 3 x USB-A 3.2 Gen1, 1 x SD card slot, 1 x microSD card slot, 1 x USB-C PD
- Dual HDMI output enables connection to multiple monitors for an expanded workspace
- USB 3.2 Gen1 technology ensures fast data transfer speeds
- Integrated SD and microSD memory card slots
- Provides USB-C power charging - easily charge your USB-C device whilst still using other ports



PART NO	DESCRIPTION
32151	USB-C® Pro Multiport Hub CMH-08 8 Ports 2 x HDMI 3 x USB-A SD microSD USB-C PD




USB-C® Pro Multiport Hub - 9 Ports

- Transform a single USB-C port into nine ports including USB-C and USB-A with different generations for maximum device compatibility
- 1 x HDMI, 1 x RJ45, 2 x USB-C 3.2 Gen2, 1 x USB-A 3.2 Gen2, 2 x USB-A 3.2 Gen1, 1 x SD card slot, 1 x microSD card slot
- 4K resolution HDMI video supported
- Benefit from a stable, wired network connection with the gigabit ethernet port
- USB 3.2 Gen 2 technology ensures fast data transfer speeds
- Integrated SD and microSD memory card slots



PART NO	DESCRIPTION
32152	USB-C® Pro Multiport Hub CMH-09 9 Ports HDMI RJ45 2 x USB-C USB-A 3.2 Gen2 2 x USB-A 3.2 Gen1 SD microSD





USB-C® Pro Multiport Hub - 13 Ports

- Transform a single USB-C port into thirteen ports including dual HDMI, High speed PD ports and gigabit ethernet connection
- 2 x HDMI, 1 x DisplayPort, 1 x RJ45, 3 x USB-A 3.2 Gen1, 1 x USB-A 3.2 Gen 2, 2 x USB-A 2.0, 1 x Audio, 2 x USB-C PD
- Triple 4K video output
- Dual HDMI outputs capable of handling up to 8K resolution for stunning visuals
- Gigabit ethernet port for high speed, wired internet access
- Dual USB-C Power Delivery - charge devices while using the hub with pass-through charging



PART NO DESCRIPTION

32153	USB-C® Pro Multiport Hub CMH-13 13 Ports 2 x HDMI DP RJ45 USB-A 3.2 Gen2 3 x USB-A 3.2 Gen1 2 x USB-A 2.0 Audio 2 x USB-C PD
-------	---



USB-C® Pro Multiport Hub - 14 Ports

- Transform a single USB-C port into fourteen ports including dual HDMI, VGA, and gigabit ethernet connection
- 2 x HDMI, 1 x VGA, 1 x RJ45, 3 x USB-A 3.2 Gen1, 1 x USB-C 3.2 Gen1, 2 x USB-A 2.0, 1 x SD card slot, 1 x microSD card slot, 1 x Audio jack, 1 x USB-C PD
- Triple 1080p video output
- Dual 4K HDMI display support
- VGA socket for legacy monitor support
- Equipped with a combination of USB-A and USB-C ports for connecting multiple devices
- Integrated SD and microSD memory card slots
- Gigabit ethernet port for high speed, wired internet access
- Dual USB-C Power Delivery - charge devices while using the hub with pass-through charging



PART NO DESCRIPTION


32154	USB-C® Pro Multiport Hub CMH-14 14 Ports 2 x HDMI VGA RJ45 3 x USB-A 3.2 Gen1 USB-C 3.2 Gen1 2 x USB-A 2.0 SD microSD Audio Jack USB-C PD
-------	--



CARD READERS

USB-C® Multiport Hubs

- USB-C multi-port hub
- USB 3.2 Gen 1 Type-A ports support up to 5Gbps* data transfer
- USB-A 2.0 ports support up to 480Mbps data transfer
- USB-C 3.2 Gen 1 ports support up to 5Gbps* data transfer
- USB-C connection



PART NO	DESCRIPTION
65679	USB-C® Multiport Hub 3 x USB 3.1 Gen 1 SD microSD
66602	USB-C® Multiport Hub 4 x USB 3.2 Gen 1
66603	USB-C® Multiport Hub 2 x USB 3.2 Gen 1 USB-C 3.2 Gen 1 USB 2.0 SD microSD



USB 3.2 Gen 1 Card Reader

- Works with a wide array of memory cards, including SD, microSD, CF-I, Memory Stick, MS-Pro Duo, xD, and M2
- USB 3.2 Gen 1 technology - blazing-fast transfer speeds that save you time when moving files between devices
- Compact and lightweight - easily fits in your pocket or laptop bag
- 65678 includes integrated USB-A Cable
- 65678 includes integrated USB-A Cable

PART NO	DESCRIPTION
65678	USB 3.2 Gen 1 Card Reader SD/MMC microSD CF M2 xD MS/MS PRO Duo
64901	USB 3.2 Gen 1 Card Reader SD/MMC microSD CF M2 MS/MS PRO



USB 2.0 Card Reader

- Works with a wide array of memory cards, including SD, microSD, CF-I, Memory Stick, MS-Pro Duo, and more
- USB 2.0
- Compact and lightweight - easily fits in your pocket or laptop bag
- 65677 includes integrated USB-A Cable
- 65676 equipped with 3 USB-A ports, allowing you to connect multiple devices or peripherals

PART NO	DESCRIPTION
65677	USB 2.0 Card Reader SD/MMC microSD CF M2 xD MS/MS PRO Duo
65676	USB 2.0 Card Reader / Hub SD/MMC microSD CF MS/MS PRO Duo





SHARE MY SCREEN



- USB-C® Wireless Display Adapter with Hub
- Enjoy crisp, clear 4K resolution for presentations, streaming and gaming without the clutter of cables
- Mirror your display wirelessly from your USB-C device to your monitor, TV or projector
- Simple and user-friendly pairing process for a quick and secure connection
- USB-C connection transmitter and HDMI connection receiver*
- Reliable 10 meter wireless range
- Compact and portable design ideal for professionals and students on the go

PART NO	DESCRIPTION
---------	-------------

32147	Share My Screen USB-C® Wireless Display Adapter 4K with Hub WDA-02
-------	--



* Receiver requires HDMI connection - HDMI cable not included.

WIRELESS PRESENTER

Agenda Wireless Presenter

- Dual USB-A & USB-C Receiver: Seamlessly connects to Mac, PC, and Android devices for universal compatibility
- Projects a sharp, clear laser up to 100 meters, perfect for large rooms
- Easily navigate slides, toggle full/black screen, and scroll pages with responsive buttons
- No drivers or setup required – just plug in and present instantly
- Built-in rechargeable battery with USB-C charging eliminates the need for disposable batteries
- Premium aluminum alloy with frosted texture and magnetic dongle storage

PART NO	DESCRIPTION
---------	-------------

32366	Agenda Wireless Presenter
-------	---------------------------



GaN CHARGERS



Tired of lugging multiple bulky chargers around to recharge your array of power-hungry digital devices? Or looking to purchase a single charger that can fast-charge multiple devices simultaneously? Then you should consider a Verbatim GaN charger.

Featuring a compact size and increased power output enabling you to fast charge multiple devices simultaneously, our GaN chargers are compatible with the latest digital devices and come with a host of features that make them the ultimate charging solution.

Verbatim's GaN Charger range feature housing constructed from 95% Post Consumer Recycled plastic. This recycling process reduces the need for virgin plastic production and diverts plastic waste from landfill and oceans, contributing to a more sustainable and eco-friendly approach to plastic use.



35W 2-Port GaN Wall Charger

- Supports charging of up to 2 devices simultaneously
- 1x USB-C® PD 3.0 35W, and 1x USB-A QC 3.0
- Supports super-fast charging with USB Power Delivery 3.0, PPS and Quick Charge 3.0
- Made with high-quality, flame-resistant materials
- 95% Recycled Plastic Housing

PART NO	DESCRIPTION
---------	-------------

67015	35W 2-Port GaN Wall Charger 1x USB-C® PD 35W / 1x USB-A QC 3.0
-------	---

65W 3-Port GaN Wall Charger

- Supports charging of up to 3 devices simultaneously
- 2 x USB-C® PD 3.0 65W, and 1x USB-A QC 3.0
- Supports super-fast charging with USB Power Delivery 3.0, PPS and Quick Charge 3.0
- Made with high-quality, flame-resistant materials
- 95% Recycled Plastic Housing

PART NO	DESCRIPTION
---------	-------------

67016	65W 3-Port GaN Wall Charger 2 x USB-C® PD 65W / 1x USB-A QC 3.0
-------	--

100W 4-Port GaN Wall Charger

- Supports charging of up to 4 devices simultaneously
- 2 x USB-C® PD 3.0 100W, 1x USB-C PD 3.0 65W, and 1x USB-A QC 3.0
- Supports super-fast charging with USB Power Delivery 3.0, PPS and Quick Charge 3.0
- Made with high-quality, flame-resistant materials
- 95% Recycled Plastic Housing

PART NO	DESCRIPTION
---------	-------------

66966	100W 4-Port GaN Wall Charger 2 x USB-C® PD 100W / 1x USB-C® PD 65W / 1x USB-A QC 3.0
-------	---

140W 4-Port GaN Wall Charger

- Supports charging of up to 4 devices simultaneously
- 2 x USB-C® PD 3.0 140W, 1x USB-C PD 3.0 20W, and 1x USB-A QC 3.0 18W
- Supports super-fast charging with USB Power Delivery 3.0, PPS and Quick Charge 3.0
- Made with high-quality, flame-resistant materials
- 95% Recycled Plastic Housing

PART NO	DESCRIPTION
---------	-------------

67035	140W 4-Port GaN Wall Charger 2 x USB-C® PD 140W / 1x USB-C® PD 20W / 1x USB-A QC 3.0
-------	---



CAR CHARGERS



WIRELESS CHARGERS

USB WALL CHARGERS

Charge 'n' Drive Qi2 Magnetic Wireless Car Charger

- Qi2 technology: charges iPhone 16/15/14/13/12 and Qi2-compatible Android devices
- Cooling system prevents overheating
- Secure magnetic hold with built-in 16 NdFeB magnets
- Flexible mounting options with 360° rotation
- Designed to accommodate phones with larger camera lens areas



3-in-1 Wireless Docking

- Wirelessly charge your phone, watch and earbuds simultaneously
- Up to 15W wireless charging for smart phones; Up to 5W wireless charging for earbuds; Up to 2.5W charging for smart watches.
- Retractable charging pad offers flexibility to fit various smartphone sizes
- Qi2 fast charging for compatible devices
- Magnetic dock ensures perfect charging position for phones
- Foldable, compact design ideal for easy transporting and travel

AC Chargers

- Compliant with Australia/New Zealand Electrical Safety Standards
- USB-A port supports 2.4A charging
- Smart IC - enhanced with a smart charging feature that detects the specifications of your connected device and supplies the best corresponding current

PART NO DESCRIPTION

31861	Charge 'n' Drive Qi2 Magnetic Wireless Car Charger
-------	--

PART NO DESCRIPTION

67036	3-in-1 Wireless Docking (Black Titanium)
67038	3-in-1 Wireless Docking (Black Desert)

PART NO DESCRIPTION

66590	USB Charger Single Port 2.4A
-------	------------------------------

2-Port Mini Car Charger

- Charge up to 2 devices simultaneously in your car
- Equipped with 1 x USB-C PD 3.0 and 1 x USB-A QC 3.0 port
- Each port supports up to 30W when being used alone.
- Total maximum output is 24W (when 2 devices connected)
- Connects to car's lighter port and sits flush when connected
- Includes a fold-away swivel handle to easily remove from lighter socket



PART NO DESCRIPTION

66681	2 Port 33W PD & QC Mini Car Charger
-------	-------------------------------------



POWER BANKS

Charge 'n' Go Essentials Power Bank Magnetic Wireless

- 15W magnetic wireless charging and 35W USB-C PD fast charging via USB-C port
- 5,000 & 10,000mAh capacities to keep your devices powered through travel, events, or outdoor adventures
- Charge 2 devices simultaneously
- Includes a USB-C to USB-C cable and a magnetic metal ring



PART NO DESCRIPTION

32225	Charge 'n' Go Essentials Power Bank Magnetic Wireless 5000mAh Black
32227	Charge 'n' Go Essentials Power Bank Magnetic Wireless 10000mAh Black

Charge'n'Go Power Bank with Stand

- 10,000mAh capacity - ample power for smartphones and more
- Integrated stand for hands-free viewing
- 15W magnetic wireless charging and 20W USB-C PD fast charging
- MagSafe compatible
- Bi-directional USB-C Port for charging in & out through a single port
- 6 essential protection systems for safer charging
- LED indicates how much power remains



PART NO DESCRIPTION

32264	Charge'n'Go Power Bank Magnetic Wireless with Stand 10,000 mAh Black
-------	--

Charge 'n' Go Power Bank with 2 Cables & Display

- 10,000mAh battery capacity for reliable, portable power on the go
- Charge up to four devices simultaneously (wired + wireless)
- Magnetic wireless charging: 15W for phones*, 5W for AirPods™, 2.5W for Apple Watch™
- 2 embedded USB-C® cables: C2 (22.5W max) and C3 (12W max)
- USB-C PD fast charging up to 22.5W
- MagSafe-compatible
- Built-in stand for hands-free viewing
- TFT display shows battery percentage and real-time charging status



PART NO DESCRIPTION

32272	Charge 'n' Go Power Bank with 2 integrated cables and display
-------	---

Charge 'n' Go 3-in-1 Foldable Power Bank

- 5,000mAh and 10,000mAh battery capacity options
- Charge up to 4 devices simultaneously (wired + wireless)
- Magnetic wireless charging: 15W for phones*, 3W for AirPods™, 2.5W for Apple Watch™
- USB-C PD fast charging up to 20W
- Foldable design for travel
- LED charging display



PART NO DESCRIPTION

32294	Charge 'n' Go 3-in-1 Foldable Power Bank 5,000mAh
32295	Charge 'n' Go 3-in-1 Foldable Power Bank 10,000mAh



LITHIUM-POLYMER VS LITHIUM-ION: WHY VERBATIM CHOOSES THE SAFER BATTERY TECHNOLOGY

We all rely on portable power to stay connected, whether that's charging your phone on the go, powering up your tablet for study, or keeping your earbuds ready for a commute. But have you ever stopped to think about what's inside your power bank?

Most power banks use either Lithium-Ion (Li-Ion) or Lithium-Polymer (Li-Po) batteries. And while both are rechargeable lithium-based technologies, there are some key differences in safety, design, and performance that make Verbatim's Lithium-Polymer choice the smarter, safer option.

WHY LITHIUM-POLYMER IS THE SAFER CHOICE

Safety is the biggest advantage of Lithium-Polymer technology. Here's why:

- Reduced risk of overheating or swelling: Li-Po batteries use a stable polymer electrolyte, meaning less chance of chemical leakage or thermal runaway.
- No liquid electrolyte: unlike Li-Ion, Li-Po batteries don't contain flammable liquids, lowering the risk of explosion or fire.
- Built-in protection circuitry: all Verbatim power banks include safeguards against overcharging, overcurrent, and short-circuiting.

Whether it's in your backpack, car, or classroom, Verbatim's Lithium-Polymer power banks are designed for peace of mind every time you charge.

SLIMMER, LIGHTER, AND SMARTER DESIGN



Because Lithium-Polymer cells are flexible and lightweight, they can be moulded into thinner shapes. That's why Verbatim's Charge'n'Go Power Banks are compact enough to slip easily into a pocket or handbag without adding extra bulk. This makes them ideal for:

- Students and teachers who need reliable power on the go
- Commuters and travellers packing light
- Professionals juggling multiple devices throughout the day

LONGER LIFESPAN AND CONSISTENT PERFORMANCE

Over time, all rechargeable batteries experience wear, but Lithium-Polymer cells degrade more slowly than traditional Lithium-Ion cells. They deliver consistent output across hundreds of charge cycles, meaning you'll enjoy longer-lasting performance and better overall value.

Verbatim has been powering everyday technology for decades. Every Charge'n'Go Power Bank is built with premium Lithium-Polymer cells, and intelligent protection circuits against overcharging and/or discharging, over current, short circuits and overheating. When it comes to safety and reliability, Verbatim simply doesn't compromise. Because life works better with Verbatim, no matter where you are or what you're doing. So, whether you're charging your smartphone, tablet, or wireless headphones, you can trust Verbatim to deliver reliable power every time.



MY FINDER DUAL

My Finder Dual Wireless

- Works with Apple Find My & Google Find Hub (Can only be actively paired with one device at a time.)
- Rechargeable battery – up to 3 months per charge
- Qi wireless charging – no disposable batteries (wireless charger not included)
- IP64 water & dust resistant for everyday durability
- Built-in buzzer to help locate items nearby
- NFC contact sharing if your item is found
- Compact design with integrated keyring hole
- No personal data stored on the device

PART NO	DESCRIPTION
30167	My Finder Dual Wireless - 1 pk
30210	My Finder Dual Wireless - 3 pk



My Finder Dual TSA Lock

- Works with Apple Find My & Google Find Hub (Can only be actively paired with one device at a time.)
- TSA-approved Travel Sentry® lock
- Accepted in 75+ countries and 750+ airports
- Rechargeable battery – up to 120 days per charge
- Secure 3-digit combination lock
- USB-C rechargeable – no batteries required
- Durable ABS body with braided stainless steel cable
- Designed for suitcases, backpacks and travel cases

PART NO	DESCRIPTION
30169	My Finder Dual TSA Lock





MY FINDER

My Finder Bluetooth Trackers

- Track personal items
- Works with Apple's Find My app
- Equipped with play prompt sound to assist in locating items in close range
- IP66 protection for water-resistance and dustproof durability
- NFC technology allows you to send your contact details to person who finds your lost device
- Up to 12 months battery power

PART NO	DESCRIPTION
66840	My Finder Bluetooth Tracker - Black



My Finder Card



- Track personal items
- Works with Apple's Find My app
- Discreet slimline design- ideal for wallets, passport folders and bag-tags
- Magnetic Wireless Charging- no need to replace batteries
- Up to 6 months usage between charging
- IP66 Protection provides water-resistance and dustproof durability

Colours available:



PART NO	DESCRIPTION
32138	My Finder Card Bluetooth Tracker - Black
32140	My Finder Card Bluetooth Tracker - 2 pack Black/Silver



BACKING-UP AND ARCHIVING



BACKING-UP AND ARCHIVING

REGULAR BACK-UPS protect against both accidental or malicious data loss – anything from hardware faults and viruses to human error or theft – as they can be used to restore original data files.

Choosing the right media and back-up procedure depends on many elements:

- The amount of data being saved
- The perceived value of the data
- The levels of accepted risk
- The length of time you need to keep the data for

3-2-1 BACKUP RULE

Have at least
Three copies of
your data



In addition to your primary data you should also have at least two more backups, which will significantly help reduce the risk of losing data. These could be physical and / or cloud solutions.

Store the copies on
at least two
different Types
of media



It is best practice to keep copies of your data on at least two different storage types, such as internal disk drives AND removable storage media (tapes, external hard drives, USB drives, SD-cards, CD's, DVDs).

Keep at least one
offsite backup
copy



It's obvious really; but it's not a good idea to keep your external storage device in the same room as your production storage.

If there is a fire, flood or burglary - you would lose all of your data.

BEST PROTECTION AGAINST ATTACK

ARCHIVE YOUR DATA

To be completely protected, a user or organisation needs to have data backed up and archived offline.

Any device that is attached to an attacked system or network is vulnerable. If your back up HDD is plugged into your laptop when a piece of ransomware software is installed, it will also be encrypted.

Having the most important data archived to optical media can eliminate this risk.



DVD & CD WRITERS

Optical Discs are the most reliable media to archive your data on. Unfortunately more and more notebook vendors choose to leave the optical drive out of their notebooks in favour of slim designs. Verbatim has the solution with its range of external DVD/CD writers. Use them to create a back-up of all the important files that you don't want to lose - family pictures, videos, accounting documents etc. Compatible with DVDs and CDs.



External Slimline CD/DVD Writer

- USB 2.0 connection
- Store up to 8.5GB on a Double Layer DVD, up to 4.7GB on a standard DVD
- Compact and lightweight, ideally suited for use with a notebook or ultrabook
- Power provided by the USB port - no need to carry a bulky adapter
- Includes USB-A to Mini-B cable
- Includes Nero Burn & Archive Software*
- Fully compliant with MDISC™ archiving technology

PART NUMBER	DESCRIPTION
98938	External Slimline CD/DVD Writer

* Nero Burn & Archive is only suitable for Windows OS

** Playback software not included. To be purchased or downloaded separately


nero
Burn&Archive

Verbatim CD/DVD Writers include Nero Burn & Archive Software:

- CD, DVD burning software for all your videos, photos and precious documents.
- DiscSpan and SmartFit helps you to organise oversized files and archives among many discs - no need to split up files.
- SecurDisc Technology allows password protection to be added for extra security, and an electronic signature so that everyone knows you own the copyright.
- Nero MediaHome Standard brings all your media files together into a single location to help you easily organise and access all your photos, music, and videos. It helps you to burn the right playlist for any occasion; rip or copy your favourite CD; use different filters for the perfect photo; or put together slide shows - including photos, videos, and even film music in the background.
- Burn music videos directly onto audio CDs.
- Convert your audio CDs into the format of your choice - MP3, AAC, FLAC, or APE.
- Various streaming options, including the Nero Streaming Player App, allows you to show your movies, photos, slide shows, and other media files on various devices such as smartphones, tablets and Smart TVs.
- Relevant song titles, band names, and other details are automatically included.



LIFETIME OF DATA STORAGE FORMATS



Optical media has the advantage that it is the ideal storage media designed for long term archival if it is stored in the right conditions. Whilst hard drives and flash memory products are great for storing and moving large volumes of data, they don't have the same long-term reliability that should be considered for keeping data for five years or more.

What's more, optical media is improving all the time, in both reliability and capacity, making it perfect for cold data storage. Verbatim's current top-of-the-range Blu-ray BD-XL discs each store up to 100GB and will last hundreds of years without degradation. In fact, industry standard ISO/IEC 10995 tests gave them a mean lifetime of 1,332 years, with just 5% of discs showing signs of data loss after 667 years. Not only is it the cheapest (portable) storage medium on the market, there is no fear for the optical disc to be hacked or catch a virus due to its offline nature - making it safe and secure to archive important files and documents.

USB DRIVES

With a wide range of award-winning designs and features, Verbatim's selection of USB drives are perfect for storing and sharing data – safely and securely. The drives include features to satisfy everyone's needs including sliding mechanisms that protect the connector, metal enclosures, and USB-C and USB-A form factors.



UNDERSTANDING THE USB STANDARDS

WHAT'S THE DIFFERENCE BETWEEN USB 3.2 GEN 1, USB 3.1 GEN1 AND USB 3.0?

In essence, they are exactly the same.

With the introduction of faster USB speeds, the USB Implementers Forum (the trade group that defines USB standards) was required to reclassify some USB terms.



Maybe the easiest way to show this new naming structure is in this table:

Original name	First re-name	New Current name	Max speed
USB 3.0	USB 3.1 Gen 1	USB 3.2 Gen 1	5Gbps
USB 3.1	USB 3.1 Gen 2	USB 3.2 Gen 2	10Gbps
USB 3.2	n/a	USB 3.2 Gen 2x2	20Gbps

It's helpful to note that USB 3.2 devices are backwards compatible with all existing USB products, meaning that the newer USB products will work with older devices. The only difference is the throughput; two products with different USB capabilities will operate at the lower transfer speed.

TYPE A VS. C

In addition to offering different speeds, USB comes in different physical forms. The common USB Type-A ports are rectangular and require you to plug in your cable with the right side up. The newer USB Type-C® ports are smaller, oval-shaped and reversible in that they save you from needing to know which end is up.



USB-C®

Dual QuickStick USB



- USB Drive with SSD performance
- USB-A / USB-C® connection
- High performance transfer rates of up to 550MB/s
- USB 3.2 Gen 1 performance
- Tough metal design



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)*
32040	Dual QuickStick USB USB-C® & USB-A 128 GB	510 MB/sec	460 MB/sec
32041	Dual QuickStick USB USB-C® & USB-A 256 GB	530 MB/sec	470 MB/sec
32042	Dual QuickStick USB USB-C® & USB-A 512 GB	550 MB/sec	500 MB/sec
32043	Dual QuickStick USB USB-C® & USB-A 1 TB	550 MB/sec	500 MB/sec

Plectra USB-C® Flash Drive



- USB-C® interface
- High transfer speed of up to 100MB/s
- USB 3.2 Gen 1 performance
- Modern, compact and lightweight design
- Three colour options (blue & white available on request)



Colours available:




PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
30224	Plectra USB Flash Drive 64GB Black	100 MB/sec	25 MB/sec
30225	Plectra USB Flash Drive 128GB Black	100 MB/sec	25 MB/sec
30226	Plectra USB Flash Drive 256GB Black	100 MB/sec	25 MB/sec
30227	Plectra USB Flash Drive 512GB Black	100 MB/sec	25 MB/sec

USB-C® 3.2 Gen 1 Drive

- Store and transfer data between USB-C compatible devices
- Retractable USB-C connector
- Transfer speed of up to 100MB/s
- USB 3.2 Gen 1 performance



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
70903	Store 'n' Go USB-C® 3.2 Gen 1 Drive 32GB	100 MB/sec	25 MB/sec
70904	Store 'n' Go USB-C® 3.2 Gen 1 Drive 64GB	100 MB/sec	25 MB/sec
70905	Store 'n' Go USB-C® 3.2 Gen 1 Drive 128GB	100 MB/sec	25 MB/sec



USB-C® 3.1 Gen 1 Smartphone & Tablet Dual Drive

- Dual Head design – share data between devices with Type-C and USB 3.0/2.0 ports
- Ultra compact design with sturdy metal housing



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
65744	Store 'n' Go USB-C® 3.1 Dual Drive 32GB	110 MB/sec	20 MB/sec
65745	Store 'n' Go USB-C® 3.1 Dual Drive 64GB	110 MB/sec	20 MB/sec

USB 3.2 GEN 1

Store 'n' Go V3 MAX USB 3.2 Gen 1 Drive

- High performance USB 3.2 Gen 1 drive
- Up to 300MB/sec transfer speed
- Sliding mechanism protects the USB connector when not in use
- Smooth, highly polished finish



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
49807	Store 'n' Go V3 MAX 64GB	300 MB/sec	70 MB/sec
49808	Store 'n' Go V3 MAX 128GB	300 MB/sec	70 MB/sec
49809	Store 'n' Go V3 MAX 256GB	300 MB/sec	70 MB/sec

Store 'n' Go V3 USB 3.2 Gen 1 Drive

- USB 3.2 Gen 1 SuperSpeed interface
- 'Slide and Lock' mechanism protects the USB connector when not in use
- Compact, stylish design



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
49172	Store 'n' Go V3 USB Drive 16GB Black	60 MB/sec	12 MB/sec
49173	Store 'n' Go V3 USB Drive 32GB Black	80 MB/sec	25 MB/sec
49174	Store 'n' Go V3 USB Drive 64GB Black	80 MB/sec	25 MB/sec
49189	Store 'n' Go V3 USB Drive 128GB Black	80 MB/sec	25 MB/sec
49168	Store 'n' Go V3 USB Drive 256GB Black	120 MB/sec	25 MB/sec

PinStripe USB 3.2 Gen 1 Drive

- Our flagship USB drive
- High speed USB 3.2 Gen 1 interface
- Lightweight, striped design
- Push and pull sliding mechanism




PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
49316	PinStripe USB 3.2 Gen 1 Drive 16GB Black	30 MB/sec	10 MB/sec
49317	PinStripe USB 3.2 Gen 1 Drive 32GB Black	30 MB/sec	10 MB/sec
49318	PinStripe USB 3.2 Gen 1 Drive 64GB Black	30 MB/sec	10 MB/sec
49319	PinStripe USB 3.2 Gen 1 Drive 128GB Black	30 MB/sec	10 MB/sec

Store 'n' Go V3 USB 3.2 Gen 1 Drive - Colours

- USB 3.2 Gen 1 SuperSpeed interface
- 'Slide and Lock' mechanism protects the USB connector when not in use
- Colour options for easy recognition



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
65265	Store 'n' Go V3 USB Drive 32GB Purple	80 MB/sec	25 MB/sec
65266	Store 'n' Go V3 USB Drive 64GB Eucalyptus Green	80 MB/sec	25 MB/sec
66316	Store 'n' Go V3 USB Drive 256GB Red	120 MB/sec	25 MB/sec
66315	Store 'n' Go V3 USB Drive 512GB Orange	120 MB/sec	25 MB/sec



 **2,250kg**
Crush resistant

 **30 meters**
Water resistant

 **-25°C / +150°C**
Temperature resistant



ToughMAX USB Drive



- Made using KyronMAX™* metal replacement material with a tensile strength ratio that is higher than steel
- Able to withstand seriously punishing conditions and used in the most demanding of applications from fighter jets to mountain bikes
- Resistant to:
 - o Crush forces up to 2,250kg**
 - o Water immersion to 30m depth**
 - o Extreme temperatures from -25°C to 150°C*
- USB 3.2 Gen 1
- Slim stylish design

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
66057	ToughMAX USB 3.2 Gen 1 Drive 32GB	30 MB/sec	10 MB/sec
66058	ToughMAX USB 3.2 Gen 1 Drive 64GB	30 MB/sec	10 MB/sec
66333	ToughMAX USB 3.2 Gen 1 Drive 128GB	30 MB/sec	10 MB/sec

* KyronMAX™ compounds are manufactured by Piper Plastics
** Based on 3rd party testing by SGS. Actual performance may vary.



USB 2.0

Store 'n' Go PinStripe USB 2.0 Drive

- Push and pull sliding feature
- Lightweight, striped design
- USB 2.0 interface




PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
49063	Store 'n' Go PinStripe USB Drive 16GB	8 MB/sec	2.5 MB/sec
49064	Store 'n' Go PinStripe USB Drive 32GB	12 MB/sec	5 MB/sec
49065	Store 'n' Go PinStripe USB Drive 64GB	12 MB/sec	5 MB/sec
49071	Store 'n' Go PinStripe USB Drive 128GB	12 MB/sec	5 MB/sec
49320	Store 'n' Go PinStripe USB Drive 256GB	12 MB/sec	5 MB/sec

Pop-up USB Drive

- Push and pull retractable USB
- Lightweight, coloured design
- Securely attach to a lanyard or keyring
- 3 pack in pastel or bright colour options
- 5 pack in assorted colour selection

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
66760	Pop-up USB Drive 32GB Triple Pack - Pastels	12 MB/sec	5 MB/sec
66761	Pop-up USB Drive 32GB Triple Pack - Brights	12 MB/sec	5 MB/sec
67030	Pop-up USB Drive 32GB Five Pack - Assorted	12 MB/sec	5 MB/sec



MEMORY CARDS

Verbatim's Premium, Pro, and Pro+ Range SD and microSD cards provide the perfect balance of speed, reliability, and durability, ensuring your data is secure no matter where your creativity or work takes you.



SD CARDS

Premium

- Perfect choice for everyday storage in cameras, laptops, and other digital devices
- Ideal for capturing high-resolution photos and Full HD videos
- Read Speed: Up to 80MB/s (90MB/s for 256GB model)
- Write Speed: Up to 10MB/s
- Video Speed Class: V10
- Speed Rating: UHS-I (U1)

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
SD Cards			
43962	SDHC 16GB C10/U1	80	10
43963	SDHC 32GB C10/U1	80	10
44024	SDXC 64GB C10/U1	80	10
44025	SDXC 128GB C10/U1	80	10
99828	SDXC 256GB C10/U1	90	10

Pro


- Superior speed and durability for professional photographers, videographers, and content creators
- Engineered for high-resolution photography and 4K video recording
- Read Speed: Up to 90MB/s
- Write Speed: Up to 45MB/s
- Video Speed Class: V30
- Speed Rating: UHS-3 (U3)

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
SD Cards			
47021	Pro SDHC 32GB C10/U3	90	45
47022	Pro SDXC 64GB C10/U3	90	45
47023	SDXC 128GB C10/U3	90	45

Pro +

- Designed for advanced users and professionals who demand the highest level of speed and endurance
- Perfect fit for use in high-performance cameras, cinema-grade video gear, and other professional-grade equipment.
- Read Speed: Up to 100MB/s
- Write Speed: Up to 80MB/s
- Video Speed Class: V30
- Speed Rating: UHS-I (U3)
- Application Performance: A1 (64GB), A2 (128GB), A3 (256GB)

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
SD Cards			
49197	Pro+ SDXC 64GB C10 U3 A1	100	80
49198	Pro+ SDXC 128GB C10 U3 A2	100	80
99141	Pro+ SDXC 256GB C10 U3 A3	100	80



MICRO SD CARDS

Premium

- Designed for smartphones, tablets, action cameras, and other mobile devices
- Perfect for mobile users, drone enthusiasts, and security camera setups
- Read Speed: Up to 90MB/s
- Write Speed: Up to 10MB/s
- Video Speed Class: V10
- Speed Rating: UHS-I (U1)

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
MicroSD Cards with Adaptor			
44082	Micro SDHC 16GB C10/U1 with adapter	90	10
44083	Micro SDHC 32GB C10/U1 with adapter	90	10
44084	Micro SDXC 64GB C10/U1 with adapter	90	10
44085	Micro SDXC 128GB C10/U1 with adapter	90	10
44087	Micro SDXC 256GB C10/U1 with adapter	90	10

Pro

- Designed for action cameras, drones, gaming consoles, and high-end mobile devices
- Lightning-fast data transfer speeds for seamless performance in demanding applications
- Read Speed: Up to 90MB/s
- Write Speed: Up to 45MB/s
- Video Speed Class: V30
- Speed Rating: UHS-3 (U3)

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
Micro SD Cards with Adapter			
47041	Pro microSDHC 32GB C10/U3 with adapter	90	45
47042	Pro microSDXC 64GB C10/U3 with adapter	90	45
47044	Pro microSDXC 128GB C10/U3 with adapter	90	45
47045	Pro microSDXC 256GB C10/U3 with adapter	100	90
47046	Pro microSDXC 512GB C10/U3 with adapter	100	90

Pro +

- Designed for 4K video recording, high-speed burst photography, gaming, and app-intensive mobile devices
- Perfect for use in professional cameras, drones, action cams, and mobile gaming devices
- Read Speed: Up to 100MB/s
- Write Speed: Up to 80MB/s or 60MB/s (512GB)
- Video Speed Class: V30
- Speed Rating: UHS-I (U3)
- Application Performance: A1 (64GB), A2 (128GB/512GB), A3 (256GB)

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
SD Cards			
70002	Pro+ microSDXC 64GB C10 U3 A1	100	80
30236	Pro+ microSDXC 128GB C10 U3 A2	100	80
30237	Pro+ microSDXC 256GB C10 U3 A3	100	80
70393	Pro+ microSDXC 512GB C10 U3 A2	100	60





EXTERNAL SSD

Still using a portable hard drive? Upgrade to an external SSD from Verbatim and experience lightning-fast performance, longer lifespan, and automatic backup options. Our External SSD range is designed to fit your lifestyle, whether you're working, creating, studying or travelling. Because life works better with Verbatim.





OVERVIEW

External solid state drives (SSDs) have quickly become the go-to solution for modern data storage, offering significantly faster performance, greater reliability, and improved durability compared to traditional external hard drives. Whether you're backing up precious memories, transferring large creative files, or carrying work on the go, SSDs provide a smarter way to store, move and protect your data.


Unlike traditional hard drives with moving parts, SSDs use flash memory, which allows them to read and write data at lightning speeds. This makes them ideal for tasks like editing 4K video, running applications from the drive, or transferring high-resolution files in seconds. They're also more shock-resistant and energy-efficient, making them perfect for life on the move.

At Verbatim, we offer a wide range of external SSDs to suit every lifestyle and budget—from compact everyday drives to professional-grade high-performance models.

No matter where you are or what you're doing, Verbatim SSDs have always got you covered.

TOP 10 BENEFITS OF EXTERNAL SSDS

1. **Faster Data Transfer:** Save time with high-speed file transfers.
2. **More Durable:** No moving parts means better resistance to shocks and drops.
3. **Slim & Lightweight:** Easily fits in your pocket, bag or laptop case.
4. **Quieter Operation:** Completely silent - no spinning disks or humming.
5. **Energy Efficient:** Draws less power, helping battery life on laptops.
6. **Better Longevity:** Designed to handle more read/write cycles than HDDs.
7. **Improved Security:** Many models support encryption and secure backup.
8. **More Reliable:** Less prone to mechanical failure than traditional hard drives.
9. **Cross-Platform Compatibility:** Works seamlessly across Windows, macOS and more.
10. **Versatile Use Cases:** Ideal for everything from basic backups to demanding professional tasks.





EXTERNAL SSD

Pocket SSD



- Pocket-sized SSD - fits in your back pocket
- Data transfer speeds of up to 1000MB/s
- USB-C® connection with USB 3.2 Gen 2 interface
- Convenient keyring and cable holder
- Compact, rugged and perfect for travel

Colours available:

PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
32190	Pocket SSD 1TB Black/Grey	1000 MB/sec	1000 MB/sec
32192	Pocket SSD 1TB Black/Red	1000 MB/sec	1000 MB/sec
32193	Pocket SSD 1TB Black/Orange	1000 MB/sec	1000 MB/sec
32195	Pocket SSD 2TB Black/Blue	1000 MB/sec	1000 MB/sec




TurboMetal SSD



- Data transfer speeds of up to 3700MB/s
- USB 4.0 interface with USB-C® connection
- Robust metal enclosure
- Integrated cooling fan



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
32021	TurboMetal SSD USB 4.0 1TB	3700 MB/sec	3600 MB/sec



SnapBack SSD

- USB 3.2 Gen 2x2 External Solid State Drive with USB-C® connection
- High speed data transfer- up to 20Gbps
- MagSafe compatible
- Store videos and photos directly to the External SSD drive
- Supports Apple ProRes 4K video recording at 120fps/60fps**
- Compatible with macOS devices, Android™ & Windows®.
- Nero Backup Software*

PART NO	DESCRIPTION	READ (UP TO)*	WRITE (UP TO)*
32060	SnapBack SSD USB 3.2 Gen 2x2 512 GB - Mocha	1900MB/s	1800 MB/s
32061	SnapBack SSD USB 3.2 Gen 2x2 1TB - Mocha	2000 MB/s	1600 MB/s
32075	SnapBack SSD USB 3.2 Gen 2x2 1TB - Blue	2000 MB/s	1600 MB/s
32062	SnapBack SSD USB 3.2 Gen 2x2 2 TB - Mocha	2000 MB/s	1800 MB/s
32076	SnapBack SSD USB 3.2 Gen 2x2 2 TB - Blue	2000 MB/s	1800 MB/s

* Nero Backup software is only suitable for Windows OS

** Apple ProRes - resolutions and frame rates vary depending on model of iPhone



Store 'n' Go Mini Diamond SSD

- USB 3.2 Gen 2 interface with USB-C® connection
- Data transfer speeds of up to 1000MB/s
- Ultra-small and lightweight SSD, weighing just 35 grams
- Stylish black design with a 3D surface



PART NO	DESCRIPTION	READ (UP TO)	WRITE (UP TO)
32024	Store 'n' Go Mini Diamond SSD USB-C 512GB	1000 MB/sec	1000 MB/sec
32025	Store 'n' Go Mini Diamond SSD USB-C 1TB	1000 MB/sec	1000 MB/sec
32026	Store 'n' Go Mini Diamond SSD USB-C 2TB	1000 MB/sec	1000 MB/sec



Store 'n' Go Mini Stripe SSD

- USB 3.2 Gen 2 interface with USB-C® connection
- Highly portable design, weighing just XXg
- Stylish black design with a striped surface
- High speed data transfer - a fast and safe solution to expand storage and backup files
- Nero Backup Software*



PART NO	DESCRIPTION	READ (UP TO)*	WRITE (UP TO)*
32034	Store 'n' Go Mini Stripe SSD USB 3.2 Gen 2 - 512 GB	1000 MB/sec	1000 MB/sec
32035	Store 'n' Go Mini Stripe SSD USB 3.2 Gen 2 - 1 TB	1000 MB/sec	1000 MB/sec
32036	Store 'n' Go Mini Stripe SSD USB 3.2 Gen 2 - 2 TB	1000 MB/sec	1000 MB/sec



HARD DRIVES

Verbatim hard drives feature Nero Backup software* that allows full system backup and restore functions. Each hard drive also includes Green Button Software, saving power when the drive is not in use as well as the Formatter Software that allows users to easily change the format of the drive from HFS+ to NTFS or FAT32, based on their own requirements. USB Rec&Play** allows your drive to act as a video recorder via USB, recording, playing back and even pausing live TV.



PORTABLE

Store 'n' Go USB 3.0 Hard Drive

- Stylish HDD for backing up desktops, notebooks & laptop computers
- USB 3.0 SuperSpeed interface
- USB plug 'n' play
- Software: Nero Backup*, Green Button, Hard Drive Easer, Hard Drive Info, Hard Drive Formatter
- USB Rec & Play**



PART NO	DESCRIPTION
53194	Store 'n' Go 1 TB USB 3.0 - Black
53195	Store 'n' Go 2 TB USB 3.0 - Black
53223	Store 'n' Go 4 TB USB 3.0 - Black



A woman with long dark hair is lying on her side on a white blanket with a brown diamond pattern. She is wearing a white lace-trimmed top and a gold watch. A grey laptop is open next to her. On the laptop, there is a Verbatim 4x DVD-RW case and a white DVD disc. To the right of the laptop, a pair of black sunglasses lies on the blanket. Below the laptop, a black Verbatim external drive is connected to a cable. In the bottom right corner, there is a red square with a white Verbatim 'V' logo. Other Verbatim optical media cases are visible at the bottom of the frame.

OPTICAL MEDIA

When drive manufacturers test their products, they use Verbatim media. It's the global No.1 for a reason - guaranteed quality!


OPTICAL TECHNOLOGY

Core technologies, like our AZO recording layer, SERL and Hard Coat give Verbatim media technological advantages over competing products.


ADVANCED AZO DYE TECHNOLOGY

AZO is patented technology used exclusively by Verbatim. The AZO recording layer provides increased protection and reliability – it not only withstands high laser and rotation speeds, it also strongly resists UV light and maximises performance delivering a high quality recording that lasts for generations.

The recording dye is critical to CD and DVD performance; its molecular structure is designed to absorb the typical wavelength of a drive's laser. The peak absorption wavelength needs to be optimised so that the disc is compatible with a wide range of recording speeds. If the peak is too short, disc sensitivity is reduced, which causes high-speed recording problems; but if the wavelength peak is too long, this reduces the reflectivity of the recording layer and can create read errors.



HARD COAT SURFACE



To protect discs that are handled repeatedly, Verbatim provides a special Hard Coat layer that protects from fingerprints, dust, scratches, static and water.

The image on the left depicts a disc comparison for typical scratch resistance. The image on the right shows how Verbatim's Hard Coat reduces fingerprint smudging, an essential feature for high quality recording.



Fingerprint proof



Static proof



Scratch proof



Dust proof



Water proof

SERL

SERL (Super Eutectic Recording Layer) is a special recording layer on Verbatim's CD-RW and DVD/RW media that ensures noise-free recording time and time again. With conventional rewriteable media, the recording layer deteriorates with every rewrite, meaning a decrease in quality. With Verbatim rewriteable media however, the recording layer is returned to perfect condition on every erasure, leaving a flawless disc for the next recording. SERL also enables this media to enjoy excellent archival stability and high-speed recording. This means users can enjoy perfect, high-speed data storage every time.



BLU-RAY

- High capacity for high definition (HD) video or long-term archiving
- Dual layer (DL) discs with two recording layers for 50GB storage
- BD-R XL – three recording layers for 100GB storage

**HARD
COAT**

**SUPER
HARD COAT**

PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
BD-R				
43715	6X	5pk Jewel Case	White/Blue	25 GB
43738	6X	25pk Spindle	Wide Inkjet No-ID	25 GB
97338	6X	50pk Spindle	Wide Thermal No-ID	25GB
BD-R DL				
43748	6X	5pk Jewel Case	White/Blue	50 GB
BD-RE				
43615	2X	5pk Jewel Case	White/Blue	25 GB






MDISC

- Over 1000 years lifetime for long-term archiving
- Data stored on an MDisc is engraved on a patented inorganic write layer which will not fade or deteriorate
- Impervious to environmental exposure, including light, temperature and humidity
- The latest optical drives read MDisc media, but please check for compatibility with your particular drive

PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
M-Disc BDXL				
98913	6X	5pk Jewel Case	White/Blue	100 GB



DVD

DVD-R AZO

- Suitable for drives which support DVD-R media
- Verbatim's AZO technology for increased protection and reliability



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Spindle				
95100	16X	10pk Spindle	Matt Silver	4.7 GB
95058	16X	25pk Spindle	Matt Silver	4.7 GB
95101	16X	50pk Spindle	Matt Silver	4.7 GB
95137	16X	50pk Spindle	Inkjet Printable	4.7 GB
95079	16X	50pk Spindle	Wide Inkjet No ID	4.7 GB
95211	16X	50pk Spindle	Wide Thermal No-ID	4.7 GB
95203	16X	50pk Spindle	Shiny Silver	4.7GB
95102	16X	100pk Spindle	Matt Silver	4.7GB
95153	16x	100pk Spindle	Inkjet Printable	4.7GB

DVD+R AZO

- Suitable for drives which support DVD+R media
- Verbatim's AZO technology for increased protection and reliability



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Jewel Case				
95049	16X	5pk Jewel Case	Matt Silver	4.7 GB
Spindle				
95136	16X	50pk Spindle	Inkjet Printable	4.7 GB
94917	16X	50pk Spindle	Wide Inkjet No-ID	4.7 GB
95145	16X	100pk Spindle	Inkjet Printable	4.7 GB

DVD-RW

- Re-writable disc
- Suitable for drives which support DVD-R media
- SERL technology for high reliability and long-term archive stability



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Spindle				
43552	4X	10pk Spindle	Matt Silver	4.7 GB

DVD-R Gold Archival

- Archival-grade DVD-R delivers new levels in longevity and performance
- Gold layer maximises disc lifetime by protecting data from corrosion
- Hard coating protects recording surface against scratches and rough handling
- Verbatim's AZO technology for increased protection and reliability



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Spindle				
95355	8X	50pk Spindle	Gold	4.7 GB





DVD

DVD+RW

- Re-writable disc
- Suitable for drives which support DVD+R media
- SERL technology for high reliability and long-term archive stability



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Jewel Case				
95043	4X	5pk Jewel Case	Matt Silver	4.7 GB



DOUBLE LAYER DVD+R DL

- Double layer (DL) discs with two recording layers for 8.5GB storage
- Suitable for drives which support DVD+R media
- Verbatim's AZO technology for increased protection and reliability



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Double Layer DVD+R DL AZO				
43541	8X	5pk Jewel Case	Matt Silver	8.5 GB
43667	8X	25pk Spindle	Wide Inkjet No-ID	8.5 GB
43754	8X	50pk Spindle	Wide Thermal No-ID	8.5 GB



CD

CD-R

- Exceptional reliability and performance for storing important data, music, and multimedia files.
- High-speed write capabilities enable quick and efficient recording.
- High-quality recording surface resists deterioration, ensuring long-term data preservation.



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Jewel Case				
41846	52X	10pk Jewel Case	Matt Silver	700 MB
Slim Case				
94935	52X	10pk Slim Case	Matt Silver	700 MB
Spindle				
43437	52X	10pk Spindle	Extra Protection	700 MB
43432	52X	25pk Spindle	Extra Protection	700 MB
95005	52X	50pk Spindle	Silver Inkjet	700 MB
94691	52X	50pk Spindle	Matt Silver	700 MB
41908	52X	50pk Spindle	Wide Inkjet No-ID	700MB
94554	52X	100pk Spindle	Matt Silver	700MB
95252	52X	100pk Spindle	Wide Inkjet No-ID	700MB
95254	52X	100pk Spindle	Wide Thermal No-ID	700 MB

CD-RW

- Re-writable disc
- SERL technology for high reliability and long-term archive stability
- 5 colour assortment adds simplicity to organise your data and important files



PART NO	SPEED	CONFIGURATION	SURFACE	CAPACITY
Slim Case				
43133	2-4X	5pk Slim Case	5 Colours	700 MB

DISC CASES

- Storage for your CD, DVD & Blu-ray optical media discs
- Available in slim or jewel case options

PART NO	DESCRIPTION
41852	CD/DVD Jewel Cases 10 pack
41854	CD/DVD Coloured Slim Cases 25 pack



KEY MILESTONES



1969
Verbatim incorporated as Information Terminals Corp. (ITC) April 28, 1969



1974
First 8" diskettes produced



1981
First monthly production of 1 million floppy disks



1985
Acquired by Eastman Kodak



1990
Mitsubishi Chemical acquired Verbatim and invested in the business



1993
Introduction of CD-ROM and CD-R disks, CD-R AZO Technology and SRAM cards



1995
Acquisitions of Laser Technologies and Ecotone. CD-R production started at MCL in Singapore



1999
Restructuring and establishment of the MKM/Verbatim Group. DVD-R & DVD-RW launched



2001
DVD+RW production started (first in the market) Memory Cards launched



2002
DVD+R and CD-R Ultra Speed 24x products launched (first in the market) Start of sales of USB Drives



2015
M-Disc collaboration. Introduction of 1000yr archival media



2014
Launch of PLA & ABS 3D printing filaments



2013
VxRGB LED lamps launched



2012
Cleansui Water Filters launched in Europe SSD Launch



2011
VELVE OLED Lighting launched utilising technology from Mitsubishi Chemical Corp



2010
Launch of LED Lighting business utilising technology from Mitsubishi Chemical Corp



2009
Mitsubishi Kagaku Media Co. Ltd announces acquisition of Freecom B.V - extending global presence and position in external storage market



2008
Blu-ray Dual Layer, SDHC & MicroSDHC, Multimedia HDD, RAID HDD & Colour HDD launched



2007
Verbatim globalises corporate identity. Acquisition of SmartDisk and launch of External HDD Business



2004
Blu-ray BD-R/RE, DVD 16x and DVD+R Double Layer 8.5GB, CD-R 52x LightScribe launched (first in market for all)



2016
Operations centralised to new headquarters in Germany. ODD launched



2018
New range of security products introduced



2019
Verbatim celebrates its 50th anniversary



2020
Acquisition of Verbatim by CMC Magnetics




2021
Launch of specialist gaming brand: SureFire



2023
Introduction of Portable Monitors



2024
Exciting new branding launched at Computex



2025
New global website design launched across Europe, Asia Pacific and the Americas

VERBATIM'S COMMITMENT TO ETHICAL SOURCING & SUSTAINABILITY

At Verbatim, we believe that sustainability and corporate responsibility are not just talking points – they are actions that shape every decision we make. Our membership in leading industry associations ensures our products are sourced and packaged with care for people and the planet. Our key partnerships with SEDEX and APCO demonstrate how we go above and beyond to meet the ethical and environmental expectations of our customers.

ABOUT SEDEX



SEDEX is a global, not-for-profit membership organisation that supports responsible and ethical business practices across supply chains. Through its secure online platform, SEDEX enables companies to share data on labour standards, health and safety, environmental performance, and business ethics. By promoting transparency and accountability, it helps ensure fair treatment of workers and supports sustainable sourcing practices worldwide.

VERBATIM'S COMMITMENT

Through SEDEX and equivalent recognised programs, we:

- Connect suppliers and customers to share verified ethical trade information.
- Undergo independent SMETA (Sedex Members Ethical Trade Audit) assessments, or accept equivalent third-party ethical audits from accredited bodies such as BSI, Amfori, or RBA.
- Require all suppliers to provide valid, independent ethical audit reports, without exception.
- Expect every supplier to maintain internationally recognised management certifications such as ISO 9001 and/or ISO 14001.

THE VERBATIM DIFFERENCE

The vast majority of our technology suppliers are active members of SEDEX, with the remainder meeting equivalent high standards through other globally recognised audit programs. This ensures that every product we source is backed by robust social compliance, environmental responsibility, and ethical business practices, giving our customers complete confidence in the integrity of our supply chain.



ABOUT APCO

The Australian Packaging Covenant Organisation (APCO) is a co-regulatory, not-for-profit organisation leading the transition to a circular economy for packaging in Australia. By working with business, government, and industry, APCO sets national targets to ensure all packaging is reusable, recyclable, or compostable. Its Sustainable Packaging Guidelines (SPGs) and the Australasian Recycling Label (ARL) help businesses design packaging that reduces waste and supports responsible disposal.

VERBATIM'S COMMITMENT

As an active APCO member, Verbatim has embedded sustainability into every stage of our packaging design process. By 2025, we have:

- Fully aligned our packaging design process with APCO's Sustainable Packaging Guidelines.

- Applied the Australasian Recycling Label (ARL) to the vast majority of our product range, improving recycling clarity for consumers.
- Achieved 100% plastic-free packaging for all newly launched products.
- Removed soft plastics from our packaging across the business.
- Transitioned most packaging to FSC-certified cardboard and paperboard formats.
- Significantly increased the proportion of recyclable and responsibly sourced materials year-on-year.

THE VERBATIM DIFFERENCE

Our packaging goes beyond compliance – it delivers real environmental benefits. Customers can be confident they are choosing products designed for recyclability, free from unnecessary plastics, and contributing to a more circular economy.

WHY THIS MATTERS FOR YOU

By partnering with Verbatim, you're choosing a supplier that:

- Meets internationally recognised ethical sourcing and environmental management standards.
- Delivers full transparency on supplier audits and certifications.
- Is actively reducing packaging waste and improving recyclability at scale.
- Helps you meet your own ESG (Environmental, Social, Governance) goals and customer expectations.

Verbatim Australia

36-40 Pacific Drive,
Keysborough, VIC 3173
Australia
T: +61 (0)3 9790 8999

www.verbatim.com

Created February 2026

