ThinkEdge SE60n Gen2 13MC0006UT





The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core Ultra 5 235H, 14C (4P + 8E + 2LPE) / 14T, Max Turbo up to 5.0GHz, 18MB Intel Smart Cache
- 1x 16GB SODIMM DDR5-5600
- 512GB SSD M.2 2280 PCIe 4.0x4 NVMe Opal 2.0
- Intel Arc 140T GPU
- Windows 11 IoT Enterprise LTSC 2024, English
- Case color - Black
- 3-year, Onsite

Premier Support - A direct 24x7x365 line to our most elite technicians.

- Advanced technical support, 24x7x365, in more than 100 markets
- Comprehensive hardware & OEM software support
- Single point of contact for simplified end-to-end case management
- Technical Account Managers for proactive relationship and escalation management
- Priority on service delivery and repair parts
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories

UAE (United Arab Emirates)



ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792



Lenovo Ultra High Speed HDMI™ Cable 1.8m

4X91U92141



Lenovo Analog In-Ear Headphones Gen II Bulk Package (20pcs)

4XD1T54899

>> View More Accessories

Recommended Services

Best

5Y Onsite upgrade from 3Y Onsite (5WS1U63800)

Better

4Y Onsite upgrade from 3Y Onsite (5WS1U63834)

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkEdge SE60n Gen2 13MC0006UT

PERFORMANCE

Processor
Intel Core™ Ultra 5 235H, 14C (4P + 8E + 2LPE) / 14T, Max Turbo up to 5.0GHz, 18MB Intel® Smart Cache

Graphics
Intel® Arc™ 140T GPU

Chipset
Intel® SoC Platform

Memory
1x 16GB SODIMM DDR5-5600

Max Memory
Standard Temperature (0~50°C): Up to 96GB DDR5-5600 SODIMM

Memory Slots
Two DDR5 SODIMM slots, dual-channel capable

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support[1]
Standard Temperature (0~50°C): Up to two drives, 1x M.2 SATA SSD + 1x M.2 SSD • M.2 2280 SSD up to 2TB each • M.2 2242 SATA SSD up to 1TB each

Power Supply
150W (0~40°C) / 120W (0~50°C) / 100W, (-20~60°C)

DESIGN

Keyboard
None

Mouse
None

Case Color
Black

Dust Filter
IP50 Dust Shield 2.1L

Mounting
DIN Rail Bracket

Dimensions (WxDxH)[2]
240 x 150 x 59 mm (9.45 x 5.91 x 2.32 inches)

Weight[3]
Around 2.4 kg (5.29 lbs)

CONNECTIVITY

Ethernet
2x Intel® I226-IT 2.5G, 2x RJ-45

WLAN + Bluetooth[4]
Intel® Wi-Fi® 6E AX210, 802.11ax 2x2 + BT5.1

WWAN
WWAN Not Supported

Front Ports
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 1x remote power switch
- 1x DIO (4DI / 4DO)
- 2x serial (RS232 / RS422 / RS485, BIOS & hardware jumper selectable)

Rear Ports
- 1x 12-36V WDC-in
- 1x Dual-Mode DisplayPort™ (DP++)
- 4x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x HDMI® 2.1 TMDS
- 1x line-out (3.5mm)
- 1x microphone-in (3.5mm)
- 2x 2.5GbE Ethernet (RJ-45)

Optional Rear Ports (configured)
None

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified

MANAGEABILITY

System Management
Intel® vPro®

SERVICE

Base Warranty
3-year, Onsite

Included Upgrade
None

ENVIRONMENTAL

Operating Temperature
Standard Temperature 0℃ to 50℃ (32℉ to 122℉)

CERTIFICATIONS

Green Certifications
- GREENGUARD®
- RoHS compliant

Other Certifications
Red Hat Enterprise Linux Certified

SOFTWARE

Operating System
Windows® 11 IoT Enterprise LTSC 2024, English

ACCESSORIES

Bundled Accessories
IP50 dust shield 2.1L

MODEL

TopSeller	: Yes	**EAN / UPC / JAN**	: 199275164903
Announce Date	: 2026-03-30	**End of Support**	: 2032-09-14



Product image is a sample, it may not match the real color of this model

Note:
[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.
[2] The system dimensions may vary depending on configurations.
[3] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
[4] Wi-Fi operation (including Wi-Fi 6, Wi-Fi 6E, Wi-Fi 7, etc.) is subject to the regulatory requirements of each country. Bluetooth may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.