

Specifications

Eaton P006-010-15RR

Computer AC Power Cable, NEMA 5-15P to C13 - 360-Degree Rotating Right-Angle 5-15P Plug, 10A, 125V, 18 AWG, 10 ft. (3 m), Black

General specifications

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P006-010-15RR
UPC	037332298300
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12.52 in
PRODUCT WIDTH	5.04 in
PRODUCT WEIGHT	0.76 lb
COMPLIANCES	WEEE
CERTIFICATIONS	CSA cUL Listed UL
GLOBAL CATALOG	P006-010-15RR
PRODUCT TYPE	Power cord



Powering Business Worldwide

Product specifications

INPUT CURRENT -MAX	10 Ampere
OPERATING TEMPERATURE RANGE	23° to 158°F (-5° to 70°C)
STORAGE TEMPERATURE	14° to 140°F (-10° to 60°C)
DEVICE COMPATIBILITY	Computer Laptop
AWG-SIZE	18
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	35% to 85% RH
OUTER CABLE DIAMETER	7.7mm
POWER CORD JACKET TYPE	SJT
STORAGE HUMIDITY RANGE	35% to 85% RH
WIRE SIZE (AWG) - MAX	1.02
CABLE JACKET RATING	SJT
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P006-010-15RR NEMA 5-15P to C13 Computer Power Cable, 10 ft. (3 m), Black
CONNECTOR TYPE	Power
PRODUCT FEATURES	Angled Plug
CABLE JACKET MATERIAL	PVC
PLUG COLOR	Black
SIDEA CONNECTOR1	NEMA 5-15P - RIGHT ANGLE
SIDEB CONNECTOR1	IEC-320-C13
CONNECTOR GROUP	5-15P C13
CONNECTOR	NEMA 5-15P right angle IEC 320-C13

Resources

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

