

HPE Aruba Networking CX 6000 Switch Series



What's new

- It simplifies IT operations with modern Layer 2 switch series that provides entry level, reliable, and convenient wired access connectivity
- The CX 6000 series has convenient built-in 1GbE uplinks and up to 740W of Class 4 PoE for support of access points, client, and IoT devices
- It has compact and fanless 8-port and 12-port models for space-constrained deployments
- The CX 6000 provides flexibility to manage and simplify configurations

Overview

The HPE Aruba Networking CX 6000 Switch Series is a modern family of entry level access switches ideal for branch offices, midsize businesses, and small enterprises. Designed for reliable, simple, and secure access, this switch family provides a convenient and cost-effective wired access solution for networks supporting Internet of Things (IoT), mobile, and cloud applications.

Prepare your network for future demands with a powerful ASIC and HPE Aruba Networking CX Switch Operating System for a consistent, and efficient operator experience. This fully-managed series has convenient built-in uplinks with up to 740W of Class 4 PoE to support IoT devices such as security cameras and wireless APs. A compact and fanless model is ideal for use in quiet, small workspaces. The CX 6000 series is easy to deploy and use with flexible management choices, allowing the ideal fit for your business and

with HPE Aruba Networking Central, HPE Aruba Networking Switch Multi-Edit Software, easy to use Web GUI, or industry standard CLI

network environment.

- Ready for software defined networking with REST APIs.

Features

Entry-level Layer 2 access switches

The HPE Aruba Networking CX 6000 Switch Series offers Ethernet gigabit connectivity and optional PoE to provide entry-level, reliable, and convenient wired access connectivity for enterprise branch offices and SMB networks.

The switch series delivers a simple, consistent operator experience with the HPE Aruba Networking CX Switch Operating System used across HPE Aruba Networking CX switching platforms.

It has fully-managed enterprise-class switches deliver Layer 2 capabilities with support static routing, access control lists (ACLs), robust quality of service (QoS), traffic prioritization, sFlow®, and IPv6.

The CX 6000 series provides right-size deployment with choice of 8, 12, 24, and 48-port 1U models with convenient built-in 1GbE uplinks and up to 740W of Class 4 PoE.

It simplifies ownership with no switch software licensing or subscriptions required.

AI-ready performance and power

The HPE Aruba Networking CX 6000 Switch Series is designed with a dedicated ASIC that delivers very low latency, increased packet buffering, and optimized power consumption ideal for AI, Wi-Fi 7, and IoT requirements.

It supports up to 740W IEEE 802.3at Class 4 PoE with up to 30W per port to enable full deployments of wireless access points and IoT devices.

It has up to four built-in wire speed 1GbE uplinks remove bottlenecks at the access layer where users and devices connect.

Simplified configuration and management

The HPE Aruba Networking CX 6000 Switch Series provides flexibility to manage and simplify configurations with HPE Aruba Networking Central, HPE Aruba Networking Switch Multi-Edit Software, easy-to-use web GUI, or industry-standard CLI.

HPE Aruba Networking Switch Multi-Edit Software introduces automation that allows for rapid network-wide changes and verifies policy conformance post network updates.

The switch series offers unified management across wired, wireless, and WAN using HPE Aruba Networking Central.

It reduces manual IT operation tasks around initial deployment or on-going configuration changes to accommodate adds, moves, and changes with colorless ports using local user roles and local MAC authentication (LMA).

The CX 6000 series is ready for software-defined networking with REST APIs for fine-grained programmability of network tasks.

Technical specifications	HPE Aruba Networking CX 6000 Switch Series
Power consumption	Maximum Power (w/o PoE): 49.7W Maximum Power (w/ PoE): 890W Depending on model
Input voltage	100-127 VAC / 200-240 VAC
Ports	8, 12, 24, or 48 10/100/1000BASE-T ports, depending on model
Latency	1 Gbps: 2.3 μSec maximum, depending on model
Switching capacity	104 Gbps maximum, depending on model
Throughput	Up to 77.3 Mpps, depending on model
Memory and processor	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC
PoE capability	Up to 740W of Class 4 PoE maximum, depending on model
Management features	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software
Operating temperature	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)
Warranty	Limited lifetime warranty. See the warranty duration .

SKU comparison

	HPE Aruba Networking CX 6000 12p 10M/100M/1G Class4 PoE 2p SFP 1G 139W Switch (R8N89B)	HPE Aruba Networking CX 6000 12p 10M/100M/1G Class4 PoE 2p SFP 1G 139W TAA Switch (S4R21A)	HPE Aruba Networking CX 6000 24p 10M/100M/1G 4p SFP 1G Switch (R8N88B)
Differentiator	Class 4 PoE/PoE+	Class 4 PoE/PoE+ TAA certified	Non-PoE
Power consumption	Max. Power (w/o PoE): 19.7W Max. Power (w/ PoE): 165W	Max. Power (w/o PoE): 19.7W Max. Power (w/ PoE): 165W	Max. Power (w/o PoE): 22.4W
Input voltage	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC
Ports	12 x 10/100/1000BASE-T Class 4 PoE ports 2 x 1 G SFP ports 2 x 1 GbE ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port	12 x 10/100/1000BASE-T Class 4 PoE ports 2 x 1 G SFP ports 2 x 1 GbE ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port	24 x 10/100/1000BASE-T ports 4 x 1 G SFP ports 1 x USB-C console port 1 x USB Type-A host port
Latency	1 Gbps: 2.3 Sec	1 Gbps: 2.3 Sec	1 Gbps: 1.5 Sec
Switching capacity	32 Gbps	32 Gbps	56 Gbps
Throughput	23.8 Mpps	23.8 Mpps	41.6 Mpps
Memory and processor	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC
PoE capability	139W Class 4 PoE/PoE+	139W Class 4 PoE/PoE+	Non-PoE model
Management features	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software
Operating temperature	32°F to 104°F (0°C to 40°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	32°F to 104°F (0°C to 40°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)
Warranty	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.

	HPE Aruba Networking CX 6000 24p 10M/100M/1G 4p SFP 1G TAA Switch (S4R27A)	HPE Aruba Networking CX 6000 24p 10M/100M/1G Class4 PoE 4p SFP 1G 370W Switch (R8N87B)	HPE Aruba Networking CX 6000 24p 10M/100M/1G Class4 PoE 4p SFP 1G 370W TAA Switch (S4R26A)
Differentiator	Non-PoE TAA certified	Class 4 PoE/PoE+	Class 4 PoE/PoE+ TAA certified
Power consumption	Max. Power (w/o PoE): 22.4W	Max. Power (w/o PoE): 26.5W Max. Power (w/ PoE): 409W	Max. Power (w/o PoE): 26.5W Max. Power (w/ PoE): 409W
Input voltage	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC
Ports	24 x 10/100/1000BASE-T ports 4 x 1 G SFP ports 1 x USB-C console port 1 x USB Type-A host port	24 x 10/100/1000BASE-T Class 4 PoE ports 4 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port	24 x 10/100/1000BASE-T Class 4 PoE ports 4 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port
Latency	1 Gbps: 1.5 Sec	1 Gbps: 1.5 Sec	1 Gbps: 1.5 Sec
Switching capacity	56 Gbps	56 Gbps	56 Gbps
Throughput	41.6 Mpps	41.6 Mpps	41.6 Mpps
Memory and processor	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC
PoE capability	Non-PoE model	370W Class 4 PoE/PoE+	370W Class 4 PoE/PoE+
Management features	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software
Operating temperature	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)
Warranty	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.

	HPE Aruba Networking CX 6000 48p 10M/100M/1G 4p SFP 1G Switch (R8N86B)	HPE Aruba Networking CX 6000 48p 10M/100M/1G 4p SFP 1G TAA Switch (S4R25A)	HPE Aruba Networking CX 6000 48p 10M/100M/1G Class4 PoE 4p SFP 1G 370W Switch (R8N85B)
Differentiator	Non-PoE	Non-PoE TAA certified	Class 4 PoE/PoE+
Power consumption	Max. Power (w/o PoE): 35.2W	Max. Power (w/o PoE): 35.2W	Max. Power (w/o PoE): 41.0W Max. Power (w/ PoE): 439W
Input voltage	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC
Ports	48 x 10/100/1000BASE-T ports 4 x 1 G SFP ports 1 x USB-C console port 1 x USB Type-A host port	48 x 10/100/1000BASE-T ports 4 x 1 G SFP ports 1 x USB-C console port 1 x USB Type-A host port	48 x 10/100/1000BASE-T Class 4 PoE ports 4 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port
Latency	1 Gbps: 1.9 Sec	1 Gbps: 1.9 Sec	1 Gbps: 1.9 Sec
Switching capacity	104 Gbps	104 Gbps	104 Gbps
Throughput	77.3 Mpps	77.3 Mpps	77.3 Mpps
Memory and processor	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC
PoE capability	Non-PoE model	Non-PoE model	370W Class 4 PoE/PoE+
Management features	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software
Operating temperature	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)
Warranty	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.

	HPE Aruba Networking CX 6000 48p 10M/100M/1G Class4 PoE 4p SFP 1G 370W TAA Switch (S4R24A)	HPE Aruba Networking CX 6000 48p 10M/100M/1G Class4 PoE 4p SFP 1G 740W Switch (R9Y03B)	HPE Aruba Networking CX 6000 48p 10M/100M/1G Class4 PoE 4p SFP 1G 740W TAA Switch (S4R20A)
Differentiator	Class 4 PoE/PoE+ TAA certified	Class 4 PoE/PoE+	Class 4 PoE/PoE+ TAA certified
Power consumption	Max. Power (w/o PoE): 41.0W Max. Power (w/ PoE): 439W	Max. Power (w/o PoE): 45.6W Max. Power (w/ PoE): 818W	Max. Power (w/o PoE): 45.6W Max. Power (w/ PoE): 818W
Input voltage	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC
Ports	48 x 10/100/1000BASE-T Class 4 PoE ports 4 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port	48 x 10/100/1000BASE-T Class 4 PoE ports 4 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port	48 x 10/100/1000BASE-T Class 4 PoE ports 4 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port
Latency	1 Gbps: 1.9 Sec	1 Gbps: 1.9 Sec	1 Gbps: 1.9 Sec
Switching capacity	104 Gbps	104 Gbps	104 Gbps
Throughput	77.3 Mpps	77.3 Mpps	77.3 Mpps
Memory and processor	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC
PoE capability	370W Class 4 PoE/PoE+	740W of Class 4 PoE/PoE+	740W of Class 4 PoE/PoE+
Management features	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software
Operating temperature	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	Maximum of 32°F to 113°F (0°C to 45°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)
Warranty	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.

	HPE Aruba Networking CX 6000 8p 10M/100M/1G 2p SFP 1G Switch (S4R22A)	HPE Aruba Networking CX 6000 8p 10M/100M/1G 2p SFP 1G TAA Switch (S4R28A)	HPE Aruba Networking CX 6000 8p 10M/100M/1G Class4 PoE 2p SFP 1G 67W Switch (S4R23A)
Differentiator	Non-PoE	Non-PoE TAA certified	Class 4 PoE/PoE+
Power consumption	Max. Power (w/o PoE): 13.8W	Max. Power (w/o PoE): 13.8W	Max. Power (w/o PoE): 16.3W Max. Power (w/ PoE): 98W
Input voltage	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC	100–127 VAC / 200–240 VAC
Ports	8 x 10/100/1000BASE-T ports 2 x 1 G SFP ports 1 x USB-C console port 1 x USB Type-A host port	8 x 10/100/1000BASE-T ports 2 x 1 G SFP ports 1 x USB-C console port 1 x USB Type-A host port	8 x 10/100/1000BASE-T Class 4 PoE ports 2 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port
Latency	1 Gbps: 3.2 Sec	1 Gbps: 3.2 Sec	1 Gbps: 3.2 Sec
Switching capacity	20 Gbps	20 Gbps	20 Gbps
Throughput	14.8 Mpps	14.8 Mpps	14.8 Mpps
Memory and processor	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC
PoE capability	Non-PoE model	Non-PoE model	67W Class 4 PoE/PoE+
Management features	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software
Operating temperature	32°F to 104°F (0°C to 40°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	32°F to 104°F (0°C to 40°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)	32°F to 104°F (0°C to 40°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)
Warranty	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.	Limited lifetime warranty. See the warranty duration.

HPE Aruba Networking CX 6000 8p 10M/100M/1G Class4 PoE 2p SFP 1G 67W TAA Switch (S4R29A)

Differentiator	Class 4 PoE/PoE+ TAA certified
Power consumption	Max. Power (w/o PoE): 16.3W Max. Power (w/ PoE): 98W
Input voltage	100–127 VAC / 200–240 VAC
Ports	8 x 10/100/1000BASE-T Class 4 PoE ports 2 x 1 G SFP ports Supports PoE Standards IEEE 802.3af, 802.3at 1 x USB-C console port 1 x USB Type-A host port
Latency	1 Gbps: 3.2 Sec
Switching capacity	20 Gbps
Throughput	14.8 Mpps
Memory and processor	CPU: Dual-core Arm® Cortex-A9 @ 1016 MHz Memory: 4 GB DDR3 Flash: 16 GB eMMC
PoE capability	67W Class 4 PoE/PoE+
Management features	Management flexibility with support for HPE Aruba Networking Central, easy-to-use Web GUI, CLI, and HPE Aruba Networking Switch Multi-Edit Software
Operating temperature	32°F to 104°F (0°C to 40°C) up to 5000 ft (1.5 km) derate -1°C for every 1000 ft (305 m) from 5000 ft (1.5 km) to 10000 ft (3.0 km)
Warranty	Limited lifetime warranty. See the warranty duration.

Related Options

The following options are available for these series:

SKU	Description
Commutateurs	
JL258A	HPE Aruba Networking 2930F 8G PoE+ 2SFP+ Switch
JL693A	HPE Aruba Networking 2930F 12G PoE+ 2G/2SFP+ Switch
R9Y04A	HPE Aruba Networking CX 6100 48G Class4 PoE 4SFP+ 740W Switch
Câbles/kits de câblage	
R9J32A	HPE Aruba Networking USB-A reversible to USB-C PC-to-Switch 3m Cable
R9J33A	HPE Aruba Networking USB-C to USB-C PC-to-Switch 3m Cable
JL742A	HPE Aruba Networking X511 12-port Cable Guard
Emetteurs-récepteurs	
J4859D	HPE Aruba Networking 1G SFP LC LX 10km SMF Transceiver
J4858D	HPE Aruba Networking 1G SFP LC SX 500m OM2 MMF Transceiver
J8177E	HPE Aruba Networking 1G SFP RJ45 100m Cat5e Transceiver
Kits de montage	
J9583B	HPE Aruba Networking X414 1U Universal 4-post Rack Mount Kit
Logiciel HPE Aruba Networking	
JL639AAE	HPE Aruba Networking NetEdit Single Node 1yr Subscription E-STU
JL640AAE	HPE Aruba Networking NetEdit Single Node 3yr Subscription E-STU

Related Services

The following services are available for these series:

SKU	Description
Technology Services	
H82MOE	HPE Aruba Networking 1Y 24x7 Technical Support 6000 48G 740W SVC
H82T3E	HPE Aruba Networking 1Y 24x7 Technical Support Volume Tier 26000 48G 740W SVC

H82N3E	HPE Aruba Networking 3Y 24x7 Technical Support 6000 48G 740W SVC
H82U8E	HPE Aruba Networking 3Y 24x7 Technical Support Volume Tier 26000 48G 740W SVC
H82Q9E	HPE Aruba Networking 5Y 24x7 Technical Support 6000 48G 740W SVC
H82X8E	HPE Aruba Networking 5Y 24x7 Technical Support Volume Tier 26000 48G 740W SVC
H55D5E	HPE Aruba Networking Foundational Care 1Y 4HR Exch 6000 12G CL4 2SFP SVC
H54Q4E	HPE Aruba Networking Foundational Care 1Y 4HR Exch 6000 24G 4SFP SVC
H54B3E	HPE Aruba Networking Foundational Care 1Y 4HR Exch 6000 24G CL4 4SFP SVC
H53N2E	HPE Aruba Networking Foundational Care 1Y 4HR Exch 6000 48G 4SFP SVC
H82L4E	HPE Aruba Networking Foundational Care 1Y 4HR Exch 6000 48G 740W SVC
H52Z1E	HPE Aruba Networking Foundational Care 1Y 4HR Exch 6000 48G CL4 4SFP SVC
H55K9E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T1 6000 12G CL4 2SFP SVC
H54W8E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T1 6000 24G 4SFP SVC
H54H7E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T1 6000 24G CL4 4SFP SVC
H53U6E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T1 6000 48G 4SFP SVC
H82S8E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T1 6000 48G 740W SVC
H53F5E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T1 6000 48G CL4 4SFP SVC
H55L0E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T2 6000 12G CL4 2SFP SVC
H54W9E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T2 6000 24G 4SFP SVC
H54H8E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T2 6000 24G CL4 4SFP SVC
H53U7E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T2 6000 48G 4SFP SVC
H82S9E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T2 6000 48G 740W SVC
H53F6E	HPE Aruba Networking Foundational Care 1Y 4HR Exch Vol T2 6000 48G CL4 4SFP SVC
H55D9E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 6000 12G CL4 2SFP SVC
H54Q8E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 6000 24G 4SFP SVC
H54B7E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 6000 24G CL4 4SFP SVC
H53N6E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 6000 48G 4SFP SVC
H82L8E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 6000 48G 740W SVC
H52Z5E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite 6000 48G CL4 4SFP SVC
H55E0E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 6000 12G CL4 2SFP SVC
H54Q9E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 6000 24G 4SFP SVC
H54B8E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 6000 24G CL4 4SFP SVC
H53N7E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 6000 48G 4SFP SVC
H52Z6E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite CDMR 6000 48G CL4 4SFP SVC

H55D8E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 6000 12G CL4 2SFP SVC
H54Q7E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 6000 24G 4SFP SVC
H54B6E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 6000 24G CL4 4SFP SVC
H53N5E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 6000 48G 4SFP SVC
H52Z4E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite HW Only 6000 48G CL4 4SFP SVC
H82L7E	HPE Aruba Networking Foundational Care 1Y 4HR Onsite Hardware Only 6000 48G 740W SVC
H55E2E	HPE Aruba Networking Foundational Care 1Y 6HR CTR 6000 12G CL4 2SFP SVC
H54R1E	HPE Aruba Networking Foundational Care 1Y 6HR CTR 6000 24G 4SFP SVC
H54COE	HPE Aruba Networking Foundational Care 1Y 6HR CTR 6000 24G CL4 4SFP SVC
H53N9E	HPE Aruba Networking Foundational Care 1Y 6HR CTR 6000 48G 4SFP SVC
H52Z8E	HPE Aruba Networking Foundational Care 1Y 6HR CTR 6000 48G CL4 4SFP SVC
H55E3E	HPE Aruba Networking Foundational Care 1Y 6HR CTR CDMR 6000 12G CL4 2SFP SVC
H54R2E	HPE Aruba Networking Foundational Care 1Y 6HR CTR CDMR 6000 24G 4SFP SVC
H54C1E	HPE Aruba Networking Foundational Care 1Y 6HR CTR CDMR 6000 24G CL4 4SFP SVC
H53POE	HPE Aruba Networking Foundational Care 1Y 6HR CTR CDMR 6000 48G 4SFP SVC
H52Z9E	HPE Aruba Networking Foundational Care 1Y 6HR CTR CDMR 6000 48G CL4 4SFP SVC
H82L9E	HPE Aruba Networking Foundational Care 1Y 24x7 CDMR 6000 48G 740W SVC
H82M1E	HPE Aruba Networking Foundational Care 1Y CTR 6000 48G 740W SVC
H82M2E	HPE Aruba Networking Foundational Care 1Y CTR CDMR 6000 48G 740W SVC
H82L5E	HPE Aruba Networking Foundational Care 1Y NBD 6000 48G 740W SVC
H82L6E	HPE Aruba Networking Foundational Care 1Y NBD CDMR 6000 48G 740W SVC
H55D3E	HPE Aruba Networking Foundational Care 1Y NBD Exch 6000 12G CL4 2SFP SVC
H54Q2E	HPE Aruba Networking Foundational Care 1Y NBD Exch 6000 24G 4SFP SVC
H54B1E	HPE Aruba Networking Foundational Care 1Y NBD Exch 6000 24G CL4 4SFP SVC
H53NOE	HPE Aruba Networking Foundational Care 1Y NBD Exch 6000 48G 4SFP SVC
H82L2E	HPE Aruba Networking Foundational Care 1Y NBD Exch 6000 48G 740W SVC
H52Y9E	HPE Aruba Networking Foundational Care 1Y NBD Exch 6000 48G CL4 4SFP SVC
H55D4E	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 6000 12G CL4 2SFP SVC
H54Q3E	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 6000 24G 4SFP SVC
H54B2E	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 6000 24G CL4 4SFP SVC
H53N1E	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 6000 48G 4SFP SVC
H52Z0E	HPE Aruba Networking Foundational Care 1Y NBD Exch HW Only 6000 48G CL4 4SFP SVC
H82L3E	HPE Aruba Networking Foundational Care 1Y NBD Exch Hardware Only 6000 48G 740W SVC

H55K5E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T1 6000 12G CL4 2SFP SVC
H54W4E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T1 6000 24G 4SFP SVC
H54H3E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T1 6000 24G CL4 4SFP SVC
H53U2E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T1 6000 48G 4SFP SVC
H82S4E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T1 6000 48G 740W SVC
H53F1E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T1 6000 48G CL4 4SFP SVC
H55K6E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T2 6000 12G CL4 2SFP SVC
H54W5E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T2 6000 24G 4SFP SVC
H54H4E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T2 6000 24G CL4 4SFP SVC
H53U3E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T2 6000 48G 4SFP SVC
H82S5E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T2 6000 48G 740W SVC
H53F2E	HPE Aruba Networking Foundational Care 1Y NBD Exch Vol T2 6000 48G CL4 4SFP SVC
H55D6E	HPE Aruba Networking Foundational Care 1Y NBD Onsite 6000 12G CL4 2SFP SVC
H54Q5E	HPE Aruba Networking Foundational Care 1Y NBD Onsite 6000 24G 4SFP SVC
H54B4E	HPE Aruba Networking Foundational Care 1Y NBD Onsite 6000 24G CL4 4SFP SVC
H53N3E	HPE Aruba Networking Foundational Care 1Y NBD Onsite 6000 48G 4SFP SVC
H52Z2E	HPE Aruba Networking Foundational Care 1Y NBD Onsite 6000 48G CL4 4SFP SVC
H55D7E	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 6000 12G CL4 2SFP SVC
H54Q6E	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 6000 24G 4SFP SVC
H54B5E	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 6000 24G CL4 4SFP SVC
H53N4E	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 6000 48G 4SFP SVC
H52Z3E	HPE Aruba Networking Foundational Care 1Y NBD Onsite CDMR 6000 48G CL4 4SFP SVC
H55E6E	HPE Aruba Networking Foundational Care 3Y 4HR Exch 6000 12G CL4 2SFP SVC
H54R5E	HPE Aruba Networking Foundational Care 3Y 4HR Exch 6000 24G 4SFP SVC
H54C4E	HPE Aruba Networking Foundational Care 3Y 4HR Exch 6000 24G CL4 4SFP SVC
H53P3E	HPE Aruba Networking Foundational Care 3Y 4HR Exch 6000 48G 4SFP SVC
H82M5E	HPE Aruba Networking Foundational Care 3Y 4HR Exch 6000 48G 740W SVC
H53A2E	HPE Aruba Networking Foundational Care 3Y 4HR Exch 6000 48G CL4 4SFP SVC
H55M3E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T1 6000 12G CL4 2SFP SVC
H54Y2E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T1 6000 24G 4SFP SVC
H54K1E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T1 6000 24G CL4 4SFP SVC
H53W0E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T1 6000 48G 4SFP SVC
H82U2E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T1 6000 48G 740W SVC

H53G9E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T1 6000 48G CL4 4SFP SVC
H55M4E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T2 6000 12G CL4 2SFP SVC
H54Y3E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T2 6000 24G 4SFP SVC
H54K2E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T2 6000 24G CL4 4SFP SVC
H53W1E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T2 6000 48G 4SFP SVC
H82U3E	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T2 6000 48G 740W SVC
H53HOE	HPE Aruba Networking Foundational Care 3Y 4HR Exch Vol T2 6000 48G CL4 4SFP SVC
H55F2E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 6000 12G CL4 2SFP SVC
H54S1E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 6000 24G 4SFP SVC
H54DOE	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 6000 24G CL4 4SFP SVC
H53P9E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 6000 48G 4SFP SVC
H82N1E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 6000 48G 740W SVC
H53A8E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite 6000 48G CL4 4SFP SVC
H55F3E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 6000 12G CL4 2SFP SVC
H54S2E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 6000 24G 4SFP SVC
H54D1E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 6000 24G CL4 4SFP SVC
H53Q0E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 6000 48G 4SFP SVC
H53A9E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite CDMR 6000 48G CL4 4SFP SVC
H55F1E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 6000 12G CL4 2SFP SVC
H54S0E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 6000 24G 4SFP SVC
H54C9E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 6000 24G CL4 4SFP SVC
H53P8E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 6000 48G 4SFP SVC
H53A7E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite HW Only 6000 48G CL4 4SFP SVC
H82N0E	HPE Aruba Networking Foundational Care 3Y 4HR Onsite Hardware Only 6000 48G 740W SVC
H55F5E	HPE Aruba Networking Foundational Care 3Y 6HR CTR 6000 12G CL4 2SFP SVC
H54S4E	HPE Aruba Networking Foundational Care 3Y 6HR CTR 6000 24G 4SFP SVC
H54D3E	HPE Aruba Networking Foundational Care 3Y 6HR CTR 6000 24G CL4 4SFP SVC
H53Q2E	HPE Aruba Networking Foundational Care 3Y 6HR CTR 6000 48G 4SFP SVC
H53B1E	HPE Aruba Networking Foundational Care 3Y 6HR CTR 6000 48G CL4 4SFP SVC
H55F6E	HPE Aruba Networking Foundational Care 3Y 6HR CTR CDMR 6000 12G CL4 2SFP SVC
H54S5E	HPE Aruba Networking Foundational Care 3Y 6HR CTR CDMR 6000 24G 4SFP SVC
H54D4E	HPE Aruba Networking Foundational Care 3Y 6HR CTR CDMR 6000 24G CL4 4SFP SVC
H53Q3E	HPE Aruba Networking Foundational Care 3Y 6HR CTR CDMR 6000 48G 4SFP SVC

H53B2E	HPE Aruba Networking Foundational Care 3Y 6HR CTR CDMR 6000 48G CL4 4SFP SVC
H82N2E	HPE Aruba Networking Foundational Care 3Y 24x7 CDMR 6000 48G 740W SVC
H82N4E	HPE Aruba Networking Foundational Care 3Y CTR 6000 48G 740W SVC
H82N5E	HPE Aruba Networking Foundational Care 3Y CTR CDMR 6000 48G 740W SVC
H82M6E	HPE Aruba Networking Foundational Care 3Y NBD 6000 48G 740W SVC
H82M7E	HPE Aruba Networking Foundational Care 3Y NBD CDMR 6000 48G 740W SVC
H55E5E	HPE Aruba Networking Foundational Care 3Y NBD Exch 6000 12G CL4 2SFP SVC
H54R4E	HPE Aruba Networking Foundational Care 3Y NBD Exch 6000 24G 4SFP SVC
H54C3E	HPE Aruba Networking Foundational Care 3Y NBD Exch 6000 24G CL4 4SFP SVC
H53P2E	HPE Aruba Networking Foundational Care 3Y NBD Exch 6000 48G 4SFP SVC
H82M4E	HPE Aruba Networking Foundational Care 3Y NBD Exch 6000 48G 740W SVC
H53A1E	HPE Aruba Networking Foundational Care 3Y NBD Exch 6000 48G CL4 4SFP SVC
H55E4E	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 6000 12G CL4 2SFP SVC
H54R3E	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 6000 24G 4SFP SVC
H54C2E	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 6000 24G CL4 4SFP SVC
H53P1E	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 6000 48G 4SFP SVC
H53A0E	HPE Aruba Networking Foundational Care 3Y NBD Exch HW Only 6000 48G CL4 4SFP SVC
H82M3E	HPE Aruba Networking Foundational Care 3Y NBD Exch Hardware Only 6000 48G 740W SVC
H55L9E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T1 6000 12G CL4 2SFP SVC
H54X8E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T1 6000 24G 4SFP SVC
H54J7E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T1 6000 24G CL4 4SFP SVC
H53V6E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T1 6000 48G 4SFP SVC
H82T8E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T1 6000 48G 740W SVC
H53G5E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T1 6000 48G CL4 4SFP SVC
H55M0E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T2 6000 12G CL4 2SFP SVC
H54X9E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T2 6000 24G 4SFP SVC
H54J8E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T2 6000 24G CL4 4SFP SVC
H53V7E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T2 6000 48G 4SFP SVC
H82T9E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T2 6000 48G 740W SVC
H53G6E	HPE Aruba Networking Foundational Care 3Y NBD Exch Vol T2 6000 48G CL4 4SFP SVC
H55E7E	HPE Aruba Networking Foundational Care 3Y NBD Onsite 6000 12G CL4 2SFP SVC
H54R6E	HPE Aruba Networking Foundational Care 3Y NBD Onsite 6000 24G 4SFP SVC
H54C5E	HPE Aruba Networking Foundational Care 3Y NBD Onsite 6000 24G CL4 4SFP SVC

H53P4E	HPE Aruba Networking Foundational Care 3Y NBD Onsite 6000 48G 4SFP SVC
H53A3E	HPE Aruba Networking Foundational Care 3Y NBD Onsite 6000 48G CL4 4SFP SVC
H55E8E	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 6000 12G CL4 2SFP SVC
H54R7E	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 6000 24G 4SFP SVC
H54C6E	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 6000 24G CL4 4SFP SVC
H53P5E	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 6000 48G 4SFP SVC
H53A4E	HPE Aruba Networking Foundational Care 3Y NBD Onsite CDMR 6000 48G CL4 4SFP SVC
H55H2E	HPE Aruba Networking Foundational Care 5Y 4HR Exch 6000 12G CL4 2SFP SVC
H54U1E	HPE Aruba Networking Foundational Care 5Y 4HR Exch 6000 24G 4SFP SVC
H54F0E	HPE Aruba Networking Foundational Care 5Y 4HR Exch 6000 24G CL4 4SFP SVC
H53R9E	HPE Aruba Networking Foundational Care 5Y 4HR Exch 6000 48G 4SFP SVC
H82Q1E	HPE Aruba Networking Foundational Care 5Y 4HR Exch 6000 48G 740W SVC
H53C8E	HPE Aruba Networking Foundational Care 5Y 4HR Exch 6000 48G CL4 4SFP SVC
H55Q3E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T1 6000 12G CL4 2SFP SVC
H55B2E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T1 6000 24G 4SFP SVC
H54N1E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T1 6000 24G CL4 4SFP SVC
H53Z0E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T1 6000 48G 4SFP SVC
H82X2E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T1 6000 48G 740W SVC
H53K9E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T1 6000 48G CL4 4SFP SVC
H55Q4E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T2 6000 12G CL4 2SFP SVC
H55B3E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T2 6000 24G 4SFP SVC
H54N2E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T2 6000 24G CL4 4SFP SVC
H53Z1E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T2 6000 48G 4SFP SVC
H82X3E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T2 6000 48G 740W SVC
H53L0E	HPE Aruba Networking Foundational Care 5Y 4HR Exch Vol T2 6000 48G CL4 4SFP SVC
H55H8E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 6000 12G CL4 2SFP SVC
H54U7E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 6000 24G 4SFP SVC
H54F6E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 6000 24G CL4 4SFP SVC
H53S5E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 6000 48G 4SFP SVC
H82Q7E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 6000 48G 740W SVC
H53D4E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite 6000 48G CL4 4SFP SVC
H55H9E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 6000 12G CL4 2SFP SVC
H54U8E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 6000 24G 4SFP SVC

H54F7E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 6000 24G CL4 4SFP SVC
H53S6E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 6000 48G 4SFP SVC
H53D5E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite CDMR 6000 48G CL4 4SFP SVC
H55H7E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 6000 12G CL4 2SFP SVC
H54U6E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 6000 24G 4SFP SVC
H54F5E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 6000 24G CL4 4SFP SVC
H53S4E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 6000 48G 4SFP SVC
H53D3E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite HW Only 6000 48G CL4 4SFP SVC
H82Q6E	HPE Aruba Networking Foundational Care 5Y 4HR Onsite Hardware Only 6000 48G 740W SVC
H55J1E	HPE Aruba Networking Foundational Care 5Y 6HR CTR 6000 12G CL4 2SFP SVC
H54VOE	HPE Aruba Networking Foundational Care 5Y 6HR CTR 6000 24G 4SFP SVC
H54F9E	HPE Aruba Networking Foundational Care 5Y 6HR CTR 6000 24G CL4 4SFP SVC
H53S8E	HPE Aruba Networking Foundational Care 5Y 6HR CTR 6000 48G 4SFP SVC
H53D7E	HPE Aruba Networking Foundational Care 5Y 6HR CTR 6000 48G CL4 4SFP SVC
H55J2E	HPE Aruba Networking Foundational Care 5Y 6HR CTR CDMR 6000 12G CL4 2SFP SVC
H54V1E	HPE Aruba Networking Foundational Care 5Y 6HR CTR CDMR 6000 24G 4SFP SVC
H54GOE	HPE Aruba Networking Foundational Care 5Y 6HR CTR CDMR 6000 24G CL4 4SFP SVC
H53S9E	HPE Aruba Networking Foundational Care 5Y 6HR CTR CDMR 6000 48G 4SFP SVC
H53D8E	HPE Aruba Networking Foundational Care 5Y 6HR CTR CDMR 6000 48G CL4 4SFP SVC
H82Q8E	HPE Aruba Networking Foundational Care 5Y 24x7 CDMR 6000 48G 740W SVC
H82R0E	HPE Aruba Networking Foundational Care 5Y CTR 6000 48G 740W SVC
H82R1E	HPE Aruba Networking Foundational Care 5Y CTR CDMR 6000 48G 740W SVC
H82Q2E	HPE Aruba Networking Foundational Care 5Y NBD 6000 48G 740W SVC
H82Q3E	HPE Aruba Networking Foundational Care 5Y NBD CDMR 6000 48G 740W SVC
H55H1E	HPE Aruba Networking Foundational Care 5Y NBD Exch 6000 12G CL4 2SFP SVC
H54U0E	HPE Aruba Networking Foundational Care 5Y NBD Exch 6000 24G 4SFP SVC
H54E9E	HPE Aruba Networking Foundational Care 5Y NBD Exch 6000 24G CL4 4SFP SVC
H53R8E	HPE Aruba Networking Foundational Care 5Y NBD Exch 6000 48G 4SFP SVC
H82Q0E	HPE Aruba Networking Foundational Care 5Y NBD Exch 6000 48G 740W SVC
H53C7E	HPE Aruba Networking Foundational Care 5Y NBD Exch 6000 48G CL4 4SFP SVC
H55H0E	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 6000 12G CL4 2SFP SVC
H54T9E	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 6000 24G 4SFP SVC
H54E8E	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 6000 24G CL4 4SFP SVC

H53R7E	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 6000 48G 4SFP SVC
H53C6E	HPE Aruba Networking Foundational Care 5Y NBD Exch HW Only 6000 48G CL4 4SFP SVC
H82P9E	HPE Aruba Networking Foundational Care 5Y NBD Exch Hardware Only 6000 48G 740W SVC
H55P9E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T1 6000 12G CL4 2SFP SVC
H55A8E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T1 6000 24G 4SFP SVC
H54M7E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T1 6000 24G CL4 4SFP SVC
H53Y6E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T1 6000 48G 4SFP SVC
H82W8E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T1 6000 48G 740W SVC
H53K5E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T1 6000 48G CL4 4SFP SVC
H55Q0E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T2 6000 12G CL4 2SFP SVC
H55A9E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T2 6000 24G 4SFP SVC
H54M8E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T2 6000 24G CL4 4SFP SVC
H53Y7E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T2 6000 48G 4SFP SVC
H82W9E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T2 6000 48G 740W SVC
H53K6E	HPE Aruba Networking Foundational Care 5Y NBD Exch Vol T2 6000 48G CL4 4SFP SVC
H55H3E	HPE Aruba Networking Foundational Care 5Y NBD Onsite 6000 12G CL4 2SFP SVC
H54U2E	HPE Aruba Networking Foundational Care 5Y NBD Onsite 6000 24G 4SFP SVC
H54F1E	HPE Aruba Networking Foundational Care 5Y NBD Onsite 6000 24G CL4 4SFP SVC
H53S0E	HPE Aruba Networking Foundational Care 5Y NBD Onsite 6000 48G 4SFP SVC
H53C9E	HPE Aruba Networking Foundational Care 5Y NBD Onsite 6000 48G CL4 4SFP SVC
H55H4E	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 6000 12G CL4 2SFP SVC
H54U3E	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 6000 24G 4SFP SVC
H54F2E	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 6000 24G CL4 4SFP SVC
H53S1E	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 6000 48G 4SFP SVC
H53D0E	HPE Aruba Networking Foundational Care 5Y NBD Onsite CDMR 6000 48G CL4 4SFP SVC
H55E1E	HPE Aruba Networking Software+Technical Support 1Y 6000 12G CL4 2SFP SVC
H54R0E	HPE Aruba Networking Software+Technical Support 1Y 6000 24G 4SFP SVC
H54B9E	HPE Aruba Networking Software+Technical Support 1Y 6000 24G CL4 4SFP SVC
H53N8E	HPE Aruba Networking Software+Technical Support 1Y 6000 48G 4SFP SVC
H52Z7E	HPE Aruba Networking Software+Technical Support 1Y 6000 48G CL4 4SFP SVC
H55L4E	HPE Aruba Networking Software+Technical Support 1Y Vol T2 6000 12G CL4 2SFP SVC
H54X3E	HPE Aruba Networking Software+Technical Support 1Y Vol T2 6000 24G 4SFP SVC
H54J2E	HPE Aruba Networking Software+Technical Support 1Y Vol T2 6000 24G CL4 4SFP SVC

H53V1E	HPE Aruba Networking Software+Technical Support 1Y Vol T2 6000 48G 4SFP SVC
H53G0E	HPE Aruba Networking Software+Technical Support 1Y Vol T2 6000 48G CL4 4SFP SVC
H55F4E	HPE Aruba Networking Software+Technical Support 3Y 6000 12G CL4 2SFP SVC
H54S3E	HPE Aruba Networking Software+Technical Support 3Y 6000 24G 4SFP SVC
H54D2E	HPE Aruba Networking Software+Technical Support 3Y 6000 24G CL4 4SFP SVC
H53Q1E	HPE Aruba Networking Software+Technical Support 3Y 6000 48G 4SFP SVC
H53B0E	HPE Aruba Networking Software+Technical Support 3Y 6000 48G CL4 4SFP SVC
H55M9E	HPE Aruba Networking Software+Technical Support 3Y Vol T2 6000 12G CL4 2SFP SVC
H54Y8E	HPE Aruba Networking Software+Technical Support 3Y Vol T2 6000 24G 4SFP SVC
H54K7E	HPE Aruba Networking Software+Technical Support 3Y Vol T2 6000 24G CL4 4SFP SVC
H53W6E	HPE Aruba Networking Software+Technical Support 3Y Vol T2 6000 48G 4SFP SVC
H53H5E	HPE Aruba Networking Software+Technical Support 3Y Vol T2 6000 48G CL4 4SFP SVC
H55J0E	HPE Aruba Networking Software+Technical Support 5Y 6000 12G CL4 2SFP SVC
H54U9E	HPE Aruba Networking Software+Technical Support 5Y 6000 24G 4SFP SVC
H54F8E	HPE Aruba Networking Software+Technical Support 5Y 6000 24G CL4 4SFP SVC
H53S7E	HPE Aruba Networking Software+Technical Support 5Y 6000 48G 4SFP SVC
H53D6E	HPE Aruba Networking Software+Technical Support 5Y 6000 48G CL4 4SFP SVC
H55Q9E	HPE Aruba Networking Software+Technical Support 5Y Vol T2 6000 12G CL4 2SFP SVC
H55B8E	HPE Aruba Networking Software+Technical Support 5Y Vol T2 6000 24G 4SFP SVC
H54N7E	HPE Aruba Networking Software+Technical Support 5Y Vol T2 6000 24G CL4 4SFP SVC
H53Z6E	HPE Aruba Networking Software+Technical Support 5Y Vol T2 6000 48G 4SFP SVC
H53L5E	HPE Aruba Networking Software+Technical Support 5Y Vol T2 6000 48G CL4 4SFP SVC

HPE Aruba Networking Services

HPE Aruba Networking services simplify and accelerate the network technology lifecycle, enabling your network to scale with better predictability and cost-effectiveness. Whether you operate your own network and need to improve your IT efficiencies, or you want to offload some of the burden, we have the services you need to reach your goals.

Learn more about what HPE Services - Aruba Networking has to offer at: hpe.com/edge/services

Support Services

Our support portfolio provides the essential support elements as well as proactive and preventive features to help you improve your team's productivity and get the most from your network. Our support customers benefit from faster issue resolution, simplified operations and efficiencies, and reduced network issues.

Professional Services

With deep intellectual capital and purpose-built tools, our team delivers a range of standard and custom professional services designed to accelerate your value from HPE Aruba Networking technology.

Project based services include:

- Planning, audit, and assessment
- Architecture review and design
- Deployment, migration, and knowledge transfer

Annual subscription services include:

- Network optimization
- Intelligent Operations
- Customer Experience Management

Our [Education Services](#) allow your team to come up to speed quickly.

GreenLake for Networking

Deliver innovative business outcomes by leveraging new ways to consume, deploy and [manage networks](#).

[For additional technical information, available models and options, please reference the QuickSpecs](#)

Visit [HPE.com](https://www.hpe.com)

[Chat now](#)

© Copyright 2026 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Arm is a registered trademark of Arm Limited. sFlow is a registered trademark of InMon Corp. All third-party marks are property of their respective owners.

Image may differ from the actual product.

[PSN1014098570USEN](#), June, 2026.

HEWLETT PACKARD ENTERPRISE

[hpe.com](https://www.hpe.com)

