

35ft (10.7m) Performance Series AOC High Speed HDMI® Cable **SKU: C2G41483**



The cable's fiber strand construction reduces the risk of EMI/RFI, making performance stable when used in high interference environments such as data centers, surgical theaters, or manufacturing facilities where high resolution and consistent displays are critical.

- Supports High Speed resolutions up to 4K (4096 x 2160) at 60Hz, which means higher quality video for viewing your screen content
- Plenum-rated jacket designed for use in spaces above dropped ceilings or beneath raised floors in schools, hospitals, and other commercial buildings
- Integrated finger grips on the connectors for easy insertion and removal
- Gripping connector shell has 2x greater port retention to keep your devices connected
- Gold plated connectors for increased electrical conductivity and enhanced durability
- Directional cable with source connector labeled and tagged to easily differentiate from the labeled display connector

Specifications

Dimensions & Measurements	Bend Radius	2.76 in (70 mm)
	Cable Diameter	0.19 in (4.8 mm)
	Cable Length	35 ft (10.7 m)
	Shipping Weight	0.97 lbs (0.4 kg)
Characteristics & Features	Cable Type	HDMI
	Color	Black
	Connector 1	(1) HDMI Male
	Connector 2	(1) HDMI Male
	HDMI Type	Active Optical
	Jacket Rating	Plenum Rated
	Signal Type	HDMI
	TAA Compliant	No
	UPC	757120414834
	Video Resolution	4K @ 60Hz
Certifications & Warranties	Certifications	• NDAA 889 • Prop 65 • REACH • RoHS • TSCA
	Data Transfer Rate	18 GBPS
	Warranty	5 years

Source: https://www.legrandav.com/products/hdmi/hdmi_cables/c2g-performance-series-hdmi/c2g41483