


OVERVIEW



1. Power-in	4. USB-B, USB upstream
2. HDMI 2.1 TMDS	5. DisplayPort 1.4 (Supports 3-in-1 ports to connect Tiny)
3. DisplayPort 1.4	6. USB-A (USB 5Gbps), USB upstream / downstream

PERFORMANCE

Panel

Panel

4-side Ultra Thin, In-Plane Switching

Backlight

WLED

Display Size

27 inches

Max View Area

- Active Area: 596.7 x 335.7 mm
- Screen Dimension: 608.8 x 352.4 mm

Resolution

2560 x 1440

Aspect Ratio

16:9

Pixel Pitch

0.2331 x 0.2331 mm

Dot / Pixel Per Inch

109 dpi

Brightness

350 cd/m²

Contrast Ratio

- Contrast Ratio (Typical): 1500:1
- Dynamic Contrast Ratio (Typical): 3000000:1

View Angle (H / V)

Horizontal: 178°, Vertical: 178°

Response Time

- Extreme Mode: 4 ms
- Normal Mode: 6 ms

Refresh Rate

48Hz - 120Hz

Color Gamut

- Coverage Ratio: 99% sRGB (CIE 1931)
- Coverage Ratio: 99% BT.709 (CIE 1931)

Color Support

16.7 Million

Color Depth

True 8-bit

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Operating System

Operating System

- Windows® 11 Support
- Windows® 10 Support

Multi-Media

Camera

5.0MP + IR

Microphone

Integrated microphone

Speakers

Integrated Speakers, 3W x2

Power Supply

Power Consumption

- Sleep / Off mode: <0.5W
- Switch-off Mode: <0.3W
- External, Power Brick (170W)
- Typical / Max: 22W / 60W
- Energy Star Power On: 18.5W
- Energy Star TEC: 59.6kWh

Voltage Required

AC 100 to 240 V (50-60Hz)

Special Features

Special Features

- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager)^[1]
- LDFM (Lenovo® Display Fleet Manager)
- Mirrored Power Button
- Natural Low Blue Light
- QHD Support VRR (HDMI®)
- Factory Calibration: Avg. Delta E<4 at sRGB

Notes:

[1] Formerly Lenovo® Display Control Center. Supports Windows® 10 & 11, Mac OS (functions vary across systems).

DESIGN

Display

Touchscreen

Non-touch

Mechanical

ThinkCentre® M Series Support

ThinkCentre® Tiny, ThinkStation® Tiny

Bezel Width

- Thickness of Head: 20.0mm
- Side: 2.0mm
- Top: 2.0mm
- Bottom: 41.6mm

Cable Management

Support

Case Color

Eclipse black

Dimensions (WxDxH)^[1]

Models	Dimensions
Lowest Position	613.6 x 212.0 x 447.2 mm (24.16 x 8.35 x 17.61 inches)
Highest Position	613.6 x 212.0 x 602.2 mm (24.16 x 8.35 x 23.71 inches)
Head Only	613.6 x 79.5 x 404.7 (24.16 x 3.13 x 15.93 inches)

Packaging Dimensions (WxDxH)

692.0 x 156.0 x 526.0 mm (27.24 x 6.14 x 20.71 inches)

Weight^[2]

Models	Weight
Monitor With Stand	7.2 kg (15.9 lbs)
Monitor Head Only	4.5 kg (9.9 lbs)

Packaging Weight

10.4 kg (22.9 lbs)

Mounting

Supports VESA mount 100 x 100 mm

Stand

Full function monitor stand, supports -5° to +23.5° tilt, left & right 45° swivel, up to 155mm lift, 0° to +90° pivot

In the Box

- Monitor with stand
- Power cable (1.0 m)^[3]
- Quick setup guide
- Power Brick (170W)

Notes:

- [1] The system dimensions may vary depending on configurations.
- [2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
- [3] Model with the “WL” suffix is shipped without a power cable.

CONNECTIVITY

Ports^[1]

Rear Ports

- 1x USB-B (USB 5Gbps / USB 3.2 Gen 1), USB upstream
- 1x HDMI® 2.1 TMDS^[2]
- 1x DisplayPort™ 1.4
- 1x DisplayPort™ 1.4(Supports 3-in-1 ports to connect Tiny)

Left Ports

1x USB-A (USB 5Gbps / USB 3.2 Gen 1, supports 3-in-1 ports to connect Tiny), USB downstream / USB upstream

Notes:

- [1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
- USB 2.0: 480 Mbit/s;
- USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
- USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
- USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
- USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;
- Thunderbolt™ 3/4: 40 Gbit/s.
- Thunderbolt™ 5: 80 Gbit/s (bidirectional), up to 120 Gbit/s in bandwidth boost mode for video-intensive applications.
- [2] Supports 2560x1440@120Hz as specified in HDMI® 2.1

SECURITY & PRIVACY

Security

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

SERVICE

Warranty

Base Warranty

3-year limited warranty

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- ENERGY STAR® Certified
- EPEAT™ Gold Registered
- EU Energy Label (E-class)
- RoHS (2011/65/EU)
- TCO Certified, generation 10
- TCO Certified Edge 2.1
- Volatile Organic Compound Certification

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications

Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Eye Comfort Certification (5-star)
- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS", WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

