IFP6563 - 65" PCAP 4K 16:9 ANDROID EDLA-CERTIFIED VIEWBOARD INTERACTIVE FLAT PANEL DISPLAY WITH INTEGRATED MICROPHONE AND USB-C

Key **Features**

- Enterprise-Grade Security
- Optimized for IT Management
- Engaging Meetings with ViewSonic® Software
- Ultra-Responsive PCAP Touch for Seamless Collaboration
- Instantaneous Collaboration
- Easy Access with Quick User Authentication
- Flexible Camera Integration



65"
DISPLAY

PANEL

RESOLUTION



Product **Description**

Elevate every meeting with the ViewSonic® ViewBoard® IFP6563 – a 65” interactive flat panel display designed to power productivity in modern boardrooms, conference spaces, and hybrid workflows. Featuring ultra-responsive Projected Capacitive (PCAP) touch technology and a stunning bezel-less 4K display, it ensures smooth, precise interactions and crystal-clear visuals that keep teams engaged. Built on the latest Android™ EDLA platform, it delivers enhanced security, seamless app integration, and future-proof performance. From dynamic brainstorming to high-stakes presentations, the IFP6563 combines enterprise-grade tools with intuitive design to make every session more efficient and impactful. Backed by ViewSonic’s robust software ecosystem and engineered for 24/7 reliability, this display is your scalable solution for driving collaboration, streamlining operations, and staying ahead in a fast-moving business world.

Specifications

More Information	
UPC	766907034226
OS	ViewBoard OS EDLA
GPU	Rockchip RK3576
Memory	16GB LPDDR
Storage	128GB eMMC
Microphone	Beamforming array x 8, full duplex echo cancellation
Internal Speakers	20W (x2)
Subwoofer	20W (x1)
HDMI 2.1 In	4
HDMI Out	1
DisplayPort	1
SPDIF	1
USB Type A	5
USB Type B	3
USB Type C	4 (up to 100W Power Delivery)
RS232	1
Ethernet LAN (RJ45)	2
Line In	1
Voltage	100-240 VAC
Stand-by	<0.5W
Temperature	32-104º F (0 - 40º C)
Non-Operating Temperature	-4°F to 140°F (-20C to 60C)
Humidity (non-condensing)	20-80%
Touch Technology	Projective Capacitive
Touch Points	Windows: 50, Android: 20
Latency	≤10ms
VESA Compatible	600 x 400 mm
NFC	Yes
Warranty	3-year limited warranty on parts, labor and backlight, onsite warranty
Recycle/Disposal	Please dispose of in accordance with local, state or federal laws.
Package Contents	IFP6563, Power Cord (3m), USB-C Cable (1.8m), Remote control, USB Touch Cable (3m), Stylus x 2, Quick Start Guide + Compliance statement, RS232 adapter, Clamp x 5, Camera Plate, Screw x 8 (camera 2+2, wall mount 4), HDMI cable 3m, VB-WIFI-005 WiFi Adapter
Regulations	CTUVus, FCC, Energy 8.0, EPEAT, CEC

Ethernet LAN	(10/100/1000M) (USB Type-C 10/100, Android & PC 10/100/1000)
Wifi	VB-WIFI-005 adapter, 802.11AX + Bluetooth 5.2
Screen Size	65"
Light Source	DLED
Display Resolution	3840 x 2160
Refresh Rate	60Hz
Aspect Ratio	16:9
Static Contrast Ratio	5,000:1
Dynamic Contrast Ratio	5,000:1
Brightness	450 cd/m2
Response Time (Typical GTG)	6.5ms
Viewing Angles	178º horizontal, 178º vertical
Panel Surface	Anti Glare + Anti Flare + Anti-bacteria (9H pencil hardness, 3mm thickness)

UPC: 766907034226







Contact Sales
ViewSonic.com
888.881.8781
email:
salesinfo@viewsonic.com