Specifications



Eaton UR038-001

Reversible USB-A to USB-C Cable, USB 2.0, White Silicone Jacket, 1-ft (0.3 m)

General specifications	
PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	UR038-001
UPC	037332304308
PRODUCT LENGTH/DEPTH	0.25 in
PRODUCT HEIGHT	8 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	0.04 lb
WARRANTY	Limited lifetime
COMPLIANCES	CE Marked REACH RoHS UKCA
GLOBAL CATALOG	UR038-001
PRODUCT TYPE	Cable

Powering Business Worldwide

Product specifications

AMPERAGE RATING	2A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	FT2
CABLE JACKET COLOR	White
CONNECTOR COLOR	White
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	Silicone
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Reversible plugs on both ends connect in either direction for immediate no-fuss use USB 2.0 cable supports data transfer rates up to 480 Mbps Flexible silicone cable jacket bends easily for connecting around corners Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
TECHNOLOGY	USB 2.0 (High Speed)
CABLE LENGTH	1 Foot
MAXIMUM INPUT WATTS	10 W
CABLE OUTER DIAMETER (OD)	4.5 mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-C USB-A
WIRE GAUGE (AWG)	28/20
CONNECTOR	USB C (male) USB A (male)

Resources

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.