

Server Rack PDU with 24 outlets - 0U

Product ID: RKPW247015



This 24 outlet rackmount power strip provides a 0U solution for your rackmount equipment and fits most 42U racks and equipment cabinets. The 10ft power cord provides plenty of reach to power outlets, and the 24 evenly spaced outlets help keep power cabling clean and efficiently routed.

Certifications, Reports and Compatibility

Applications

Features

- Provides 24 (120V 15A) power outlets
- Mounts vertically, taking up 0U of rack space
- 10 ft (3 m) power cord

Hardware

Warranty	Lifetime
Number of Power Outlets	24
Form Factor	Vertical
Rack-Mountable	Yes

Performance

Maximum Total Current	15A
Maximum Total Current Draw per Phase	15A
Regulatory Derated Input Current (North America)	12A
Nominal Input Voltage	120V
Nominal Output Voltage	120V
Maximum Output Voltage	125V

Connector(s)

Input Connector(s)	NEMA 5-15 Power (North America)
Output Connectors	NEMA 5-15 Power (North America)

Power

Input Voltage	120 AC
---------------	--------

Physical Characteristics

Color	Black
Material	Steel
Cable Length	10.0 ft [3.0 m]
Product Length	1.5 in [38.0 mm]
Product Width	1.0 in [25.0 mm]
Product Height	6.0 ft [1.8 m]
Weight of Product	3.3 lb [1.5 kg]

Packaging Information

Package Length	6.1 ft [1.9 m]
Package Width	2.3 in [58.0 mm]
Package Height	3.0 in [76.0 mm]
Shipping (Package) Weight	4.4 lb [2.0 kg]



**What's in the
Box**

Included in Package	24 Outlet PDU
	Mounting Bracket
	Backing Plate
	Bag of Screws

****Product appearance and specifications are subject to change without notice.***

