



**C2G**  
**3.3ft (1m) USB 2.0 A/B Cable - Black**  
Part No. CG-28101



Just plug-and-play for keyboards, mice, modems, printers, and other USB peripherals. This cable provides a transfer rate up to 480 Mbps depending upon the peripheral's USB version, and easily attaches to any USB device. Foil and braid shielding reduces EMI/RFI interference and twisted pair construction helps reduce crosstalk thus ensuring high speed, error-free data transfer.

## Features & Benefits

Easily connect a USB Hub, Keyboard or Mouse to a computer  
PC and Mac® compatible

Supports high speed USB 2.0 and 1.1 devices  
Available in lengths up to 5m

## Specifications

### General Info

Product Line	C2G	Color	Black
UPC Number	757120281016	Country Of Origin	VietNam
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Cable		

### Dimensions

Cable Length	3.3 ft
--------------	--------

### Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

### Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Cable Type	USB	Data Transfer Rate	480 Mbps
Adapter Rear	USB-B Male	Adapter Front	USB-A Male