

6 ft Coax Low Profile High Resolution Monitor VGA Cable HD15 M/M

Product ID: MXT101MMLP6



StarTech.com's premium VGA Cables are designed to provide the highest video quality available through VGA.

This 6ft super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality VGA cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Extends VGA/SVGA monitor cable
- Lightweight video cable for laptop

Features

- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

Connector(s)

Warranty

Lifetime

Connector A VGA (15 pin, High Density D-Sub)

Connector B VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature -5~+70

Storage Temperature -10~+80 best (25)

Humidity 0~70%

Physical Characteristics

Color Black

Cable Length 6.0 ft [1.8 m]

Product Length 6.0 ft [1.8 m]

Weight of Product 3.6 oz [101 g]

Packaging Information

Package Length 8.9 in [22.5 cm]

Package Width 4.9 in [12.5 cm]

Package Height 0.5 in [12 mm]

Shipping (Package) Weight 3.7 oz [106 g]

What's in the Box

Included in Package 6 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M

**Product appearance and specifications are subject to change without notice.*

