

Product data sheet

Specifications

APC Network SurgeArrest, 7 outlet

NET7



⚠ Discontinued on: Feb 14, 2024

⚠ To be discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	6 ft (1.8 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Beige
Height	2.008 in (5.1 cm)
Width	4.3 in (10.8 cm)
Depth	10.5 in (26.7 cm)
Net Weight	2.006 lb(US) (0.91 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1283 UL 1363 UL 1449

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Equipment protection policy	Lifetime : \$100000
-----------------------------	---------------------

Environmental

Ambient Air Temperature for Operation	32.0000000000...104.0000000000 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

eP Joule Rating	3420 J
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	70 dB
Peak current	26 kAcommon mode 13 kAnormal mode
Surge energy rating	1680 J

Ordering and shipping details

GTIN	731304000204
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.09 in (5.3 cm)
Package 1 Width	12.8 in (32.4 cm)
Package 1 Length	7.2 in (18.4 cm)
Package 1 Weight	2.31 lb(US) (1.05 kg)
SCC14	10731304000201

Contractual warranty

Warranty	Limited Lifetime
----------	------------------