

Product data sheet

Specifications



APC NetShelter 13U Wallmount Rack Cabinet Glass Door Double Hinged Server Depth

AR100

Overview

Presentation Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack hinges at the rear allowing for access to the back of the rack during installation and setup or while undergoing maintenance. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top-mounted and caster kit. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 13U Wall mount cabinet, 19 inches maximum mounting depth, 200lb weight capacity, 19" rack width, ships fully assembled, glass door, 5 year APC warranty.

Lead time Usually in Stock

Main

number of rack unit 13U

Number of cables 1

Provided equipment Key(s)
User Manual
Wall-mounting template

Physical

Color Black

Height 26.1 in (66.3 cm)

Width 23.0 in (58.4 cm)

Depth 24.8 in (63.1 cm)

Net Weight 94.20 lb(US) (42.73 kg)

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 19.0000000000 in (48.26 cm)

rack width 19"

Marking 16 gauge EIA mounting rail
16 gauge front door
16 gauge post
13 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load 200 lb(US) (90.7 kg) static

Conformance

Standards EIA-310E

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

GTIN 731304111429

Country of origin TH

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 33.0 in (83.8 cm)

Package 1 Width 27.008 in (68.6 cm)

Package 1 Length 30.5 in (77.5 cm)

Package 1 Weight 114.99 lb(US) (52.16 kg)

Contractual warranty

Warranty 5 year repair or replace

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back RoHS/REACH

Resource performance

Take-Back Program Available

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
