

Product data sheet

Specifications



APC Workshop SurgeArrest 7 Outlets



PDIY7

 Discontinued on: Feb 14, 2024

! To be end-of-service on: Sep 30, 2024

① To be discontinued

Overview

Lead time Usually Ships within 8 Weeks

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	8 ft (2.4 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Yellow
Height	15.0 in (38 cm)
Width	2.8 in (7 cm)
Depth	1.8 in (4.5 cm)
Net Weight	1.59 lb(US) (0.72 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase 15 A

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : \$5000

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

Ambient Air Temperature for Operation	32.0000000000...104.0000000000 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

eP Joule Rating	820 J
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	20 dB
Peak current	12 kAcommon mode 6 kAnormal mode
Surge energy rating	800 J

Ordering and shipping details

GTIN	731304238324
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 in (38 cm)
Package 1 Width	2.008 in (5.1 cm)
Package 1 Length	4.3 in (10.9 cm)
Package 1 Weight	1.1 lb(US) (0.5 kg)

SCC14 10731304238321

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

 Reach Free Of Svhc

 Mercury Free

 RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)