

CineTension 2 Dimensions Table (Inches)

Model Number	Screen Diag.	Aspect Ratio	Case Length (A)	View Width (A1)	Screen Width (A2)	Weight Bar Length (A3)	Overall Height w/ Bracket (B)	View Height (B1)	(B2)	Overall Height (B3)	Bottom Edge (B4)	Case Height (B5)	(B6)	Top Black Masking (B8)	Case Width (C)	(C1)	(C2)	G1	G2	G3	G4	G5	G6	G7	G8
Unit: Inch																									
TE92HC2	92"	16:9	96.0	80.2	87.7	91.5	61.5	45.1	54.8	59.6	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE100VW2	100"	4:3	96.0	80.0	87.5	91.5	76.5	60.0	69.8	74.5	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE100VW2-E12	100"	4:3	96.0	80.0	87.5	91.5	82.5	60.0	75.8	80.5	3.8	4.7	6.7	12.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE106XW2-E24	106"	16:10	107.2	89.9	97.4	102.7	90.7	56.2	84.0	88.7	3.8	4.7	6.7	24.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE120VW2	120"	4:3	113.4	96.0	104.6	108.9	86.5	72.0	79.8	84.5	3.8	4.7	6.7	4.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE125C-E20	125"	2.35:1	132.3	115.0	123.7	127.8	79.4	48.9	72.7	77.4	3.8	4.7	6.7	20.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE128XW2-E12	128"	16:10	125.4	108.5	116.0	120.9	90.3	67.8	83.6	88.3	3.8	4.7	6.7	12.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE135VW2	135"	4:3	125.4	108.0	116.7	120.9	95.5	81.0	88.8	93.5	3.8	4.7	6.7	4.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE150VW2	150"	4:3	138.2	120.0	128.7	133.7	104.5	90.0	97.8	102.5	3.8	4.7	6.7	4.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE153C-E12	153"	2.35:1	158.1	140.8	149.4	153.5	82.4	59.9	75.7	80.4	3.8	4.7	6.7	12.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE84HW2	84"	16:9	89.8	73.2	80.7	84.6	57.6	41.2	50.9	55.7	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE84HW2-E30	84"	16:9	89.8	73.2	80.7	84.6	81.7	41.2	75.0	79.7	3.8	4.7	6.7	30.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE92VW2	92"	4:3	89.8	73.6	81.1	84.6	71.7	55.2	65.0	69.7	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE94XW2	94"	16:10	96.0	79.7	87.2	91.5	66.3	49.8	59.6	64.3	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE96C-E24	96"	2.35:1	105.6	88.3	95.8	101.1	72.1	37.6	65.4	70.1	3.8	4.7	6.7	24.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE84VW2	84"	4:3	83.1	67.2	74.7	78.0	66.9	50.4	60.2	64.9	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE100VW2	100"	4:3	96.0	80.0	87.5	91.5	76.5	60.0	69.8	74.5	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE84HG2	84"	16:9	89.8	73.2	80.7	84.6	57.6	41.2	50.9	55.7	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE84VG2	84"	4:3	83.1	67.2	74.7	78.0	66.9	50.4	60.2	64.9	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE92HG2	92"	16:9	96.0	80.2	87.7	91.5	61.5	45.1	54.8	59.6	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE92VG2	92"	4:3	89.8	73.6	81.1	84.6	71.7	55.2	65.0	69.7	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE120HD2	120"	16:9	122.3	104.6	113.3	117.8	73.3	58.8	66.6	71.3	3.8	4.7	6.7	4.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE92HW2	92"	16:9	96.0	80.2	87.7	91.5	61.5	45.1	54.8	59.6	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE100HW2	100"	16:9	103.0	87.2	94.6	98.4	65.5	49.0	58.8	63.5	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE100HW2-E24	100"	16:9	103.0	87.2	94.6	98.4	83.5	49.0	76.8	81.5	3.8	4.7	6.7	24.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE100HW2-E36	100"	16:9	109.0	87.2	96.6	104.4	95.5	49.0	88.8	93.5	3.8	4.7	6.7	36.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE106HW2	106"	16:9	109.0	92.4	99.9	104.4	68.4	52.0	61.7	66.5	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE106HW2-E24	106"	16:9	109.0	92.4	99.9	104.4	86.5	52.0	79.8	84.5	3.8	4.7	6.7	24.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE110HW2	110"	16:9	113.4	95.9	104.5	108.9	70.4	53.9	63.7	68.4	3.8	4.7	6.7	6.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE110HW2-E36	110"	16:9	115.4	95.9	106.5	110.8	100.4	53.9	93.7	98.4	3.8	4.7	6.7	36.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE120HW2	120"	16:9	122.3	104.6	113.3	117.8	73.3	58.8	66.6	71.3	3.8	4.7	6.7	4.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE120HW2-E36	120"	16:9	126.2	104.6	115.2	121.7	105.3	58.8	98.6	103.3	3.8	4.7	6.7	36.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE135HW2	135"	16:9	135.4	117.7	126.3	130.9	80.7	66.2	74.0	78.7	3.8	4.7	6.7	4.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE135HW2-E20	135"	16:9	135.4	117.7	126.3	130.9	96.7	66.2	90.0	94.7	3.8	4.7	6.7	20.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE150HW2	150"	16:9	149.7	130.7	139.4	145.2	88.0	73.5	81.3	86.1	3.8	4.7	6.7	4.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4
TE150HW2-E20	150"	16:9	149.7	130.7	139.4	145.2	104.1	73.6	97.4	102.1	3.8	4.7	6.7	20.0	4.8	0.9	5.2	3.4	1.9	1.4	0.7	4.1	2.2	0.8	0.4

Note : A3 Data Error ± 2"; A2, B3 Data Error 1.2"; Error of left data be ±1".

The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

