

Product data sheet

Specifications



APC AV 15 Amp G Type Rack Power Filter, 120V



G5BLK

To be discontinued on: Sep 30, 2024

To be discontinued

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Product or Component Type	Power filter
Input Connection Type	NEMA 5-15P
Number of rack unit	1U
Cable length	8 ft (2.4 m)
Number of cables	1
Provided equipment	Rack Mounting brackets User Manual

Physical

Color	Black
Height	1.71 in (4.35 cm)
Width	17.1 in (43.5 cm)
Depth	9.4 in (24 cm)
Net Weight	8.6 lb(US) (3.9 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Switching current capacity	15 A
Maximum Input Current per Phase	15 A

Output

Number of power socket outlets	9
Outlet standard	NEMA 5-15R

Conformance

Standards	UL 1449
-----------	---------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Equipment protection policy	Lifetime : \$450000
UL 1449 TVSS Rating	330

Environmental

Ambient Air Temperature for Operation	32.0000000000...122.0000000000 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage altitude	0...10000 ft (0.0000000000...3048.0000000000 m)
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Let Through Voltage Rating	40 V
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	55 dB
Surge energy rating	3400 J

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304263920
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 in (8.6 cm)
Package 1 Width	13.0 in (33 cm)
Package 1 Length	21.7 in (55.2 cm)
Package 1 Weight	10.63 lb(US) (4.82 kg)
SCC14	20731304263924

Contractual warranty

Warranty	Lifetime
----------	----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)





Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Reach Free Of Svhc

 Lead Free

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)