Grounding Kit (RM2408):

• (6) 8" (20.3-cm) grounding straps

• (12) hex bolts

• This user's manual

3-Fan Unit (RM2409):

• (3) fans in one unit with power cord

• This user's manual

Optional cabinet doors should include the following items:

Optional Curved Mesh Front Door 15U (RMD2511A):

• (1) Fully assembled curved mesh front door, 15U

Optional Curved Mesh Front Door 38U (RMD2512A):

• (1) Fully assembled curved mesh front door, 38U

Optional Curved Mesh Front Door 42U (RMD2513A):

• (1) Fully assembled curved mesh front door, 42U

Optional Split Door 15U (RMTD2501A):

• (1) Fully assembled split door, 15U

Optional Split Door 38U (RMTD2502A):

• (1) Fully assembled split door, 38U

Optional Split Door 42U (RMTD2503A):

• (1) Fully assembled split door, 42U

• (1) user's manual

6-Fan Unit (RM2415):

• (6) fans in one unit with power cord

• This user's manual

3U Cable Access Panel (RM2505):

• (4) 12-24 cup-head screws

• (4) 10-32 cup-head screws

• (1) cable access panel

• (1) user's manual


© Copyright 2009. Black Box Corporation. All rights reserved.



APRIL 2009

RM2500A RM2525A RM2510A RM2530A RM2515A RM2540A RM2520A RM2550A

Select Server Plus Cabinets



SELECT SERVER PLUS CABINETS

TRADEMARKS USED IN THIS MANUAL

Black Box and the Double Diamond logo are registered trademarks of BB Technologies, Inc.

UL is a registered trademark of Underwriters Laboratories Inc.

Any other trademarks mentioned in this manual are acknowledged to be the property of the trademark owners.

Specifications

Capacity: 2250 lb. (1020.6 kg)

Mounting Rails: 19" square hole rails

Compliance: UL® Listed

Interior Height: RM2500A, RM2510A: 26.3" (15U) (66.8 cm); RM2515A, RM2525A: 42.2" (24U) (107.2 cm);

RM2520A, RM2530A: 66.5" (38U) (168.9 cm); RM2540A, RM2550A: 73.5" (42U) (186.7 cm)

Exterior Height: RM2500A, RM2510A: 30.4" (77.2 cm); RM2515A, RM2525A: 46.3" (117.5 cm);

RM2520A, RM2530A: 70.7" (38 U) (179.6 cm); RM2540A, RM2550A: 77.6" (197.1 cm)

NOTE: Exterior height does not include casters.

Interior Width: 21.3" (54.1 cm)

Exterior Width: 23.6" (59.9 cm)

Interior Depth: 38.5" (97.8 cm)

Exterior Depth: 39.4" (100.1 cm)

Overview

The Select Server Plus Cabinet holds your data center servers. It arrives fully assembled and includes keyed door locks and locking side panels for security. The cabinet has a lockable rear split door for easy access in tight spaces. Eight models are available with either mesh or tempered glass front doors.

- Select Server Plus Cabinet, 15U, Mesh (RM2500A)
- Select Server Plus Cabinet, 15U, Tempered Glass (RM2510A)
- Select Server Plus Cabinet, 24U, Mesh (RM2515A)
- Select Server Plus Cabinet, 24U, Tempered Glass (RM2525A)
- Select Server Plus Cabinet, 38U, Mesh (RM2520A)
- Select Server Plus Cabinet, 38U, Tempered Glass (RM2530A)

- Select Server Plus Cabinet, 42U, Mesh (RM2540A)
- Select Server Plus Cabinet, 42U, Tempered Glass (RM2550A)

Optional accessories are also available:

- Multicabinet Joining Kit (RM2407)
- Grounding Kit (RM2408)
- 3-Fan Unit (RM2409)
- 6-Fan Unit (RM2415)
- 3U Cable Access Panel (RM2505)

Optional doors include the following:

- Curved Mesh Front Door, 15U (RMD2511A)
- Curved Mesh Front Door, 38U (RMD2512A)
- Curved Mesh Front Door, 42U (RMD2513A)
- Split Mesh Rear Door, 15U (RMTD2501A)
- Split Mesh Rear Door, 38U (RMTD2502A)
- Split Mesh Rear Door, 42U (RMTD2503A)

What's Included

Your Select Server Plus Cabinet (RM2500A, RM2510A, RM2515A, RM2525A, RM2520A, RM2530A, RM2540A, or RM2550A) package should include the following items. If anything is missing or damaged, please contact Black Box Technical Support at 724-746-5500.

- (1) Select Server Plus Cabinet with attached casters and leg levelers
- (2) sets of panel keys
- (2) sets of door keys
- (1) bag of clip nuts, M6
- (1) bag of screws
- (1) bag of clear plastic washers
- This user's manual

Your optional accessories packages should include the following items:

Multicabinet Joining Kit (RM2407):

- (24) ¾ " (1.9-cm) screws
- (6) joining connectors
- This user's manual