

# Product data sheet

Specifications



## APC Power-Saving Home/Office SurgeArrest, 8 Outlets with Phone Protection, 120V

P8GT

⚠ Discontinued on: Feb 14, 2024

⚠ To be end-of-service on: Sep 30, 2024

⚠ To be discontinued

### Overview

Lead time Usually in Stock

### Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	6 ft (1.8 m)
Number of cables	1
Provided equipment	Telephone Cable User Manual

### Physical

Color	White
Height	10.5 in (26.7 cm)
Width	4.8 in (12.2 cm)
Depth	1.5 in (3.8 cm)
Net Weight	1.21 lb(US) (0.55 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Input Frequency	50/60 Hz
Maximum Input Current per Phase	15 A

### Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

### Conformance

UL 1449 TVSS Rating	400
Product Certifications	ETL
Standards	UL 1449

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Equipment protection policy	Lifetime : \$150000
-----------------------------	---------------------

## Environmental

---

Ambient Air Temperature for Operation	32.0000000000...113.0000000000 °F (0...45 °C)
---------------------------------------	---

---

Relative Humidity	0...95 %
-------------------	----------

---

Operating altitude	0...10000 ft
--------------------	--------------

---

Ambient Air Temperature for Storage	23.0000000000...113.0000000000 °F (-5...45 °C)
-------------------------------------	--

---

Storage Relative Humidity	0...95 %
---------------------------	----------

---

Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
------------------	--

## Surge Protection and Filtering

---

NM Surge Response Time (ns)	1 ns common mode
-----------------------------	------------------

---

Common mode rejection	58 dB
-----------------------	-------

---

Peak current	144 kA common mode
--------------	--------------------

---

Surge energy rating	2160 J
---------------------	--------

## Ordering and shipping details

---

GTIN	731304269229
------	--------------

## Packing Units

---

Unit Type of Package 1	PCE
------------------------	-----

---

Number of Units in Package 1	1
------------------------------	---

---

Package 1 Height	14.3 in (36.2 cm)
------------------	-------------------

---

Package 1 Width	1.7 in (4.4 cm)
-----------------	-----------------

---

Package 1 Length	9.8 in (24.8 cm)
------------------	------------------

---

Package 1 Weight	2.12 lb(US) (0.96 kg)
------------------	-----------------------

---

SCC14	10731304269226
-------	----------------

## Contractual warranty

---

Warranty	Limited Lifetime
----------	------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Circularity Profile [End of Life Information](#)

**California Proposition 65** WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)