

# Product data sheet

Specifications



## Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 1.2m

AP8714R

### Overview

**Presentation** Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

**Lead time** Usually in Stock

### Main

<b>Product or Component Type</b>	Power cord
<b>Input Connection Type</b>	IEC 60320 C20
<b>Cable length</b>	4 ft (1.2 m)
<b>Number of cables</b>	6
<b>Provided Equipment</b>	3 Left-angle jumper cords 3 Right-angle jumper cords

### Physical

<b>Color</b>	Black
<b>Height</b>	11.8 in (30 cm)
<b>Width</b>	2.6 in (6.5 cm)
<b>Depth</b>	2.8 in (7 cm)
<b>Net Weight</b>	3.62 lb(US) (1.64 kg)
<b>Mounting preference</b>	No preference
<b>Mounting Mode</b>	Not rack-mountable

### Input

<b>Max line current</b>	16 A
<b>Input current limits</b>	16 A

### Output

<b>Maximum Total Current Draw per Phase</b>	16 A
<b>Number of power socket outlets</b>	1 IEC 60320 C19
<b>Cord Length</b>	4 ft (1.2 m)

### Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Product Certifications</b>	CCC CSA PSE UL Listed VDE
-------------------------------	---------------------------------------

## Environmental

<b>Ambient Air Temperature for Operation</b>	32.0000000000...167.0000000000 °F (0...75 °C)
<b>Relative Humidity</b>	20...80 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13.0000000000...167.0000000000 °F (-25...75 °C)
<b>Storage Relative Humidity</b>	20...80 %
<b>Storage altitude</b>	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

<b>Category</b>	11309 - APC RESALE PRODUCTS
<b>GTIN</b>	731304279693
<b>Returnability</b>	No

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	11.8 in (30 cm)
<b>Package 1 Width</b>	2.6 in (6.5 cm)
<b>Package 1 Length</b>	2.8 in (7 cm)
<b>Package 1 Weight</b>	3.62 lb(US) (1.64 kg)
<b>Unit Type of Package 2</b>	PAL
<b>Number of Units in Package 2</b>	9
<b>Package 2 Height</b>	56.69 in (143.99 cm)
<b>Package 2 Width</b>	39.4 in (100 cm)
<b>Package 2 Length</b>	47.2 in (120 cm)
<b>Package 2 Weight</b>	32.481 lb(US) (14.733 kg)
<b>Unit Type of Package 3</b>	CAR
<b>Number of Units in Package 3</b>	9
<b>Package 3 Height</b>	9.8 in (25 cm)
<b>Package 3 Width</b>	13.2 in (33.5 cm)
<b>Package 3 Length</b>	22.2 in (56.5 cm)
<b>Package 3 Weight</b>	32.481 lb(US) (14.733 kg)
<b>SCC14</b>	10731304279690

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Take-back Transparency RoHS/REACH

## Resource performance

 Take-Back Program Available

## Well-being performance

 Lead Free

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)