

Product data sheet

Specifications



APC NetShelter AV, Server Rack Enclosure, 42U, 10-32 Threaded Rails, Black, 1991H x 600W x 825D mm

AR3810

Overview

Presentation	Feature-rich enclosure specifically for the professional AV market and optimized for cable management, power distribution, and airflow management.
Lead time	Usually in Stock

Main

Product or Component Type	Rack enclosure
number of rack unit	42U
Provided equipment	Documentation CD Installation guide Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Height	78.4 in (199.1 cm)
Width	23.6 in (60 cm)
Depth	32.5 in (82.5 cm)
Net Weight	263.56 lb(US) (119.55 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	26.73 in (67.89 cm)
rack width	19"
Permanent permissible load	2250 lb(US) (1020.6 kg) dynamic 3000 lb(US) (1360.8 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

Ordering and shipping details

GTIN	731304281436
Country of origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83.5 in (212.1 cm)
Package 1 Width	40.5 in (102.9 cm)
Package 1 Length	29.5 in (74.9 cm)
Package 1 Weight	294.63 lb(US) (133.64 kg)

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH


Resource performance


 Take-Back Program Available

Well-being performance

 Reach Free Of Svhc

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
