



Cat5e Snagless Cables

- Supports voice/data/video distribution applications up to 350 MHz
- Meets all Cat6 TIA/EIA-568-C.2 standards
- Lifetime Warranty



Specifications: Cat5e Snagless Cables

Electrical Specifications:

Conductor DC Resistance:	9.38Ω/100m (maximum)
Impedance:	100Ω
Capacitance:	5600pf/100m
Propagation Delay:	545ns/100m (maximum)
Delay Skew:	45ns/100m (maximum)

Physical Specifications:

Wiring Scheme:	T568B
Temperature Rating:	60°C
Voltage Rating:	30V
Approvals:	CE
Warranty:	Lifetime
Package Type:	Polybag

Conductor (4 pair):


Conductor:	24AWG (7/0.20 BC)
Insulation:	HD-PE ID: $\varnothing 0.95 \pm 0.02$
Twist Pair:	Orange, White/Orange, Blue, White/Blue, Green, White/Green Brown, White/Brown

Connectors (Qty 2):

Connector Type:	8P8C (RJ45)
Gender:	Male
Contacts:	Gold Plated 50μ
Hood:	Molded PVC, UL94V-0

Overall Cable

Jacket:	PVC
OD:	5.3 ± 0.15



Specifications: Cat5e Snagless Cables

Length	Gray	Blue	Black	Green	Red	Yellow	Orange	Purple	White	Pink
6"	00931	00932	00933	00934	00935	00936	00937	00938	00939	00940
1ft	24814	23828	26969	24229	26968	22105	00440	00461	29952	00492
2ft	00383	00392	00401	00410	00420	00430	00441	00462	00482	00493
3ft	15177	15178	15180	15179	15223	15221	00442	00463	19479	00494
4ft	00384	00393	00402	00411	00421	00431	00443	00464	00483	00495
5ft	15187	15188	15189	15185	15190	15191	00444	00465	19477	00496
6ft	00385	00394	00403	00412	00422	00432	00445	00466	00484	00497
7ft	15192	15193	15196	15194	15197	15198	00446	00467	19478	00498
8ft	00386	00395	00404	00413	00423	00433	00447	00468	00485	00499
9ft	00387	00396	00405	00414	00424	00434	00448	00469	00486	00500
10ft	15199	15200	15202	15201	15203	15204	00449	00470	25428	00501
12ft	00388	00397	00406	00415	00425	00435	00450	00471	00487	00502
14ft	15205	15206	15208	15207	15224	15210	00451	00472	19529	00503
15ft	22013	22012	22011	00416	00426	00436	00452	00473	00488	00504
20ft	00389	00398	00407	00417	00427	00437	00453	00474	00489	00505
25ft	15211	15212	15222	15213	15215	15216	00454	00475	19520	00506
30ft	00390	00399	00408	00418	00428	00438	00455	00476	00490	00507
35ft	00391	00400	00409	00419	00429	00439	00456	00477	00491	00508
50ft	19305	20037	20038	20036	20088	22142	00457	00478	24046	00509
75ft	26970	22146	26971	22147	22122	22148	00458	00479	27094	00510
100ft	19329	21471	27096	19387	19386	20579	00459	00480	21472	00511
150ft	19378	23870	19381	19389	19388	19349	00460	00481	19352	00512
200ft	19145	23870	—	—	—	—	—	—	—	—
250ft	20345	—	—	—	—	—	—	—	—	—

