

Product data sheet

Specifications



NetShelter SV 42U 800mm Wide x 1200mm Deep Enclosure with Sides Black

AR2580

Overview

Presentation Wide and Deep Universal IT enclosure with increased enclosure width for more cable management options in denser server and networking applications. Includes integrated vertical 1U mounting spaces adjacent the enclosures standard EIA-310 equipment mounting u-spaces that can be removed and replaced with 1U accessories. Enclosures are deep to provide additional equipment clearance space or more open space for ease of access in the rear of the enclosure. 42U height to easily roll through doorways.

Lead time Usually in Stock

Main

Product or Component Type Rack enclosure

number of rack unit 42U

Provided equipment Baying hardware
Doors
Key(s)
Keyed-alike doors and side panels
Leveling feet
Mounting Hardware
Pre-installed casters
4 x Bolt down brackets
Roof
Side Panels
Unpacking sheet

Physical

Height 81.0 in (205.7 cm)

Width 31.5 in (80 cm)

Depth 47.2 in (120 cm)

Net Weight 307.5 lb(US) (139.5 kg)

Color Black

Mounting preference No preference

Mounting Mode Not rack-mountable

Maximum Mounting Depth 36.10 in (91.69 cm)

minimum mounting depth 6.60 in (16.76 cm)

rack width 19"

Marking 14 gauge EIA mounting rail
16 gauge front door
18 gauge post
16 gauge rear door
19 gauge roof
18 gauge side panels

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Permanent permissible load	1014 lb(US) (459.9 kg) dynamic 2205 lb(US) (1000.2 kg) static
-----------------------------------	--

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
-----------------	-----------------------------

GTIN	731304302117
-------------	--------------

Returnability	No
----------------------	----

Country of origin	CN
--------------------------	----

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Number of Units in Package 1	1
-------------------------------------	---

Package 1 Height	85.9 in (218.1 cm)
-------------------------	--------------------

Package 1 Width	37.008 in (94 cm)
------------------------	-------------------

Package 1 Length	51.2 in (130 cm)
-------------------------	------------------

Package 1 Weight	352.881 lb(US) (160.064 kg)
-------------------------	-----------------------------

Contractual warranty

Warranty	5 year repair or replace
-----------------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH


Resource performance


 [Take-Back Program Available](#)

Well-being performance

 [Reach Free Of Svhc](#)

 [Toxic Heavy Metal Free](#)

 [Mercury Free](#)

 [Rohs Exemption Information](#) [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
