




REVISIONS		
Rev	DESCRIPTION	DATE

MATERIALS LIST:

1,CABLE:UL20379 HDMI 1.4V(7/0.2TA*1PR+EAM)*5+7/0.2TA*4C+AB 65%
OD:10.3MM COLOR:P001(BLACK) (W12112306)

2,CONNECTOR: 19M PIN GOLD PLATED 15u", GOLD PLATED FRONT SHELL

3,PVC:BLACK(V398) 45P

4,DUST COVER: PE

5,LABEL:YEAR/MONTH LABEL

ELECTRONIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 20M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: 0<L<10FT 2 ohm (MAX)
10FT<L<15FT 3 ohm (MAX)
15FT<L<30FT 4 ohm (MAX)
30FT<L<99FT 6 ohm (MAX)
L>100FT 10 ohm (MAX)

SSFT P/N:	BBOX P/N:	LENGTH
J00581499	VCB-HDMI-007M	7000 ⁺¹⁵⁰ ₋₀ mm
J00581500	VCB-HDMI-010M	10000 ⁺¹⁵⁰ ₋₀ mm
J00581501	VCB-HDMI-015M	15000 ⁺¹⁵⁰ ₋₀ mm
J00581502	VCB-HDMI-020M	20000 ⁺³⁰⁰ ₋₀ mm
J00581503	VCB-HDMI-025M	25000 ⁺³⁰⁰ ₋₀ mm
J00581504	VCB-HDMI-030M	30000 ⁺³⁰⁰ ₋₀ mm

CABLE MARKING: BLACK BOX CORPORATION GUARANTEED FOR LIFE(724) 746-5500---
PREMIUM HDMI CABLE---A AWM E101344-C STYLE 20379 80°C 30V

ALL MATERIALS TO MEET RoHS

PIN OUT

CN1	CN2	CN1	CN2
1 WHITE	1	13 RED	13
3 BROWN	3	15 WHITE	15
2 DRAIN	2	16 VIOLET	16
4 WHITE	4	18 BLACK	18
6 RED	6	14 WHITE	14
5 DRAIN	5	19 ORANGE	19
7 WHITE	7	17 DRAIN	17
9 GREEN	9	SHELL BRAID	SHELL
8 DRAIN	8		
10 WHITE	10		
12 BLUE	12		
11 DRAIN	11		

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.
©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ±
ANGULAR: MACH ± BEND ±
TWO PLACE DECIMAL ±
THREE PLACE DECIMAL ±
INTERPRET GEOMETRIC TOLERANCING PER:
MATERIAL CRS
FINISH POWDER COAT
DO NOT SCALE DRAWING

BLACK BOX®			
DRAWN	NAME	DATE	TITLE:
ENG APPR.	Wayne	4/29/2013	VCB-HDMI-xxxM
CHECKED	Lucency	4/29/2013	SIZE DWG. NO.
COMMENTS:	HDMI 1.4 24AWG(7M-30M)		REV B
SCALE: 1:1			SHEET 1 OF 1