


REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	05/15/2017




ELECTRICAL TEST :

- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE: 3 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms

PRODUCT SPECIFICATIONS :

- 1.Connector Type: Mini DisplayPort MALE TO DisplayPort MALE
- 2.Connector Plating and Material:
Mini DisplayPort Port M White Insulation ,Gold Plated 3u Terminal ,Nickel Plated Shell.
DisplayPort Port M Black Insulation ,Gold Plated 3u Terminal ,Nickel Plated Shell.
- 3.Color: Black Connectors and Black ABS Shell
- 4.RoHS 2.0: Yes
- 5.Resolution Supported: 4K*2K 60Hz
- 6.Cable Specifications:
Display Port UL20276~(32AWG*1P+EAM)*5C+32AWG*4C+AEB 85%AL~OD:4.8MM~Black~Marking:DisplayPort cable E342987 AWM STYLE 20276 80C 30V VW-1
- 7.Passive Adapter Supports TMDS

PIN Assignment



The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.
©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± ANGULAR: MACH ± BEND ± TWO PLACE DECIMAL ± THREE PLACE DECIMAL ±				TITLE: Mini DisplayPort M TO DisplayPort M CABLE L=6FT Black	
INTERPRET GEOMETRIC TOLERANCING PER	DRAWN AX.Dhg			DATE 05/15/2017	SIZE B
MATERIAL CRS	CHECKED	COMMENTS:	SCALE: 1:1		SHEET 1 OF 2
FINISH POWDER COAT	DO NOT SCALE DRAWING				