



REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	05/15/2017



**ELECTRICAL TEST :**

- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE: 3 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms

**PIN Assignment**



**PRODUCT SPECIFICATIONS :**

- 1.Connector Type: Mini DisplayPort MALE TO DisplayPort MALE
- 2.Connector Plating and Material:  
Mini DisplayPort Port M White Insulation ,Gold Plated 3u Terminal ,Nickel Plated Shell.  
DisplayPort Port M Black Insulation ,Gold Plated 3u Terminal ,Nickel Plated Shell.
- 3.Color: Black Connectors and Black ABS Shell
- 4.RoHS 2.0: Yes
- 5.Resolution Supported: 1080P 60Hz
- 6.Cable Specifications:  
Display Port UL20276~(32AWG\*1P+EAM)\*5C+32AWG\*4C+AEB 85%AL~OD:4.8MM~Black~Marking:DisplayPort cable E342987 AWM STYLE 20276 80C 30V VW-1
- 7.Passive Adapter Supports TMDS

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL ±  
ANGULAR: MACH ± BEND ±  
TWO PLACE DECIMAL ±  
THREE PLACE DECIMAL ±  
INTERPRET GEOMETRIC TOLERANCING PER  
MATERIAL CRS  
FINISH POWDER COAT  
DO NOT SCALE DRAWING

**BLACK BOX**

DRAWN	NAME	DATE	TITLE:	REV
AX.Dwg		05/15/2017	Mini DisplayPort M TO DisplayPort M CABLE L=15FT Black	A
ENG APPR.			SIZE DWG. NO. B ENVMDPDP-0015-MM	
CHECKED			SCALE: 1:1	SHEET 1 OF 2
COMMENTS:				

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.  
©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.