


REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	09/26/2018
B	ADD SCREEN PRINTING LOGO	12/06/2018




ELECTRICAL TEST :

- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE: 2 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms
- 5.100% of image Test

PRODUCT SPECIFICATIONS :

- 1.Connector Type: DisplayPort MALE TO DVI FEMALE
- 2.Connector Plating and Material:
Display Port to DVI Adapter DVI Plug Nickel Plated Terminal+PCB
DisplayPort M Shell Nickel Plated Terminal Gold Plated 3U" Black Insulation
- 3.Color: Black connectors and Black Cable
- 4.RoHS 2.0: Yes
- 5.Resolution Supported: 1920X1080P / 60Hz
- 6.Cable Specifications:
DISPLAY PORT UL20276[34AWG(7/0.06TC)*1P+EAM]*5C+32AWG(7/0.08TC)*5C+AEB
(16/5/0.12MM 85%AL) OD:4.5MM Black
- 7.Passive Adapter Supports TMDS



The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.

©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ±
ANGULAR: MACH ± BEND ±
TWO PLACE DECIMAL ±
THREE PLACE DECIMAL ±

INTERPRET GEOMETRIC TOLERANCING PER:	
MATERIAL	CRS
FINISH	POWDER COAT
DO NOT SCALE DRAWING	

BLACK BOX®

	NAME	DATE	TITLE: DP TO DVI ADAPTER DP1.1, PASSIVE,ABS HOUSING		
DRAWN	JX.YAO	09/26/2018			
ENG APPR.			SIZE	DWG. NO. B EVNDPDI-MF-R3	REV B
CHECKED					
COMMENTS:					
			SCALE: 1:1		SHEET 1 OF 1