



HP 952 3-pack Cyan/Magenta/Yellow Original Ink Cartridges (N9K27AN)

Overview



Versatile HP inks print everything you need

Most Original HP Cartridges have been engineered to contain recycled content and meet HP's quality standards.

Reliable performance, standout results

Original HP ink cartridges are specially designed to work flawlessly with your HP printer or all-in-one.

Professional quality, perfect for the office

Print professional-quality business documents with vibrant color, using pigment inks designed for the office.

Get a great value for office productivity

Print affordably with individual cartridges. Simply replace each cartridge separately, as needed.

Designed to conserve

Easily recycle your Original HP cartridges at no charge through HP Planet Partners.[4]

Specifications

Ink Types	Pigment-based
Print Cartridge/Bottle, Color(s)	Cyan, magenta, yellow
Technology	Ink
Supply Type	Cartridges
Ink Drop	7 pl
Print Head Nozzles	1568
Print Cartridge/Bottle Volume (metric)	8.5 ml (cyan), 9 ml (magenta), 8.5ml (yellow)
Operating Temperature Range (celsius)	5 to 35°C
Storage Temperature Range (celsius)	-40 to 60°C
Operating Humidity Range	10 to 90% RH
Non-operating Humidity Range	10 to 90% RH
Print Resolution Technologies	TIJ 4.X
Compatibility Statement	HP OfficeJet Pro 8210 Printer, HP OfficeJet Pro 8216/8218 Printer, HP OfficeJet Pro 7740 All-in-One, HP OfficeJet Pro 8710 All-in-One, HP OfficeJet Pro 8720 All-in-One, HP OfficeJet Pro 8730 All-in-One, HP OfficeJet Pro 8740 All-in-One
Product Count Per Unit	3
Case or Master Carton Quantity	24
Quantity Per Pallet	2304
Cartons Per Pallet	96
UPC Number	(140) 889894824646; (RFD) 198990537771
Pallet Barcode	(140) 40889894824644
Product Dimensions (metric)	114.8.1 x 45 x 100.1 mm
Product Dimensions (imperial)	4.52 x 1.77 x 3.94 in
Package Dimensions (metric)	114.8.1 x 45 x 100.1 mm
Package Dimensions (imperial)	4.52 x 1.77 x 3.94 in
Dimensions (case or master carton, metric)	252 x 249.9 x 170.9 mm
Case Dimensions (case or master carton, imperial)	9.92 x 9.84 x 6.73 in
Pallet Dimensions (metric)	1016 x 1219.2 x 1163.3 mm
Pallet Dimensions (imperial)	40 x 48 x 45.8 in
Case Weight (case or master carton, metric)	4.04 kg

Package Weight (metric)	~0.12 kg
Package Weight (imperial)	~0.27 lb
Pallet Weight (metric)	408.3 kg
Pallet Weight (imperial)	899.4 lb
Page Yield	630
Page Yield (combo-pack)	Per cartridge: ~630 pages cyan, ~630 pages magenta, ~630 pages yellow
What Is In The Box	3 ink cartridges: cyan, magenta, yellow
Manufacturer Warranty	HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty.

Additional specifications

Business Segment (filter)	OfficeJet Pro
Cartons Per Layer	16
Cartridge Color	Cyan; Magenta; Yellow
Cartridge Package Selectability	952
Case Weight (case or master carton, imperial)	8.9 lb
Compatibility Headline	HP 952 ink cartridges work with:
Count of Layers In Pallet	6
Datasheet Feature Photo 02	https://hp.widen.net/content/ndg4rv4cgt/jpeg/ndg4rv4cgt.jpg?w=2000&h=2000&dpi=72
Environmental Certifications	UL ECOLOGO® certified
ITF-14 Unit Code Numerical Equivalent (smaller master carton)	(140) 20889894824640
Inner Pack ITF-14 Unit Code	(140) 10889894824643
Operating Temperature Range (fahrenheit)	41 to 95°F
Package Count	3
Page Yield (cyan)	1 Cyan (~630 pages)
Page Yield (magenta)	1 Magenta (~630 pages)
Page Yield (yellow)	1 Yellow (~630 pages)
Page Yield Footnote	Tested in HP OfficeJet Pro 8700 Printer Series. Average continuous composite (cyan/magenta/yellow) yield based on ISO/IEC 24711 or HP testing methodology and continuous printing. Actual yield varies considerably based on content of printed pages and other factors. For details, see http://www.hp.com/go/learnaboutsupplies .
Print Technology	HP Thermal Inkjet
Printhead Swath (in Inch)	1.25 in
Product Subgroup	Combo-packs
Quantity Per Box	4
SNF JPEG Product Photo 190x170	Ink Toner Paper Printer Supplies/hp-950-officejet-ink-cartridges_190x170.jpg
SNF JPEG Product Photo 70x100	Ink Toner Paper Printer Supplies/hp-950-officejet-ink-cartridges_70x100.jpg
Segment (filter)	OfficeJet Pro
Stacking Number For Pallet	2
Storage Temperature Range (fahrenheit)	-40 to 140°F

Subgroup	Standard Capacity Cartridges
Technology Logo 01	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08990360.png
Technology Logo 02	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08990361.png
UNSPSC Code	44103105
Warranty Standard Statement	HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty. This warranty pertains to the product when used in its designated HP or authorized OEM printing device. HP will, at HP's option, either refund the purchase price or replace products that prove to be defective. Visit the HP online support web site http://www.hp.com/support for a list of support phone numbers and conditions or return to your point of purchase.
Weight (imperial)	~0.35 lb
Weight (metric)	~0.16 kg

Ink/Toner/Paper/Printer Supplies

Ink Supplies

★ : Recommended

HP Inkjet Printer Cartridges and Ink Supplies

HP 952XL High Yield Black Original Ink Cartridge	F6U19AN
HP 952XL High Yield Black/952 Cyan/Magenta/Yellow 4-pack Original Ink Cartridges	N9K28AN
HP 952XL High Yield Cyan Original Ink Cartridge	LOS61AN
HP 952XL High Yield Magenta Original Ink Cartridge	LOS64AN
HP 952XL High Yield Yellow Original Ink Cartridge	LOS67AN

Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Mar 08, 2026 1:55 AM UTC+0000