



# HP 65XL Black Original Ink Cartridge (N9K04AN)

## Overview



**Print photos and documents with low-cost Original HP ink cartridges—designed for consistent results.**

Create high-quality color photos and everyday documents with low-cost Original HP ink cartridges. These dependable cartridges deliver consistent results, so you can print vivid color and crisp text for the life of your cartridge.

### Low-cost ink, high-quality results

Take advantage of outstanding Original HP print quality with low-cost cartridges.

### Printing made so simple

Receive notifications when cartridges are running low for quick ordering.

### Designed to deliver

Original HP ink cartridges are specially designed to work with your HP printer or all-in-one.

---

## Specifications

<b>Ink Types</b>	Pigment-based
<b>Print Cartridge/Bottle, Color(s)</b>	Black
<b>Technology</b>	Ink
<b>Supply Type</b>	Cartridges
<b>Ink Drop</b>	22 pl
<b>Print Head Nozzles</b>	328
<b>Print Cartridge/Bottle Volume (metric)</b>	5.5 ml
<b>Operating Temperature Range (celsius)</b>	15 to 32°C
<b>Storage Temperature Range (celsius)</b>	-40 to 60°C
<b>Operating Humidity Range</b>	20 to 80% RH
<b>Non-operating Humidity Range</b>	20 to 80% RH
<b>Print Resolution Technologies</b>	TIJ 2.X
<b>Compatibility Statement</b>	HP DeskJet 2220 All-in-One, HP DeskJet 2255 All-in-One, HP DeskJet 3720 All-in-One, HP DeskJet 3755 All-in-One
<b>Product Count Per Unit</b>	1
<b>Case or Master Carton Quantity</b>	24
<b>Quantity Per Pallet</b>	3168
<b>Cartons Per Pallet</b>	132
<b>UPC Number</b>	(140) 889894900753; (RFD) 198990537764
<b>Pallet Barcode</b>	30889894900754
<b>Product Dimensions (metric)</b>	114 x 36.3 x 102.9 mm
<b>Product Dimensions (imperial)</b>	4.49 x 1.43 x 4.05 in
<b>Package Dimensions (metric)</b>	114 x 36.3 x 102.9 mm
<b>Package Dimensions (imperial)</b>	4.49 x 1.43 x 4.05 in
<b>Dimensions (case or master carton, metric)</b>	357.2 x 138.1 x 169.9 mm
<b>Case Dimensions (case or master carton, imperial)</b>	14.06 x 5.44 x 6.69 in
<b>Pallet Dimensions (metric)</b>	1219.2 x 1016 x 1168.4 mm
<b>Pallet Dimensions (imperial)</b>	48 x 40 x 46 in
<b>Case Weight (case or master carton, metric)</b>	1.53 kg
<b>Package Weight (metric)</b>	~0.05 kg

**Package Weight (imperial)** ~0.12 lb

**Pallet Weight (metric)** 223 kg

**Pallet Weight (imperial)** 491.2 lb

**Page Yield** 300

**Average Page Yield For A4 Format,  
Black and White** ~300 pages

**What Is In The Box** Ink cartridge

**Manufacturer Warranty** HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty.

## Additional specifications

<b>Automation Feature Photo 01</b>	<a href="https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08923428.jpg">https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c08923428.jpg</a>
<b>Business Segment (filter)</b>	Premium Home
<b>Cartons Per Layer</b>	22
<b>Cartridge Color</b>	Black
<b>Cartridge Package Selectability</b>	65XL
<b>Case Weight (case or master carton, imperial)</b>	3.38 lb
<b>Compatibility Headline</b>	HP 65 ink cartridges work with:
<b>Count of Layers In Pallet</b>	6
<b>Datasheet Feature Photo 02</b>	<a href="https://hp.widen.net/content/tuqgaeirkn/jpeg/tuqgaeirkn.jpg?w=2000&amp;h=2000&amp;dpi=72">https://hp.widen.net/content/tuqgaeirkn/jpeg/tuqgaeirkn.jpg?w=2000&amp;h=2000&amp;dpi=72</a>
<b>Empty Weight</b>	24.83 g
<b>Environmental Certifications</b>	UL ECOLOGO® certified
<b>ITF-14 Unit Code Numerical Equivalent (smaller master carton)</b>	(140) 20889894900757
<b>Inner Pack ITF-14 Unit Code</b>	(140) 10889894900750
<b>Operating Temperature Range (fahrenheit)</b>	59 to 90°F
<b>Package Count</b>	1
<b>Page Yield (black)</b>	1 Black (~300 pages)
<b>Page Yield Footnote</b>	Tested in HP Deskjet 3700 All-in-One Printer series. Approximate average based on ISO/IEC 24711 or HP testing methodology and continuous printing. Actual yield varies considerably based on content of printed pages and other factors. For details, see <a href="http://www.hp.com/go/learnaboutsupplies">http://www.hp.com/go/learnaboutsupplies</a> .
<b>Print Technology</b>	HP Thermal Inkjet
<b>Printhead Swath (in Inch)</b>	0.56 in
<b>Product Subgroup</b>	High Capacity Ink Cartridges
<b>Quantity Per Box</b>	4
<b>Segment (filter)</b>	Premium Home
<b>Stacking Number For Pallet</b>	2
<b>Storage Temperature Range (fahrenheit)</b>	-40 to 140°F
<b>Subgroup</b>	High Capacity Cartridges
<b>Technology Logo 01</b>	<a href="https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08990360.png">https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08990360.png</a>
<b>Technology Logo 02</b>	<a href="https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08990361.png">https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08990361.png</a>

**UNSPSC Code**

44103105

**Warranty Standard Statement**

HP's ink cartridges and printheads are warranted to be free from defects in materials and workmanship during the period of the warranty. This warranty pertains to the product when used in its designated HP or authorized OEM printing device. HP will, at HP's option, either refund the purchase price or replace products that prove to be defective. Visit the HP online support web site <http://www.hp.com/support> for a list of support phone numbers and conditions or return to your point of purchase.

**Weight (imperial)**

0.09 lb

**Weight (metric)**

0.04 kg

---

## Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Mar 08, 2026 10:57 AM UTC+0000