











REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	2014.08.22



SUGGESTED MOUNTING CUTOUT



MATERIAL
Housing: High-impact Acrylonitrile Butadiene Styrene (ABS resin), UL 94 V-0 rated
Jack Contacts: Phosphor Bronze flat wire, plated with 50 µin (1.27 µm) thick hard gold over nickel underplate
PCB: FR4
IDC Terminals: Phosphor Bronze, plated with tin over nickel underplate
IDC Block: High-impact Polycarbonate (PC resin), UL 94 V-0 rated
RoHS 2 compliant

WIRE RANGE
Conductor Diameters: 0.020 in (0.51 mm) 24 AWG - 0.025 in (0.64 mm) 22 AWG
Insulation Diameters: 0.032 in (0.8 mm) - 0.039 in (1.0 mm)
Cable Diameters: 0.197 in (5 mm) - 0.354 in (9 mm)

PERFORMANCE
Rating: TIA-568-C.2, Category 5e
MHz Rating: 1 - 100 MHz
Bandwidth Support: 10/100/1000 Mbps
Compliant: Meets TIA-568-C.2 Category 5e
Connecting Hardware Requirement for Component Level
Insertion Cycles: 750 Times for 8P Modular Plug
Cable Re-termination Cycles: 20 Times



UL 1863
41VW COMMUNICATIONS-CIRCUIT
E191644 ACCESSORIES

DIMENSIONS ARE IN[MM]					ANGLE
TOLERANCES:					
-0.787[20]	-1.969[50]	-5.906[150]	5.906*[150]-		
±0.008*[0.2]	±0.016*[0.4]	±0.020*[0.5]	±0.059*[1.5]	±2°	
3rd Angle Projection					

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.
©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ±
ANGULAR: MATCH ± BEND ±
TWO PLACE DECIMAL ±
THREE PLACE DECIMAL ±

INTERPRET GEOMETRIC
TOLERANCING PER:
MATERIAL
FINISH
DO NOT SCALE DRAWING

PIN ASSIGNMENTS		T568B	T568A
	1	WHITE/ORANGE	WHITE/GREEN
	2	ORANGE	GREEN
	3	WHITE/GREEN	WHITE/ORANGE
	4	BLUE	BLUE
	5	WHITE/BLUE	WHITE/BLUE
	6	GREEN	ORANGE
	7	WHITE/BROWN	WHITE/BROWN
	8	BROWN	BROWN



TITLE:			A	
22	GigaBase2 Universal Jack			
22	Category 5e, Orange			
22	SIZE	DWG. NO.		REV
	B	FMT926-R2		A
SCALE: X		SHEET 1 OF 1		