


SPECIFICATION SHEET



18 AWG C14 to C13 Color Power Cord

- Color coded
- Constructed of heavy duty 18AWG conductors
- Rated up to 250V 10A
- UL listed and TAA compliant
- Lifetime Warranty


Specifications: 18 AWG C14 to C13 Color Power Cord

Electrical Specifications:

Voltage Rating:	250V
Amperage Rating:	10A
Conductor:	41/ 0.16mm 18AWG

Physical Specifications:

Overall Diameter:	7.4mm $\pm$ 0.3mm
Operating Temperature:	105°C
Certifications:	UL 817, RoHS, REACH



Specifications: 18 AWG C14 to C13 Color Power Cord

Length	Blue	Red	Orange	Green	Yellow	White
1ft	17474	17475	17476	17477	17478	17479
2ft	17480	17481	17482	17483	17484	17485
3ft	17486	17487	17488	17489	17490	17491
4ft	17492	17493	17494	17495	17496	17497
5ft	17498	17499	17500	17501	17502	17503
6ft	17504	17505	17506	17507	17508	17509
8ft	17510	17511	17512	17513	17514	17515
10ft	17516	17517	17518	17519	17520	17521



CABLES TO GO

Cables To Go
3555 Kettering Blvd.
Moraine, OH 45439
Phone: 800.287.2843
www.c2g.com

Follow Us

