

Product data sheet

Specifications



APC Essential SurgeArrest PE66W, 6 Outlets, 6 Foot Cord, 120V, White

PE66W

⚠ Discontinued on: Feb 14, 2024

⚠ To be end-of-service on: Sep 30, 2024

⚠ To be discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	6 ft (1.8 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Green White
Height	1.2 in (3 cm)
Width	2.05 in (5.2 cm)
Depth	11.02 in (28 cm)
Net Weight	1.1 lb(US) (0.5 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz
Maximum Input Current per Phase	15 A
Switching current capacity	15 A

Output

Number of power socket outlets	6
Outlet standard	NEMA L5-15R

Conformance

UL 1449 TVSS Rating	500
---------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	MET Canada MET USA
Standards	UL 1363 UL 1449
Equipment protection policy	Lifetime : \$50000

Environmental

Ambient Air Temperature for Operation	32.0000000000...104.0000000000 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	48 kAcommon mode 24 kAnormal mode
Surge energy rating	1080 J

Ordering and shipping details

GTIN	731304328889
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 in (4 cm)
Package 1 Width	12.2 in (31 cm)
Package 1 Length	4.5 in (11.5 cm)
Package 1 Weight	1.28 lb(US) (0.58 kg)
SCC14	10731304328886

Contractual warranty

Warranty	Limited Lifetime
-----------------	------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Lead Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
