

Product data sheet

Specifications



APC Home Office SurgeArrest 8 Outlets, 120V

PH8

⚠ Discontinued on: Apr 30, 2024

⚠ To be discontinued

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	6 ft (1.8 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Black
Height	1.2 in (3 cm)
Width	3.03 in (7.7 cm)
Depth	9.7 in (24.7 cm)
Net Weight	1.3 lb(US) (0.6 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz
Maximum Input Current per Phase	15 A
Switching current capacity	15 A

Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

Conformance

Product Certifications	MET Canada MET USA
------------------------	-----------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	UL 1363 UL 1449
Equipment protection policy	Lifetime : \$150000

Environmental

Ambient Air Temperature for Operation	32.0000000000...104.0000000000 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	56 kAcommon mode 28 kAnormal mode
Surge energy rating	2160 J

Ordering and shipping details

GTIN	731304335979
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.9 in (4.8 cm)
Package 1 Width	11.2 in (28.5 cm)
Package 1 Length	5.7 in (14.5 cm)
Package 1 Weight	1.5 lb(US) (0.7 kg)
SCC14	10731304335976

Contractual warranty

Warranty	Limited Lifetime
-----------------	------------------