

Product data sheet

Specifications



APC Essential SurgeArrest 6 Outlet 4 Foot Cord with 2 Port 2.4A USB Charger Dual Pack 120V White

PE64U2WGDP

! To be discontinued

! Discontinued on: Feb 14, 2024

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Input Connection Type	NEMA 5-15P
Cable length	4 ft (1.2 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Gray White
Height	1.2 in (3 cm)
Width	2.05 in (5.2 cm)
Depth	13.8 in (35 cm)
Net Weight	1.1 lb(US) (0.5 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz
Maximum Input Current per Phase	15 A
Switching current capacity	15 A

Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

Conformance

Product Certifications	MET Canada MET USA
------------------------	-----------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	FCC Part 15 class B UL 1363 UL 1449
Equipment protection policy	Lifetime : \$50000

Environmental

Ambient Air Temperature for Operation	32.0000000000...104.0000000000 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5.0000000000...113.0000000000 °F (-15...45 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	48 kAcommon mode 24 kAnormal mode
Surge energy rating	1080 J

Ordering and shipping details

GTIN	731304336624
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.0 in (38 cm)
Package 1 Width	1.6 in (4 cm)
Package 1 Length	8.9 in (22.5 cm)
Package 1 Weight	2.54 lb(US) (1.15 kg)
SCC14	10731304336621

Contractual warranty

Warranty	Limited Lifetime
-----------------	------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Circularity Profile [End of Life Information](#)
