

 HP 1 GB 90-pin DDR3 DIMM (2NR03A)



Specifications

Minimum dimensions (W x D x H)	43.4 x 29.1 x 7.0 mm
Minimum dimensions (W x D x H)	1.7 x 1.1 x 0.3 in
Weight	0.005 kg
Weight	0.013 lb
Package dimensions (W x D x H)	177.8 x 133.4 x 25.4 mm
Package weight	0.0525 kg
UPC number	193808481826
Manufacturer Warranty	90 Day HP or Dealer Exchange. Warranty and support options vary by product, country and legal requirements (wrtty code 3R, wrty ID A065)
What's in the box	HP 1 GB 90-Pin DDR3 TAA Version DIMM; Install-Guide

Additional specifications

Accessory type	Other
Business filter	cMPS
Cartons per layer	6
Case dimensions (case or master carton)	22.9 x 16.2 x 11.7 in
Case or master carton dimensions (W x D x H)	581 x 411 x 297 mm
Case or master carton quantity	72
Case weight (case or master carton)	4.57 kg
Case weight (case or master carton, imperial)	10.1 lb.
Compatibility	HP LaserJet Enterprise M607n, HP LaserJet Enterprise M607dn, HP LaserJet Managed E60055dn, HP LaserJet Managed E60155dn, LaserJet Managed E50145dn Printer, HP LaserJet Enterprise M507n, HP LaserJet Enterprise M507dn, HP LaserJet Enterprise M507x, HP LaserJet Enterprise M507dng, HP Color LaserJet Enterprise M553n, HP Color LaserJet Enterprise M553dn, HP Color LaserJet Enterprise M553x, HP Color LaserJet Enterprise M553dh, HP Color LaserJet Managed M553dnm, HP Color LaserJet Managed M553xm, HP Color LaserJet Managed E55040dw, HP LaserJet Enterprise M609dh, HP LaserJet Enterprise M609dn, HP LaserJet Enterprise M609x, HP LaserJet Managed E60075dn, HP LaserJet Managed E60075x, HP LaserJet Managed E60175dn, HP LaserJet Enterprise M608n, HP LaserJet Enterprise M608dn, HP LaserJet Enterprise M608x, HP LaserJet Enterprise M608nk, HP LaserJet Managed E60065dn, HP LaserJet Managed E60065x, HP LaserJet Managed E60165dn, HP LaserJet Enterprise M506n, HP LaserJet Enterprise M506dn, HP LaserJet Enterprise M506x, HP LaserJet Enterprise M506dh, HP LaserJet Managed E50045dn, HP LaserJet Managed M506dnm, HP LaserJet Managed M506xm
Component type	Printer accessories
Count of layers in pallet	4
Country of origin	Made in USA
Electromagnetic compatibility	CISPR 22: 2008 (International) - Class A, CISPR32: 2012 (International) - Class A, EN 55032: 2012 (EU) - Class A, FCC CFR 47 Part 15 Class A/ICES-003, Issue 6 Class A
Metric depth	3.81
Metric height	30
Metric width	67.6
Non-Operating Humidity Range	10 to 80% RH (non-condensing)
Operating humidity range	10 to 90% RH (non-condensing)
Operating temperature range	10 to 32°C
Operating temperature range	50 to 90°F

Orderable product number	2NR03A
Package dimensions (W x D x H)	7.0 x 5.25 x 1.0 in
Package weight	0.12 lb
Pallet dimensions	47.2 x 39.4 x 79.8 in
Pallet dimensions (W x D x H)	1200 x 1000 x 2027 mm
Pallet weight	124.7 kg
Pallet weight	274.9 lb
Product count per unit	1
Quantity per pallet	1728
Safety	IEC 60950-1:2005 +A1:2009 +A2:2013 (International); EN60950-1:2006 +A11:2009 +A1:2010 +A12:2011 +A2:2013 (EU);
Storage temperature range	-30 to 60°C
Storage temperature range	-22 to 140°F
Tariff numbers	8443992550
UNSPSC code	32101621
Warranty	Telephone support for basic setup, installation, and troubleshooting during warranty.

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Sep 20, 2024 6:49 AM UTC+0000