



FORD INTERCEPTOR UTILITY VEHICLE

2020-2024
SOLUTIONS



THE EVOLUTIONARY VSX CONSOLE

The new C-VSX-1800-INUT Series of vehicle-specific consoles for the 2020-2024 Ford Interceptor Utility redefines the vision of the public safety console from the ground up.

- Lightweight & durable engineered polycarbonate housing
- Steel floor-mounting structure
- Low profile for safety & side-to-side egress
- 13" wide at front, 9" wide at seats
- 18" total internal mounting space
- 6" section at front with option for tray (C-APX-101) or printer mount (C-PMX-101)
- Rugged hood for equipment mounting
- 8" nut track for side-mounted accessories on driver & passenger sides
- Access to OEM controls
- Storage pockets on driver & passenger sides
- Access panels on driver & passenger sides
- Rear floor bracket with mounting hole pattern for CG-X
- Motorola speaker mounting hole pattern on rear console enclosure



C-VSX-1800-INUT SERIES

C-VSX-1800-INUT SERIES

FRONT BIN



C-APX-101

- Creates additional mounting space
- Port for Relocating OEM lighter plug
- (2) Blanks for Optional C-USB-2
- Space for driver's licenses & pens
- Tray can be replaced with Siren Light Control Head Options
- Mounting for Whelen, Federal Signal & Code 3 control heads

INTEGRATED PRINTER



C-PMX-101

- Creates additional mounting space
- Space for driver's licenses & pens
- Access to OEM Controls
- Access to printed reports
- Supports Brother PocketJet Printers

RUGGED HOOD



C-VSX-1800-INUT SERIES

- Access to vehicle factory controls
- Provides rigid mounting platform for critical equipment
- Patent pending

ARMREST



C-ARM-1001

- Internally mounted in console extrusion
- Locking accessory pocket
- Creates more space in-vehicle
- Durable & comfortable polyurethane armrest pad
- Offers bi-level accessory compartment

EXTRUSIONS



C-VSX-1800-INUT SERIES

- Lightweight & durable aluminum
- Internal reinforcement of polycarbonate housing
- 18" of mounting space
- 8" nut track for external mounting
- Easy attachment for accessories
- Concealed by trim strips for OEM styling

8-POSITION FUSE BLOCK



CMX15600-08

- For standard automotive blade type fuses up to 30 amps
- Provides safe, reliable power distribution
- Protects wiring & components
- Max capacity 240 amps

CONSOLES

MID-HEIGHT & ANGLED

C-VS-1210-INUT

- 22" of total internal mounting space
- Lower overall height
- Improves emergency egress
- Mid-height front section
- Access to HVAC controls on dash





HIGH & ANGLED

C-VS-1012-INUT-2, C-PM-124

- 22" of total internal mounting space
- Wide angled section fits optional drop-in printer mounts
- Optional rear HVAC relocation plate
- Heavy gauge steel
- Black powder coat finish



ULTRA-LOW & ANGLED

C-VS-1508-INUT



- 23" of total internal mounting space
- Sits lower than seat height
- Optimizes driver comfort
- Ideal for mounting remote heads
- Perfect for shallow equipment



HIGH & FLAT

C-VS-0618-INUT, C-PM-124

- 24" of total horizontal internal mounting space
- Ideal for deep radios & other tall equipment
- Mounts between seats & fits lower dash contour
- Wide forward section fits optional drop-in printer mounts



OVERHEAD CONSOLE

C-OHC-INUT-1



- Mounting for a remote light & siren control head
- Low-profile with smooth edges
- Minimizes head impact
- Preserves OEM dome lights
- Retains passenger airbag indicator lights
- Compatible with wide range of control heads

CONSOLE & TABLET



C-DMM-3015, C-VS-1012-INUT-2

- Flip-up dash mount, holds 12 lbs
- Driver & passenger access
- Havis USB keyboard & mount

CONSOLE & LAPTOP



C-MD-119, C-VSX-1800-INUT-PM

- Heavy-duty telescoping side mount
- 11" slide-out arm & low profile rotation
- 180-degree horizontal rotation

CONSOLE & TOUCH SCREEN



C-DMM-3015, C-VSX-1800-INUT

- Flip-up dash mount, holds 4 lbs
- Driver & passenger access
- Havis USB keyboard & mount

DASH MOUNTS

HEAVY-DUTY DASH MOUNT

C-DMM-3015

- Flip-up design
- 12 lb carrying weight
- Ideal for tablet docks
- Access to vehicle controls
- Driver & passenger access
- Secure dual action latch
- No drill solution
- 30-minute install





C-DMM-3015

PEDESTAL MOUNTS

PREMIUM SOLUTION

PKG-PSM-3006

- Heavy duty base, pole, & side support
- Mounts to existing OEM seat bolts
- Swing arm & motion device

STANDARD SOLUTIONS

PKG-PSM-1006

- Heavy duty base, pole, tilt swivel & offset
- Mounts to existing OEM seat bolts





PKG-PSM-3006

K9 TRANSPORTS

ALL NEW DESIGN

- Rattle-eliminating design
- Sliding front door with infinite locking points
- Trim fitted to the vehicle interior to hinder chewing
- Optional partition for XL transports
- Lowest possible floor for ease of entry/egress
- Smooth powder coat
- Available in black or white
- Long-lasting & durable



STANDARD K9 TRANSPORT



K9-F28-1; K9-F28-1-B

- Optimal for 1 dog
- 36" in length
- Front slider door exit
- Window guards & door panels
- Optional 10" window fan & mount
- Optional Heat Alarm Pro or Hot-N-Pop Pro
- Available in black or white

EXTENDED K9 TRANSPORT



K9-F28-XL; K9-F28-XL-B

- Optional dual dog divider available
- 45" in length
- Front slider door with exit
- Window guards & door panels
- Optional 10" window fan & mount
- Optional Heat Alarm Pro or Hot-N-Pop Pro
- Available in black or white

PREMIUM K9 PRISONER



K9-F28-PT; K9-F28-PT-B

- 60/40 K9 & prisoner
- Prisoner behind driver
- Uses OEM seat & belt
- Emergency exit door
- Available in black or white

STORAGE

MODULAR SOLUTIONS

Protect & Stow. Designed to fit the most popular SUVs, such as the Ford Interceptor Utility.

Easy to Install. Multiple drawers, toppers, lock options & accessories with one footprint that meet your needs.

American Made. Constructed from lightweight & durable aluminum material.

Versatility. Knockouts for wiring & venting support all types of equipment & accessory mounting.



RAISED CARGO PLATE

SBX-3003; SBX-4003; SBX-1001;
PKG-TTP-INUT-1201-4

- Fold-up raised cargo plate replaces OEM floor
- Easy access & removal of spare tire
- Locking latches secure equipment
- Fan mounting & ventilation for electronics
- Equipment mounted to C-TTP-INUT-4
- 200 lb lift struts for mounting storage



LOW PROFILE CARGO PLATE

PKG-TTP-INUT-1201-4



- 3" space between tray & tire
- Access to spare tire
- 80-lb & 200-lb strut options

- No drill solution
- Rests flush with rear sill plate

STORAGE DRAWER MOUNTS FOR HAVIS K9

SBX-5001, SBX-5007

- Rugged mount attaches drawers to vehicle floor & rear of Havis K9
- Positions drawer 4" off vehicle floor & allows access to spare tire
- For use with Havis K9-XL & K9-PT –SBX-5001
- For use with Havis Standard Length K9 – SBX-5007



LOW STORAGE DRAWER MOUNT

SBX-5004

- Raises storage drawers 4" off floor
- Allows full access & removal of spare tire
- Includes all hardware to mount Havis modular storage drawer to base in vehicle
- PROKIT-2 required when used with Pro-gard rear partition



SINGLE DRAWER RAISED MOUNT

SBX-5006

- Raises storage drawers 12.5" off floor
- Provides additional storage space on vehicle floor
- Allows full access and removal of spare tire
- Adjustable block-off plate included
- PROKIT-2 required when used with Pro-gard rear partition



PREMIUM SINGLE MEDIUM DRAWER PACKAGE WITH TRUNK TRAYS

PKG-SBX-INUT-105

- Includes Premium Raised Fold-Up Equipment Tray & Cargo Plate w/ 200 Lbs Lift Struts
- Includes modular medium storage drawer with medium-duty keyed lock & open topper
- 40"x20" footprint, medium-duty cam-style locks
- Heavy-duty drawer sliders w/ positive latching will keep drawers open



MEDIUM-DUTY KEYED LOCK SOLUTIONS



SBX-1001; SBX-1004

- Modular drawers with 40" x 20" footprint
- 5.5" H drawer, 8" H overall
- Medium-duty cam-style lock with flat-style keys
- Lightweight & durable aluminum construction with black powder coat finish

HEAVY-DUTY COMBINATION LOCK SOLUTIONS



SBX-1007; SBX-1008

- Modular drawers with 40" x 20" footprint
- 5.5" H drawer, 8" H overall
- Heavy-duty push-button combination lock & reinforced drawer face
- Lightweight & durable aluminum construction with black powder coat finish

HEAVY-DUTY KEYED T-HANDLE SOLUTIONS



SBX-1002; SBX-1005

- Modular drawers with 40" x 20" footprint
- 5.5" H drawer, 8" H overall
- Heavy-duty cast Medeco T-handle lock with keys & reinforced drawer face
- Lightweight & durable aluminum construction with black powder coat finish



PUBLIC SAFETY
ENERGY & UTILITIES
TRANSPORTATION & LOGISTICS
RETAIL & HOSPITALITY

WAREHOUSE & DISTRIBUTION
FIELD OPERATIONS
HEALTHCARE
MILITARY, DEFENSE & AEROSPACE

Havis is the leader in providing end-to-end rugged mobility solutions for demanding environments. We partner with leading automotive and technology companies to design innovative products that maximize productivity, safety, and quality.

1.800.524.9900 | 75 JACKSONVILLE ROAD, WARMINSTER, PA 18974
HAVIS.COM

