



# Quick Install Guide

NP04WK-QIG-01



● NP-UM330X series

D (inch)	W (cm)	H2 (cm)	L1 (cm)	L2 (cm)	H1 (cm)
61.5	125.0	93.7	10.5	44.8	21.2
70	142.2	106.7	16.8	51.1	23.1
80	162.6	121.9	24.1	58.5	25.4
90	182.9	137.2	31.5	65.8	27.6
100	203.2	152.4	38.8	73.2	29.9

● NP-UM330W series

D (inch)	W (cm)	H2 (cm)	L1 (cm)	L2 (cm)	H1 (cm)
58	124.9	78.1	10.5	44.8	21.3
60	129.2	80.8	12.0	46.4	21.8
70	150.8	94.2	19.8	54.2	24.1
80	172.3	107.7	27.6	62.0	26.5
90	193.9	121.2	35.4	69.8	28.9
100	215.4	134.6	43.2	77.6	31.3

● NP-U300X series

D (inch)	W (cm)	H2 (cm)	L1 (cm)	L2 (cm)	H1 (cm)
63	128.0	96.0	13.3	47.5	31.2
65	132.1	99.1	15.0	49.2	32.0
70	142.2	106.7	19.2	53.4	34.2
75	152.4	114.3	23.5	57.7	36.3
77	156.5	117.3	25.1	59.4	37.2
80	162.6	121.9	27.7	61.9	38.4
85	172.7	129.5	32.0	66.2	40.6

● NP-U310W series

D (inch)	W (cm)	H2 (cm)	L1 (cm)	L2 (cm)	H1 (cm)
77	165.9	103.7	15.3	49.5	30.2
80	172.3	107.7	17.4	51.6	31.2
85	183.1	114.4	21.4	55.6	32.9
87.2	187.8	117.4	22.6	56.8	33.6
90	193.9	121.2	24.6	58.8	34.6
95	204.6	127.9	28.3	62.5	36.3
100	215.4	134.6	31.9	66.1	38.0

● NP-UM383WL series

Screen		Projection distance				Height between wall adapt-er's lower edge screw hole center and screen's upper edge - H1 (cm)	
		L1 ( cm )		L2 ( cm )			
Size (D)	W (width) x H2 (height) (cm)	wide	tele	wide	tele	Lens Shift MAX	Lens Shift MIN
70	150.8 x 94.2	8.0	10.1	41.0	43.2	27.08	21.38
80	172.3 x 107.7	13.8	16.3	46.8	49.3	30.58	24.08
90	193.9 x 121.2	19.7	22.4	52.7	55.4	33.98	26.78
100	215.4 x 134.6	25.5	28.5	58.5	61.5	37.48	29.48
110	236.9 x 148.1	31.3	34.6	64.3	67.6	40.98	32.08
120	258.5 x 161.5	37.1	40.8	70.1	73.8	44.48	34.78
130	280.0 x 175.0	42.9	46.9	75.9	79.9	47.98	37.48