


REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	02/21/2020




MARKING: E314459 兄 AWM 20276 80°C 30V VW-1
PREMIUM HIGH SPEED HDMI® CABLE WITH ETHERNET


WIRE CONNECTION

P/N	L(FT)
VCB-HD2L-003	3FT
VCB-HD2L-006	6FT
VCB-HD2L-010	10FT
VCB-HD2L-015	15FT

L	T(INCHES)
0~9.9FT	+3IN/-0
10FT~99.9FT	+6IN/-0
100FT+	+12IN/-0



PE BAG PACKING WITH
HDMI PREMIUM LABEL



NOTE:

- CABLE:UL20276 HIGH SPEED HDMI CABLE (28AWG*1P+AL+D+MYLAR)*5C +28AWG*4C+AEB(AL.) JACKET COLOR: BLACK OD:7.3±0.2mm.
- CONNECTOR:P1&P2: HDMI 19P MALE GOLD FLASH PLATED CONTACTS. GOLD FLASH PLATED SHELL WITH BUMPS
- MOLDING BLACK 45P PVC.
- 100% OPEN & SHORT & MIS WIRE TEST
- Max Resolution:3840*2160/60Hz.
- HDMI Premium Certified Cables

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.

©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± ANGULAR: MACH ± BEND ± TWO PLACE DECIMAL ± THREE PLACE DECIMAL ±				TITLE:	
				Premium High Speed HDMI Cable with Ethernet 4K 60Hz UHD, Gripping Connectors XXft	
INTERPRET GEOMETRIC TOLERANCING PER:		NAME	DATE	SIZE	DWG. NO.
MATERIAL CRS		DRAWN	CYK	02/21/2020	B
FINISH POWDER COAT		ENG APPR.	BOBO	02/21/2020	VCB-HD2L-XXX
DO NOT SCALE DRAWING		CHECKED	CP	02/21/2020	REV A
		COMMENTS:		SCALE:	
				SHEET 1 OF 1	