



Performance II Wireless Optical Mouse

USB Micro Receiver with 2.4 GHz Wireless, Four Buttons with Scroll Wheel, 800/1200/1600 dpi, Black

Part No.: [179904](#)

EAN-13: 0766623179904 | UPC: 766623179904

Wireless Mouse that was born to perform

The Manhattan Performance Wireless Optical Mouse II combines modern design with advanced precision and performance. Its top-mount push button instantly shifts resolution from 800 to 1200 to 1600 dpi to suit a wide range of applications, including routine computing tasks or computer games and editing requiring a fine touch. Its full-sized shape and four-button configuration provide direct access to essential commands with minimal wrist movement. A non-slip texture applied to critical surfaces helps provide a secure, comfortable grip. The remarkably small yet powerful USB micro receiver with 2.4 GHz technology provides an effective range up to 10 m (33 ft.) and stores in a special on-board compartment or remains installed for true wireless convenience. Included auto power management helps maintain proper battery levels for long, reliable operation.

Features:

- Wireless freedom via USB micro receiver with 2.4 GHz RF technology offering an effective range up to 10 m (33 ft.)
- Top-mount push-button control to instantly shift resolution between 800, 1200 and 1600 dpi
- Auto-power management to help maintain proper battery levels
- Ergonomic shape and no-slip texture for a secure grip
- On-board storage compartment to protect USB receiver from loss and damage
- Low-friction base for smooth gliding over work surfaces

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Plug-and-play installation; Windows and Mac compatible
- Three-year warranty

Specifications:

Standards and Certifications

- CE
- FCC
- RoHS

General

- Range: 2.4 GHz wireless: up to 10 m (33 ft.)
- Optical sensor: 800 / 1200 / 1600 dpi resolution
- Right, left and center mouse with scroll wheel and resolution adjustment button
- Automatic power save/power off mode
- Battery details:
 - Type: alkaline
 - Battery size: AA
 - Number of batteries required to power product: 1 (included)
 - Battery voltage: 1.5 V
 - Battery capacity: 2400 mAh
 - Number of battery cells: 1

Physical

- Dimensions mouse: 56 x 95 x 40 mm (2.20 x 3.74 x 1.57 in.)
- Dimensions USB micro receiver: 22 x 5 x 14 mm (0.8 x 0.2 x 0.5 in.)
- Weight: 73 g (2.58 oz.)
- Material: ABS plastic

Operating Environment

- Operation temperature: -5 - 50°C (23 - 122°F)
- Storage temperature: -20 - 60°C (-4 - 140°F)
- Operation humidity (noncondensing): 10 - 85% RH
- Storage humidity (noncondensing): 10 - 95% RH

System Requirements

- Compatible with Windows XP/Vista/7/8.1/10 and Mac OS

Package Contents

- Performance Wireless Optical Mouse II
- AA battery
- Instructions

