



HP ScanJet Pro N4600 fnw1

(20G07A)

Network connected, high-speed flatbed Scanner with HP EveryPage technology.

Boost productivity for professional scanning tasks with the fast, reliable, network connected HP ScanJet Pro, designed for scanning up to 6,000 pages daily. Automate workflows with shortcuts and fast, two-sided scanning from the auto document feeder.



Work-team Productivity.

- Scan up to 80 images (40 pages) per minute¹ with a 100 page, two-sided, single-pass auto document feeder.
- Optimize document workflows. Scan directly to e-mail, network folders, or a PC via Ethernet or WiFi connection.
- Don't wait for warm-up – Instant-on Technology lets you begin scanning quickly.²
- Place the scanner where the work happens. With a compact design that fits on the desktop.

Easy to use.

- Scan a variety of documents including books, magazines, and ID cards from the ADF or the Legal-size flatbed.
- Connect and scan directly to a storage device using the host USB plug.
- Simplify work processes with pre-configured workflows, and powerful editing tools from HP Scan Pro software.
- Scan directly to document applications using HP's full-featured WIA, ISIS and TWAIN support.

Workteam Reliability.

- Capture every page easily, HP EveryPage technology uses ultrasonic sensing to separate pages in the ADF.
- Designed for the productive workteam with high daily volumes of scanning up to 6,000 pages daily.
- Rely on automated scanning from the 100 page automatic document feeder with single-pass two-sided scanning.
- Get sharp, true-to-life scans of documents, graphics, and photos with up to 1200 dpi resolution.

Strong Security.

- Secure with genuine HP boot code signature validation that prevents booting if the code has been altered.
- Worry-free updates, validate and ensure any firmware updates are code-signed, Only authentic HP code is loaded.



Footnotes

¹ Scan speeds measured at 300 dpi (black and white, grayscale, and color). Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

² Compared with products that use traditional fusing and cold cathode fluorescent lamp (CCFL) copying.

Accessories and services

| | |
|---------------------|---|
| Accessories | C9943B HP ADF Cleaning Cloth Package |
| Maintenance Kit | 4T8E5A HP ScanJet A Separation Unit (100,000 pages) 618J9A HP ScanJet B Roller Unit (100,000 pages) |
| Service and Support | U35KDE HP 3 year Next Business Day Advanced Exchange Service for ScanJet Pro N4600 fww1 (All EMEA except Baltics, Serbia, Middle-East, Turkey) U35KJE HP 3 year Onsite Exchange Service for ScanJet Pro N4600 fww1 (Austria, Belgium, Switzerland, Denmark, Finland, Netherlands, Norway, Sweden, Spain, Portugal, Russia, Poland, Greece) U34WZE HP 3 year Advanced Exchange Service for ScanJet Pro N4600 fww1 (Baltics, Serbia, Middle-East) U34XOE HP 3 year Return to Depot Service for ScanJet Pro N4600 fww1 (Turkey only) U34X1PE HP 1 year Post Warranty Next business day Advanced Exchange Service for ScanJet Pro N4600 fww1 (All EMEA except Baltics, Serbia, Middle-East, Turkey) U34X2PE HP 1 year Post Warranty Onsite Exchange Service for ScanJet Pro N4600 fww1 (Austria, Belgium, Switzerland, Denmark, Finland, Netherlands, Norway, Sweden, Spain, Portugal, Russia, Poland, Greece) U34X3PE HP 1 year Post Warranty Advanced Exchange Service for ScanJet Pro N4600 fww1 (Baltics, Serbia, Middle-East) U34X4PE HP 1 year Post Warranty Return Service for ScanJet Pro N4600 fww1 (Turkey only) |

Technical specifications

| | |
|--------------------------------|---|
| Control panel | 2.8-in (7.11-cm) Touchscreen, Buttons (Power, Back, Home, Help) |
| Scanner specifications | Scanner type ADF; CIS scanning technology; Flatbed; Scan technology ADF; Flatbed; Contact Image Sensor (CIS); Scan input modes : Scan front-panel function: Scan to Computer, Scan to E-mail, Scan to Network Folder, Scan to Share Folder, Scan to USB Drive and Everyday Scan. HP Scan in Win OS, HP Easy Scan/ICA in Mac OS and THIRD parties applications via TWAIN; Twain version : Version 2.4; Colour scanning : Yes; Output resolution dpi settings : 75; 150; 200; 240; 300; 400; 500; 600; 1200 ppi; Image scaling or enlargement range : Will not perform any arbitrary scaling |
| Scan Size | ADF: Maximum 216 x 5362 mm; Minimum 89 x 148 mm; Flatbed : 216 x 356 mm |
| Scan speed ² | Up to 40 ppm/80 ipm (b&w, gray and color, 300 dpi) |
| Scan resolution | Optical Up to 600 dpi (color and mono, ADF); Up to 1200 dpi (color and mono, flatbed); Hardware : Up to 600 x 600 dpi (color and mono, ADF); Up to 1200 x 1200 dpi (color and mono, flatbed) |
| Scan file format | For text and image pages: PDF, JPEG, PNG, BMP, TIF, Text(TXT), Rich Text(RTF), SEARCHABLE PDF, PDF/A, Word(DOC), Word(DOXX), Excel(XLS), Excel(XLSX), CSV |
| Scanner advanced features | One pass duplex scanning; Multi-feed detection sensor; Configurable Scan shortcuts with HP Scan (included): OCR; Auto exposure; Auto threshold; Auto detect colour; Background smooth/removal; Auto detect size; Straighten content; Enhance content; Auto orient; Multicolour dropout; Edge erase; Blank page options: Delete Blank Page, Blank Page Detection Sensitivity, Zonal Blank Detect; Merge pages; Document separation options: Zonal Text Separation, Barcode Separation, Blank Page Separation (Front/Back/Both/Any side selection), Add Page Separator Manually; Auto Feed; Show Viewer After Scan and Post Scan Operations are: Mark the image for Deletion, Rotate option, Move Left/Right, Create/Delete New Selection, Save as Scan Area, Manual Straighten option, Drag and Crop, Undo Options, image - Basic Zoom Slider, Open in Zoom Window(Zoom, Crop, Rotate); Background Clean-up options: Clean-up Background, Remove: make white, Smooth: make consistent, Remove Holes, Multi-Streaming: Single zone Selection for Zonal OCR, Barcode and QR Code; PDF options: PDF Security Settings (Applicable for PDF and Searchable PDF), Password Security & Document Permission Settings, PDF - iHQC compression, File Size/Quality Slider; TIFF Compression Options: for Gray or Color: Uncompressed/LZW/Jpeg-TIFF, for BW: Uncompressed/LZW/TIFF G3/TIFF G4; File Name Options: Base Name, Date, Time, Document Counter, Barcode Value, Zonal Text, File name sequence Settings, If File name already exists Actions - Overwrite/Append Date Time Stamp/Prompt for File Name, Intelligent File Naming; Destinations options: Email (Mail Clients, Save Local Copy Option, Local or NW), Folder, Save Folder path, Show Save as Dialog Box, After Saving the File(s) action, Printer/Fax, Plugins available if not already included: SMTP, SFTP, Box and Evernote, SharePoint, SharePoint365, Google Drive, Dropbox, OneDrive, One Drive for Business and more; Enable Book Scan (Flatbed); Vertical Streak Removal/Detection; Multi Document Scanning; Enable Desktop Icons creation for Scan Profiles/Shortcuts; Shortcut Management: Create new Scan Shortcut, Delete Shortcut, Rename Shortcut, Shortcut Move Up/Down, Shortcut - Save/Undo, Restore Shortcut Defaults-Factory Settings, Import/Export Shortcut; retrieve shortcuts from Scanner without accessing the software on the PC; Configurable Scan shortcuts as standalone (using only the firmware of the scanner) without using the HP Scan Software: Scan to Computer, E-mail, Network Folder, SharePoint, Scan to USB Drive |
| Grayscale levels/Bit depth | 256/24-bit (external), 48-bit (internal) |
| Duty cycle | Recommended daily duty cycle: 6000 pages |
| Auto document feeder capacity | Standard, 100 sheets (80 g/m ²) |
| Connectivity | Standard Ethernet 10/100/1000 Base-T, USB 3.0, WiFi 802.11 b/g/n, WiFi Direct |
| Memory | Standard 512 MB |
| Media handling | |
| Media types | Paper (banner, inkjet, photo, plain), envelopes, labels, cards (greeting, index) |
| Media size (ADF) | Letter; Legal; Executive; A4; A5; A6; B5; B5 (JIS) |
| Media weight (ADF) | 45 to 120 g/m ² |
| Compatible operating systems | Windows 11; Windows 10; Windows 8; Windows 8.1; Windows 7; Windows Server; macOS 10.14 Mojave; macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; Linux |
| Minimum system requirements | PC: Microsoft® Windows® (11, 10, 8.1, 7: 32-bit and 64-bit, 2008 R2, 2012 R2, 2016, 2019); 2 GB available hard disk space, Internet connection, Microsoft® Internet Explorer or any browser |
| Software included | HP Scan Software, HP Scanner Device Driver, HP WIA scan driver, HP TWAIN scan driver, HP Scanner Tools Utility, ISIS driver |
| Scan Server Specifications | |
| Security management | Power button to on/off |
| Dimensions and weight | |
| Product dimensions (W x D x H) | Minimum : 536.5 x 325.4 x 133.3 mm; Maximum : 536.5 x 442.6 x 387.42 mm |
| Package dimensions (W x D x H) | 645 x 245 x 499 mm |
| Product weight | 6.1 kg |
| Package weight | 7.8 kg |
| Operating environment | Temperature : 17.5 to 25°C Humidity : 30 to 70% RH |
| Storage | Temperature : -40 to 60°C |
| Power | Requirements : Input Voltage: 100 to 240 VAC; Consumption : 17.4 watts (Active-Scanning), 7.5 watts (Ready), 1.9 watts (Sleep), 0.06 watts (Auto-Off), 0.06 watts (Manual-Off) ; ENERGY STAR : Yes |
| Certifications | IEC62368-1:2018, IEC 60950-1:2005 +A1 and all applicable amendments; CSA/UL 60950-1, 2nd edition (2007); EN 60950-1:2006 +A11 +A1 +A12+A2; EAC safety; Canada cUL CoC; China CCC; European Union CE; Kenya PVOC; Kuwait TER; Nigeria SON; Saudi Arabia SASO; South Africa NRCs; Taiwan BSMI; Ukraine safety approval Electromagnetic compatibility : Class B Emissions; CISPR 32:2015 (International); European Union EMC Directive 2004/108/EC, EN 55032:2015 (CE mark); China GB9254-2008 (CCC); Taiwan CNS13438:2006 (BSMI); USA CFR47 Part 15, Subpart B (FCC); ICES-003:2020 Issue 7 (Canada); Australia C-tick (includes New Zealand); KN 22 and Korea KCC; EAC EMC Certificate; Ukraine EMC approval; EN 61000-3-2:2014 (harmonics); EN 61000-3-3:2013 (flicker); Immunity 505035:2017 CECP; SEPA; IT ECO Declaration; EPEAT® Silver registered |
| What's in the box | Z0G07A HP ScanJet Pro N4600 fww1 Scanner; Install guide; Supporting flyers; Cushions; USB cable; Power adapter; Power cords |
| Warranty | One-year limited hardware warranty, phone and Web support included. Warranty may vary by country as required by law. Go to http://www.hp.com/support to learn about HP world-class service and support options in your region. |

Technical specifications disclaimers

¹ EPEAT® Silver registered where applicable. EPEAT registration varies by country. See <http://www.epeat.net> for registration status by country.

² Scan speeds of up to 40 ppm measured at 300 dpi (color) from automatic document feeder when scanning to digital file. Actual speeds may vary depending on scan resolution, network conditions, computer performance and application software.

