

OVERVIEW



1. Power button	4. Volume buttons
2. Card slot	5. Headphone / microphone combo jack (3.5mm)
3. Microphone	6. USB-C 2.0

Notes:

- Card slot is for microSD card (WLAN model) or nano-SIM + microSD card (WWAN model)

PERFORMANCE

Processor

Processor Family

MediaTek Processor or Qualcomm® Snapdragon™ Processor

Processor

Processor Name	Cores	Max Frequency	Memory Support	Processor Graphics
MediaTek Helio G80	Octa-core 2x A75 + 6x A55	A75@2.0GHz / A55@1.8GHz	LPDDR4x	ARM Mali-G52 MC2 GPU

Operating System

Operating System^[1]

Android™ 12 or later

Notes:

1. Lenovo® tablets typically receive at least 1 Android OS upgrade cycle. May vary depending on models, countries, regions, retailers or operators. For latest software upgrade information, please visit [Android Upgrade Matrix](#).

Graphics

Graphics

Graphics	Type	Memory
ARM Mali-G52 MC2 GPU	Integrated	Shared

Chipset

Chipset

MediaTek SoC (System on Chip) platform

Memory

Max Memory

- 3GB soldered memory, not upgradable
- 4GB soldered memory, not upgradable

Memory Type

LPDDR4x

Storage

Storage Support^[1]

- 32GB eMCP on systemboard (eMMC 5.1)
- 64GB eMCP on systemboard (eMMC 5.1)
- 128GB eMCP on systemboard (eMMC 5.1)
- microSD card, supports up to 1TB

Storage Type

Disk Type	Interface	Offering
Flash Memory	eMMC 5.1	32GB / 64GB / 128GB

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Card Reader

MicroSD card slot (WLAN model)

Multi-Media

Speakers

4 stereo speakers, 1W x4, optimized with Dolby® Atmos®

Microphone

Single microphone

Camera

Front 8.0-megapixel RGB, f/2.0, 83° FoV (field of view), fixed focus, 2D face recognition unlock
Rear 8.0-megapixel RGB, f/2.2, 86.2° FoV, autofocus

VoiceCall^[1]

No support

Notes:

1. For LTE voice call models, cellular data plan required. Speeds are based on theoretical throughput and vary based on site conditions and carrier. For details on cellular support, contact your carrier for details.

Sensor

Vibration Motor

No support

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor

Battery

Battery

Integrated Li-Polymer 7500mAh (minimum) / 7700mAh (typical) battery, capable of 20W quick charge

Max Battery Life^[1]

Standby time: 4 wks
Online video playback time: 12 hr
Web browsing time: 14 hr
Music playback time: 60 hr

Charging Time

Over 5 hr to fully charged

Notes:

1. All battery life claims are approximate and based on internal testing under optimal laboratory and network conditions. Actual battery performance will vary and depend on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage.

Power Adapter

Power Adapter

5V/2A (10W) USB-C AC adapter, 100-240V, 50-60Hz

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Color Gamut	Key Features
10.61"	2K (2000x1200)	Multi-touch	IPS	400 nits	Anti-fingerprint	15:9	72% NTSC	220 PPI, refresh rate 60Hz, 85% screen-to-body ratio

Touchscreen

Capacitive-type multi-touch, supports 10-point touch, TDDI technology

Notes:

1. California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product.

For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Pen

- Lenovo Active Pen 3 with replaceable AAAA alkaline battery, tilt detection, 4096 levels of pressure sensitivity, supports WGP, AES 2.0, and MPP 2.0 protocols
- Lenovo Precision Pen 2 with built-in rechargeable battery, 4096 levels of pressure sensitivity, tilt detection, supports WGP, AES 2.0 and MPP 2.0 protocols
- No pen (pen sold separately)

Mechanical

Dimensions (WxDxH)

251.2 x 158.8 x 7.45 mm (9.89 x 6.25 x 0.29 inches)

Weight

Around 465 g (1.03 lbs)

Case Color

- Frost blue, dual-tone design
- Storm grey, dual-tone design

Case Material

PC + ABS + metal for back cover

Buttons

- Power button
- Volume buttons

CONNECTIVITY

Network

WLAN + Bluetooth^[1]

802.11a/b/g/n/ac dual band 1x1 Wi-Fi® + Bluetooth 5.0

WWAN

No support

SIM Card

No SIM card inbox

Cellular Bands

No support

Wi-Fi Direct

Support (Miracast®)

Wi-Fi Display

Support

FM Radio

FM Radio

Location Services

Models	Location
WLAN model	GPS + GLONASS

Notes:

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Standard Ports

- 1x USB-C 2.0 (support data transfer and Power Delivery)
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports

1x microSD card slot (WLAN model)

Notes:

- The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
 - USB 2.0: 480 Mbit/s;
 - USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
 - USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
 - USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
 - Thunderbolt™ 3/4: 40 Gbit/s;
 - FireWire 400: 400 Mbit/s;
 - FireWire 800: 800 Mbit/s

SERVICE

Warranty

Base Warranty^[1]

- 1-year carry-in service
- 1-year mail-in service
- 1-year depot service
- 2-year (1-yr battery) carry-in service
- 2-year (1-yr battery) mail-in service
- 2-year (1-yr battery) depot service
- 2-year (2-yr battery) carry-in service
- 2-year (2-yr battery) depot or carry-in service
- 3-year (1-yr battery) depot service

Notes:

- More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature

Operating: 0°C (32°F) to 40°C (104°F)

Humidity

Maximum humidity: 95%, 39°C (102.2°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft) / 0°C (32°F) to 40°C (104°F)

ACCESSORIES

Bundled Accessories

Bundled Accessories

- Folio case
- None

SOFTWARE

Preinstalled Software

Preinstalled Software^{[1][2]}

- Tablet Center
- YouTube Kids
- Messages
- Google One
- Netflix
- Google Photos

- Google Podcasts
- Google Play
- Google Sheets
- Google TV
- Instant Memo
- YouTube
- Gmail
- Google
- Google Chrome
- Google Docs
- Google Drive
- Files by Google
- Google Duo
- Google Entertainment Space
- Google Kids Space
- Google Lens
- Google Maps
- Amazon Music

Notes:

1. Actual application availability varies by country/region.
2. For Google Kids Space, books and video content may be not available in all regions. Video content is subject to availability of YouTube Kids app. Books content requires the Play Books app. Availability of apps, books, and video content may change without notice. Google Assistant is not available in Google Kids Space. Google Kids Space requires a Google Account for your child. Parental controls require the Family Link app on a supported Android, Chromebook, or iOS device.

CERTIFICATIONS

Green Certifications

Green Certifications

- (Optional) ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

Other Certifications

Other Certifications

TÜV Rheinland® Low Blue Light (Hardware Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

