

PERFORMANCE

Panel

Panel

In-Plane Switching (IPS)

Display Size

21.5 inches (546.1mm)

Max View Area

WxH: 476.1 x 267.8 mm (18.74 x 10.54 inches)

Native Resolution

1920x1080

Aspect Ratio

16:9

Pixel Pitch

0.24795 x 0.24795 mm

DPI

102.4 dpi

Brightness

200 nits (Minimum), 250 nits (Typical)

Contrast Ratio

1000:1

Pixel Response Time

4 ms (extreme mode) / 6 ms (typical mode) / 14 ms (off mode)

Color Gamut

99% sRGB

Viewing Angle

Horizontal: +/- 89°, vertical: +/- 89°

Power Supply

Power Consumption

15 watts typical, 48 watts max

DESIGN

Mechanical

Compatible Tiny

ThinkCentre® Tiny, ThinkStation® Tiny

Bezel Width

Side: 2mm

Buttons

- Power button
- Input Source Switch button
- Menu stick

Cables

Undetachable 3-in-1 cable, embedded into TIO, connects to the I/Os of Tiny (Power connector, USB [supports USB 3.1 Gen 1 / USB 2.0], DisplayPort™™)

Case Color

Raven black

Dimensions (WxDxH)

494.41 x 489.3 x 223 mm (19.46 x 19.3 x 7.87 inches)

Weight

Around 6.05 kg (13.34 lbs)

Mounting

Supports VESA mount 100mm

Stand

- TIO Flex stand, supports -5° to +23° tilt, up to 50mm lift
- Build in DisplayPort connector for Tiny
- Build in USB-A connector for Tiny
- Build in DisplayPort cable for monitor
- Build in USB-B cable for monitor

In the Box

- Information flyer
- Manual
- Monitor Head
- Monitor Stand
- Power cord

CONNECTIVITY

Ports

Rear Ports

- 1x USB 3.2 Gen 1
- 1x USB-B
- 1x VGA
- 1x HDMI® 1.4
- 1x DisplayPort 1.2

Top Ports

1x USB 3.2 Gen 1

Left Ports

- 2x USB 3.2 Gen 1
- 1x headphone (3.5mm)

SERVICE

Warranty

Base Warranty^[1]

- TIO Flex stand: 1-year CRU warranty
- Monitor: up to 3-year warranty

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

CERTIFICATIONS

Green Certifications

Green Certifications

- ENERGY STAR® Certified
- TCO Certified
- RoHS compliant

Other Certifications

Other Certifications

TÜV Rheinland® Eye Comfort Certification

responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

